

# SIEMENS

CATALOG NO. 3F3Y300FCLN3D16

SERIAL NO. SERIES H

300 kVA 60 Hz 3 PHASE

5.5 % IMP AT 135 °C

115 °C RISE 30 °C AVG. AMBIENT

220 °C TEMP CLASS 40 °C MAX. AMBIENT

PRIMARY ( H1 H2 H3 ) 480V V 10 kV BIL

SECONDARY( X0 X1 X2 X3 ) 208Y/120V V 10 kV BIL

WINDING MATERIAL CU

ENCLOSURE TYPE 3R WEIGHT 2050LBS

ENERGY EFFICIENCY EXCEEDS CSA DOE 10 CFR PART 431:2016  
C802.2-2012


SPACINGS BETWEEN ANY VENTILATED ENCLOSURE PANEL AND  
ANY ADJACENT WALL SHALL BE A MINIMUM OF 5 INCHES  
EXCEPT WHEN WALL MOUNTED USING APPROVED WALL MOUNTING KIT  
SOUND LEVEL IS 3 DB LOWER THAN NEMA ST20 REQUIREMENTS

SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS  
BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL

NEMA Class ANN Dry Type Transformer

Siemens Industry, Inc. Norcross, GA

des00066



| VOLTS | CONNECT |
|-------|---------|
| 504   | 1       |
| 492   | 2       |
| 480   | 3       |
| 468   | 4       |
| 456   | 5       |
| 444   | 6       |
| 432   | 7       |



SEISMIC QUALIFICATIONS, FLOOR MOUNT ONLY  
OSP-0136-10 IBC 2012/ASCE 7-10  
SDS<=2.0g Z/h=1 Ip=1.5



3F3Y300FCLN3D16

| REVISION | DATE | BY      | DATE     | BY |
|----------|------|---------|----------|----|
|          |      | DRAWN   | 16/02/01 | PP |
|          |      | CHEK'D  |          |    |
|          |      | VERIF'D |          |    |

|  |           |                 |
|--|-----------|-----------------|
| <p>Confidential - Property of<br/>Siemens Industry, Inc.</p> |           |                 |
| CUSTOMER   | ORDER NO. | DWG. NO.        |
|  |           | 3F3Y300FCLN3D16 |
|  |           | SH 1 OF 2       |

FRONT VIEW




SIDE VIEW




All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY - OUTDOOR

H.V.1. TERMINAL DETAIL



L.V.1. TERMINAL DETAIL



CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential - Property of  
Siemens Industry, Inc.

| REVISION | DATE | BY | DATE    | BY       | CUSTOMER                  |
|----------|------|----|---------|----------|---------------------------|
|          |      |    | DRAWN   | 16/02/01 | PP                        |
|          |      |    | CHEK'D  |          |                           |
|          |      |    | VERIF'D |          |                           |
|          |      |    |         |          | ORDER NO.                 |
|          |      |    |         |          | DWG. NO.                  |
|          |      |    |         |          | 3F3Y300FCLN3D16 SH 2 OF 2 |