

Pushbutton Units and Indicator Lights

30 mm Heavy Duty, Watertight/Oiltight, Class 52

Selector switch operators

Selection and ordering data

Version	Lever type	Color of lever insert	Cam ¹⁾	Order no.	Weight approx.	Pack
					lbs.	unit
Selector Switches with 2 switching positions						
Maintained operation	Short lever, non-Illuminated	white	A	52SX2AAB		1
	Long lever, non-Illuminated	white	A	52SW2AAB		1
Spring return from right operation	Short lever, non-Illuminated	white	A	52SX2ACB		1
	Long lever, non-Illuminated	white	A	52SW2ACB		1
Selector Switches with 3 switching positions						
Maintained operation	Short lever, non-Illuminated	white	B	52SX2BAB		1
	Long lever, non-Illuminated	white	B	52SW2BAB		1
	Short lever, non-Illuminated	white	C ²⁾	52SX2CAB		1
	Long lever, non-Illuminated	white	C ²⁾	52SW2CAB		1
	Short lever, non-Illuminated	white	D	52SX2DAB		1
	Long lever, non-Illuminated	white	D	52SW2DAB		1
	Short lever, non-Illuminated	white	E	52SX2EAB		1
	Long lever, non-Illuminated	white	E	52SW2EAB		1
	Short lever, non-Illuminated	white	G	52SX2GAB		1
	Long lever, non-Illuminated	white	G	52SW2GAB		1
Spring return from right operation	Short lever, non-Illuminated	white	B	52SX2BCB		1
	Long lever, non-Illuminated	white	B	52SW2BCB		1
	Short lever, non-Illuminated	white	C ²⁾	52SX2CCB		1
	Long lever, non-Illuminated	white	C ²⁾	52SW2CCB		1
	Short lever, non-Illuminated	white	D	52SX2DCB		1
	Long lever, non-Illuminated	white	D	52SW2DCB		1
	Short lever, non-Illuminated	white	E	52SX2ECB		1
	Long lever, non-Illuminated	white	E	52SW2ECB		1
	Short lever, non-Illuminated	white	G	52SX2GCB		1
	Long lever, non-Illuminated	white	G	52SW2GCB		1
Spring return from left operation	Short lever, non-Illuminated	white	B	52SX2BBB		1
	Long lever, non-Illuminated	white	B	52SW2BBB		1
	Short lever, non-Illuminated	white	C ²⁾	52SX2CBB		1
	Long lever, non-Illuminated	white	C ²⁾	52SW2CBB		1
	Short lever, non-Illuminated	white	D	52SX2DBB		1
	Long lever, non-Illuminated	white	D	52SW2DBB		1
	Short lever, non-Illuminated	white	E	52SX2BBB		1
	Long lever, non-Illuminated	white	E	52SW2BBB		1
	Short lever, non-Illuminated	white	G	52SX2GBB		1
	Long lever, non-Illuminated	white	G	52SW2GBB		1
Spring return from left and right operation	Short lever, non-Illuminated	white	B	52SX2BDB		1
	Long lever, non-Illuminated	white	B	52SW2BDB		1
	Short lever, non-Illuminated	white	C ²⁾	52SX2CDB		1
	Long lever, non-Illuminated	white	C ²⁾	52SW2CDB		1
	Short lever, non-Illuminated	white	D	52SX2DDB		1
	Long lever, non-Illuminated	white	D	52SW2DDB		1
	Short lever, non-Illuminated	white	E	52SX2EDB		1
	Long lever, non-Illuminated	white	E	52SW2EDB		1
	Short lever, non-Illuminated	white	G	52SX2GDB		1
	Long lever, non-Illuminated	white	G	52SW2GDB		1
Selector Switches with 4 switching positions						
Maintained operation	Non-Illuminated, Short lever	white	B	52SA2HAB		1
	Non-Illuminated, Long lever	white	B	52SB2HAB		1



1) For contact operation, see cam selection table on page 10/123.

2) C- Cam is limited to 4 contact blocks, 1 or 2 pole.