

Terminal Blocks

8WA1 Terminals with Screw Connection

Circuit-breaker terminals
for auxiliary circuits

Selection and ordering data

With insulating body of moulded thermoplastic -
Screw connections on both sides, for two conductors each

Dimensions ¹⁾	Circuit diagram	Maximum rated voltage	Rated uninter- rupted current I_N A	Order No.	Price
	Terminal size 1.5 · Assembly width 12.5 mm · AWG 14-12 @ AWG 14				
	Circuit-breaker terminal with short-circuit release,				
		AC 240 V, DC 60 V	1 2 4 6 10	8WA1 011-1SF24 8WA1 011-1SF25 8WA1 011-1SF26 8WA1 011-1SF27 8WA1 011-1SF28	
	Circuit-breaker terminal with overload and short-circuit release,				
		AC 240 V, DC 60 V	1 2 4 6 10	8WA1 011-2SF24 8WA1 011-2SF25 8WA1 011-2SF26 8WA1 011-2SF27 8WA1 011-2SF28	
	Terminal size 1.5 · Assembly width 22.5 mm				
	Circuit-breaker terminal with short-circuit release, auxiliary switch with 1 NO and 1 NC contact				
		AC 240 V, DC 60 V	1 2 4 6 10	8WA1 011-6SF24 8WA1 011-6SF25 8WA1 011-6SF26 8WA1 011-6SF27 8WA1 011-6SF28	
	Circuit-breaker terminal with overload and short-circuit release, auxiliary switch and through-connection AWG 14-12 @ AWG 14				
		AC 240 V, DC 60 V	1 2 4 6 10	8WA1 011-4SF24 8WA1 011-4SF25 8WA1 011-4SF26 8WA1 011-4SF27 8WA1 011-4SF28	
Circuit-breaker terminal with overload and short-circuit release, auxiliary switch with 1 NO and 1 NC contact					
	AC 240 V, DC 60 V	0,5 1 2 4 6 10	8WA1 011-8SF23 8WA1 011-8SF24 8WA1 011-8SF25 8WA1 011-8SF26 8WA1 011-8SF27 8WA1 011-8SF28		

Accessories

Example	For terminals	Rated uninter- rupted current A	Description	Length mm ¹⁾	Fig. No.	Order No.	Price
	8WA1 011-1SF2, 8WA1 011-2SF2, 8WA1 011-4SF2, 8WA1 011-6SF2, 8WA1 011-8SF2.	76	Feeder terminal connection up to 16 mm ²	-		8WA1 822-7VD00	
	8WA1 011-1SF2, 8WA1 011-2SF2.	65	Link rail, one-pole 18 connections 9 connections	206 104		8WA1 822-7VD06 8WA1 822-7VD07	
	8WA1 011-4SF2, 8WA1 011-6SF2, 8WA1 011-8SF2.	65	Link rail, one-pole 10 connections 5 connections	206 104	① ②	8WA1 822-7VD01 8WA1 822-7VD02	
	8WA1 011-4SF2.	120	Link rail, two-pole 9 connections/pole 5 connections/pole	206 104	③ ④	8WA1 822-7VD03 8WA1 822-7VD04	

Labelling accessories see page 15/40 - 43.

1) 25.4 mm = 1.00 inch.