

Terminal Blocks

8WA2 Terminals with Cage Clamps

Through-type terminals


Selection and ordering data

With insulating body of molded thermoplastic · Front connection with Cage Clamps

Dimensions ²⁾	IEC ratings uninterrupted current	UL ratings current / voltage	Description	Color	Fig. No.	Height H	Depth D	Order No.	Price
	IEC ratings insulation voltage					mm ²⁾	mm ²⁾		

Through-type terminals with 3 clamping points

Terminal size 2.5 mm² · Overall width 5.2 mm AWG 28-14 AWG 26-14




24 A 800 V	15 A 600 V	Through-type terminal	light gray blue	73.5	28.6	8WA2 011-1DF30 8WA2 011-1BF33
		Barrier	yellow ②			8WA2 813
		Small partition	yellow ⑩			8WA2 836
		Retaining partition for link rail	light gray ⑫			8WA2 835

Terminal size 4 mm² · Overall width 6.2 mm AWG 28-12 AWG 26-12

32 A 800 V	20 A 600 V	Through-type terminal	light gray blue	79.5	28.6	8WA2 011-1DG30 8WA2 011-1BG33
		Barrier	yellow ②			8WA2 813
		Small partition	yellow ⑩			8WA2 836
		Retaining partition for link rail	light gray ⑫			8WA2 835

Through-type terminals, 1-pole, with 4 clamping points

Terminal size 2.5 mm² · Overall width 5.2 mm AWG 28-14 AWG 26-14




24 A 800 V	10 A 300 V	Through-type terminal	light gray blue			8WA2 011-1DF40 8WA2 011-1BF43
		Barrier	yellow ②			8WA2 813
		Small partition	yellow ⑩			8WA2 836
		Retaining partition for link rail	light gray ⑫			8WA2 835


Two-tier terminals

Two-tier terminals, 1-/2-pole, with 4 clamping points

Terminal size 4 mm² · Overall width 6.2 mm AWG 28-12 AWG 26-12



Design:



32 A 690 V	20 A 600 V	2-pole with 2 × 2 clamping points	light gray ¹⁾ blue			8WA2 011-2DG20 8WA2 011-2BG23
32 A 800 V	20 A 600 V	1-pole with 1 × 4 clamping points	light gray blue			8WA2 011-2DG40 8WA2 011-2BG43
		Barrier	yellow ③			8WA2 812
		Small partition	yellow ⑩			8WA2 836
		Retaining partition for link	light gray ⑫			8WA2 835
		Label holder (included in scope of supply of two-tier terminal, can also be used for through-type terminal)	light gray ⑦			8WA2 850

Linking accessories see page 15/13, other accessories see page 15/14, labelling accessories see page 15/40 - 43.

1) Included in the scope of delivery are 2 label holders, 2 additional holders can be added.
2) 25.4 mm = 1 inch