

BOX TERMINAL 3 PCS. ACCESSORY FOR: 3VA6 400/600



Model	
Product brand name	SENTRON
Product designation	accessories
Connections according IEC	
Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / finely stranded / minimum 	35 mm ²
<ul style="list-style-type: none"> • for copper cable / finely stranded / maximum 	240 mm ²
<ul style="list-style-type: none"> • for copper cable / stranded / minimum 	35 mm ²
<ul style="list-style-type: none"> • for copper cable / stranded / maximum 	300 mm ²
Wire stripping length	26 mm
Tightening torque / when using copper cables	
<ul style="list-style-type: none"> • stranded 	<= 95 mm ² : 16 Nm, >= 120 mm ² : 28 Nm
<ul style="list-style-type: none"> • finely stranded 	<= 95 mm ² : 16 Nm, >= 120 mm ² : 28 Nm
Connections according UL	
Wire stripping length	1.0 in
Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / stranded / minimum 	1/0 AWG
<ul style="list-style-type: none"> • for copper cable / stranded / maximum 	500 kcmil

<ul style="list-style-type: none"> • for copper cable / finely stranded / minimum • for copper cable / finely stranded / maximum 	<p>1/0 AWG</p> <p>500 kcmil</p>
<p>Tightening torque / when using copper cables</p> <ul style="list-style-type: none"> • stranded • finely stranded 	<p><= 4/0 AWG: 140 lb-in, >= 250 kcmil: 250 lb-in</p> <p><= 4/0 AWG: 140 lb-in, >= 250 kcmil: 250 lb-in</p>

Certificates

General Product Approval	EMC	Declaration of Conformity	other
--------------------------	-----	---------------------------	-------



[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9473-0JA13>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9473-0JA13>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9473-0JA13

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/20/2017