

WIRE CONNECTOR 2 CABLES 4 PCS. ACCESSORY FOR: 3VA6
150/250








Model	
Product brand name	SENTRON
Product designation	accessories
Design of the product	circular conductor terminal

Connections according IEC	
Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / finely stranded / minimum 	25 mm ²
<ul style="list-style-type: none"> • for copper cable / finely stranded / maximum 	150 mm ²
<ul style="list-style-type: none"> • for copper cable / stranded / minimum 	25 mm ²
<ul style="list-style-type: none"> • for copper cable / stranded / maximum 	150 mm ²
<ul style="list-style-type: none"> • for aluminum cable / stranded / minimum 	25 mm ²
<ul style="list-style-type: none"> • for aluminum cable / stranded / maximum 	150 mm ²
Wire stripping length	25 / 50 mm
Tightening torque / when using copper cables	
<ul style="list-style-type: none"> • stranded 	31
<ul style="list-style-type: none"> • finely stranded 	31

Connections according UL	
Wire stripping length	1.0 / 2.0 in

Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / stranded / minimum • for copper cable / stranded / maximum • for copper cable / finely stranded / minimum • for copper cable / finely stranded / maximum • for aluminum cable / stranded / minimum • for aluminum cable / stranded / maximum 	<p>4 AWG 300 kcmil 4 AWG 300 kcmil 4 AWG 300 kcmil</p>
Tightening torque / when using copper cables	
<ul style="list-style-type: none"> • stranded • finely stranded 	<p>275 lb-in 275 lb-in</p>

Certificates

General Product Approval	EMC	Declaration of Conformity	other
 CSA	 UL		 RCM
		 EG-Konf.	Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9244-0JJ22>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9244-0JJ22>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)





http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9244-0JJ22

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/20/2017