



Unless otherwise specified dimensions are in inches tolerances are non-cumulative unless specified otherwise.		Confidential - Property of Siemens Industry, Inc. Building Technologies Division	
XX ±.030	XXX ±.015	SCLD6 MOUNTING BRANCH BUS	
Do not scale drawing		Dwg No.	12-B-2013-00
Rev	Date	Scale	NDINE
4	1B-908 04-13-95	1:1	
3	1B-184 10-31-91	1:1	
2	1A-870 3-22-91	1:1	
1	1A-280 11-30-90	1:1	
0	1A-066 2-16-89	1:1	

Dwg No. 12-B-2013-00
 Sht 1 of 4
 AutoCAD filename: 1B/RB0650

FOR USE WITH SCLD6 FRAME BREAKERS MOUNTED
 IN SPP/FPP/S4/F1/P4 PANELBOARDS (SHALLOW BOX).

Apvd PM 11-30-90	ITEM	DESCRIPTION	PC. NO.	QTY.
	1	A PHASE BRANCH BUS	12-B-4008-06	1
	2	B PHASE BRANCH BUS	12-B-4008-07	1
	3	C PHASE BRANCH BUS	12-B-4008-08	1
	4			
	5	MOUNTING BRACKET	15-B-3032-01	1
	6	BARRIER CLIP	11-B-3007-03	2
	7	BARRIER CLIP	11-B-3007-04	2
	8	LOAD BARRIER	11-B-4501-01	1
	9	LOAD BARRIER	11-B-4501-04	1
	10	COVER PLATE	12-6487-03	1
	11	CIRCUIT I. D. CARD	11-7505-01	1
	12	CARD HOLDER	11-7506-01	1
	13	5/16-18 X 1 1/4 HHMS	11-1566-07	3
	14	5/16 LOCK WASHER	11-1618-04	3
	15			
	16	STRAP-BUS HARDWARE KIT	11-B-2023-05	1
	17	1/4-20 X 3/8 SHHWS	11-1553-02	14
	18	1/4-20 X 2 1/2 SRHMS	11-1542-13	2
	19			
	20			
	21			
	22			
	23			
	24	NEUTRAL LUG ASSEMBLY	12-B-2105-06	1
	25			
	26			
	27			
	28	INSTRUCTION SHEET	31-1213-01	1
	29	CARTON LABEL	15-A-1027-01	1
	30	CARTON	48001057 ▲	1
	31			
	32			
	33			
	34			
	35			
Revisions 0: 1A-280/4:1B-148 10-06-92 1:1A-870 3-22-91/5:1B-908 5-8-95 2:1B-184 10-31-91/6:1C-831A 4-12-04 3:1B-184B 1-17-92/7:1C-831B 7-31-06				
Chk SH 11-30-90	FOR I. T. E. TYPE BREAKERS: SCLD6			
By MC 11-20-90	MERCHANDISE KIT NO. SSCL			
Confidential - property of Siemens Industry, Inc. Building Technologies Division		SCLD6 BRANCH BREAKER S4, MOUNTING - COPPER BUS	12-B-2013-03 Dwg No.	7 Rev.
		Title	Sht. 1 Of 1	