

SIEMENS



Selection & Application Guide

Un-assembled ES Load Centers

www.usa.siemens.com/loadcenters

Siemens Un-assembled ES program

- Available for the most popular ES Load Centers
- Gives the ability to order in bulk
- Enclosures will have minimal packaging for less hassle and waste at the job site
- Keeps the covers separate to prevent damage or theft
- Includes full size cardboard covers to keep the interior safe during painting
- All main lug panels include factory installed ground bars



Construction and Ratings

Enclosure

All enclosures are NEMA type 1 rated, conform to UL standard 50, and are fabricated using G90 galvanized steel & coated with a baked-on polyester powder coating.


Interior

Aluminum bus bars are mounted on a thermoplastic interior designed for extended life and rated 100-225 amps as marked.

Applicable US Standards

UL67, UL50

Catalog Numbering System



Mobile Home 1-phase Un-Assembled

1-phase, 3 wire SN, 120/240 Volts AC

- Invertible for bottom feed application.
- 12-30 spaces, 24-48 circuits
- 125-200 Amp
- NEMA Type 1 Enclosures



Amp Rating	Box Catalog Number	Main	No. of Spaces	No. of Circuits	Dimensions			Trim Catalog Number	Pallet Quantity
					H	W	D		
Unassembled Main Lug, 125 - 200 amps									
125	SB2440L1125G	Main Lug	24	40	24	14.5	4.25	ST2440L1125	36
125	SB3040L1125G	Main Lug	30	40	30	14.5	4.25	ST3040L1125	36
200	SB3040L1200G	Main Lug	30	40	30	14.5	4.25	ST3040L1200	36
200	SB4040L1200G	Main Lug	40	40	36	14.5	4.25	ST4040L1200	30

Amp Rating	Box Catalog Number	Main	No. of Spaces	No. of Circuits	Dimensions			Trim Catalog Number	Pallet Quantity
					H	W	D		
Unassembled Convertible, 200 amps									
150/200	SB3040C1200G	Convertible	30	40	36	14.5	4.25	ST3040X1200	30
150/200	SB4040C1200G	Convertible	40	40	36	14.5	4.25	ST4040X1200	30

Amp Rating	Box Catalog Number	Main	No. of Spaces	No. of Circuits	Dimensions			Trim Catalog Number	Pallet Quantity
					H	W	D		
Unassembled Main Breaker, 125 - 200 amps									
125	SB2424B1125	Main Breaker	24	24	24	14.5	4.25	ST2424B1125	36
200	SB3040B1200	Main Breaker	30	40	36	14.5	4.25	ST3040B1200	30
200	SB4040B1200	Main Breaker	40	40	36	14.5	4.25	ST4040B1200	30

Load Center Accessories

Catalog Number	Description	Pack Qty.
Ground Bar Kits		
EC1GB8	Ground Bar Kit-8 Pos	1
EC1GB82	Ground Bar Kit-8 Pos, 2/0 Lug	1
EC2GB12	Ground Bar Kit-12 Pos	1
EC2GB122	Ground Bar Kit-12 Pos, 2/0 Lug	1
EC2GB15	Ground Bar Kit-15 Pos	1
EC2GB152	Ground Bar Kit-15 Pos, 2/0 Lug	1
Main Breaker Kits		
MBK100A	Main Breaker Kit 100-125A 1Ph 22K	1
MBK125A	Main Breaker Kit 125A 1Ph 22K	1
MBK150A	Main Breaker Kit 150A-225A 1Ph 22K	1
MBK200A	Main Breaker Kit 200A-225A 1Ph 22K	1
MBK225A	Main Breaker Kit 225A 1Ph 22K	1
Lug Kits		
ECLK1-2	Neutral Lug Kit #2 To 2/0	1
ECLK2	Neutral Lug Kit #4-2/0	1
ECLK2125	125A Sub Feed Lugs-Uses 2 Spaces	1
ECLK2225	150A-225A Sub Feed Lugs-Uses 4 Spaces	1
Miscellaneous Load Center Accessories		
ECCP1	Pkg Of 100 Circuit Directory	100
ECQF3	Qp/Bq/Ed2 Filler Plate	5
ECMBF125	1 Ph 100&125A Main Breaker Filler Plate	1
ECTS2	Load Center Trim Screws	6
ECTS2W	Load Center Trim Screws White	6
ECLCHINGE	Grey Load Center Hinges	100
ECADHLCDIRLBL	Adhesive Lc Directory Labels	100
ECBONDSCRW	Load Center Bond Screw	10
ECQFL2	Door Lock	1
ECMBR2	Breaker Hold Down	1
ECSBPK02	Standby Power Interlock Kit	1
ECSBPK03	Standby Power Interlock Kit	1

Notes

Notes

Siemens Industry, Inc.
5400 Triangle Parkway
Norcross, GA 30092

1-800-241-4453
info.us@siemens.com

Order No. RPSA-USESL-0915 | Printed in USA |
© 2015, Siemens Industry, Inc.

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.