











# ALPHA FIX Terminal Blocks

## ALPHA FIX SL Compact Terminals, Spring-Loaded

### Through-type terminals

#### Selection and ordering data

Dimensions	Version	Color	DT	Order No.	PS*	Weight per PU approx. kg	
<b>Through-type terminals</b>							
 <p>8WA2 511-1DF20</p>	Terminal size 2.5 mm <sup>2</sup> , width 5 mm  AWG 26-14		Through-type terminals, with two clamping points				
	Gray	A	8WA2 511-1DF20	50 units	0.005		
Blue	A	8WA2 511-1BF23	50 units	0.005			
 <p>8WA2 511-1DF30</p>	Through-type terminals, with three clamping points		Gray	A	8WA2 511-1DF30	50 units	0.007
	Blue	A	8WA2 511-1BF33	50 units	0.007		
 <p>8WA2 511-1DG20</p>	Terminal size 4 mm <sup>2</sup> , width 6 mm  AWG 26-10		Through-type terminals, with two clamping points				
	Gray	A	8WA2 511-1DG20	50 units	0.009		
Blue	A	8WA2 511-1BG23	50 units	0.009			
 <p>8WA2 511-1DG30</p>	Through-type terminals, with three clamping points		Gray	A	8WA2 511-1DG30	50 units	0.010
	Blue	A	8WA2 511-1BG33	50 units	0.010		
<b>Accessories</b>							
 <p>8WA8 522-7WG01</p>	<b>Cover plates</b>		Gray	A	8WA8 522-7WF01	50 units	0.003
	For 2.5 mm <sup>2</sup> through-type terminals		Blue	A	8WA8 522-7WF03	50 units	0.003
	For 4 mm <sup>2</sup> through-type terminals		Gray	A	8WA8 522-7WG01	50 units	0.003
Blue	A	8WA8 522-7WG03	50 units	0.003			
 <p>8WA8 522-7VF02</p>	<b>Connection combs</b>		Yellow	A	8WA8 522-7VF02	60 units	0.060
	For 2.5 mm <sup>2</sup> through-type terminals		Yellow	A	8WA8 522-7VF03	60 units	0.099
	– For two terminals		Yellow	A	8WA8 522-7VF04	60 units	0.132
	– For three terminals		Yellow	A	8WA8 522-7VF10	20 units	0.124
	– For four terminals		Yellow	A			
	– For ten terminals		Yellow	A			
	For 4 mm <sup>2</sup> through-type terminals		Yellow	A	8WA8 522-7VG02	60 units	0.115
	– For two terminals		Yellow	A	8WA8 522-7VG03	60 units	0.159
	– For three terminals		Yellow	A	8WA8 522-7VG04	60 units	0.173
	– For four terminals		Yellow	A	8WA8 522-7VG10	20 units	0.149
– For ten terminals		Yellow	A				
 <p>8WA8 522-7WF06</p>	<b>Covers, with warning arrow</b>		Yellow	A	8WA8 522-7WF06	20 units	0.010
	For 2.5 mm <sup>2</sup> through-type terminals		Yellow	A	8WA8 522-7WG06	20 units	0.020
For 4 mm <sup>2</sup> through-type terminals		Yellow	A				
 <p>8WA8 522-7WF07</p>	<b>Test adapters</b>		Black	A	8WA8 522-7WF07	25 units	0.202
	For 2.5 mm <sup>2</sup> through-type terminals		Black	A	8WA8 522-7WG07	25 units	0.215
For 4 mm <sup>2</sup> through-type terminals		Black	A				