



TEL (915) 590-8500
FAX (915) 590-8510

3.75"

6.00"

**Enclosed Switch
General Duty**

Catalog Number	Enclosure	Model
GU221AW	Type 3R	4

Amperes 30	Horsepower Rating		
	Volts-PH	Std.	Max.
	120 AC-1Ø	½	2
	240 AC-1Ø	1-½	3
	240 AC-3Ø	3	7-½

Wire Connector Information:
Line / Neutral Terminals: USE 14-6 Cu/ 12-6 Al 60°/75° C WIRE
Load Terminals: USE 14-8 Cu/ 12-8 Al 60°/75° C WIRE

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	15 LB. IN.	18 LB. IN.	27 LB. IN.

Fuse & Short Circuit Information:
This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, rms symmetrical, 240 Volts maximum, when protected by fuses or circuit breakers rated 30 Amps maximum. (120 Volts Max. on single pole devices.)

Accessories and Replacement Parts:

Service Equipment:
To bond enclosure to neutral, use No. 10 screw provided. Force the screw through the aluminum seal.

Hub Information: Catalog Number: HA075 HA100 HA125
¾" 1" 1-¼"

Use closure plate screws provided, to mount hubs.

Equipment Ground Bar Kit: GSGK60M. USE Cu/Al 60°/75° C WIRE

WIRE SIZE:	14-10 AWG	8 AWG	6 AWG
NOMINAL TORQUE:	35 LB. IN.	40 LB. IN.	45 LB. IN.

Neutral Assembly: Order Catalog No. W410190M.

⚠ DANGER HAZARDOUS VOLTAGE. WILL CAUSE DEATH OR SERIOUS INJURY. Turn off power ahead of switch before doing work inside. Close cover before turning power on.	⚠ PELIGRO VOLTAJE PELIGROSO. CAUSARÁ LA MUERTE O LESIONES GRAVES. Desconectar el suministro de energía al interruptor antes de efectuar cualquier trabajo dentro de la unidad. Cerrar la cubierta antes de conectar la energía.
--	--

This device has been inspected and tested.

Inspection Record No.



UL LISTED
ENCLOSED SWITCH
Issue No. AL-265
File No. E4776

Pc. No. 410384J02

Murray Electrical Products
Siemens Industry, Inc.
Norcross, GA 30092 U.S.A.
Assembled in Mexico (E)



.125" RCR

COMPANY NAME		MATERIAL		SIZE		JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.				PART NO.	
Siemens Industry, Inc.		Semi-Gloss Paper		WIDTH		<input type="checkbox"/> OK TO PRINT AS IS		<input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF		410384J02	
THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.		LAMINATION: NO		3.75"		<input type="checkbox"/> OK TO PRINT WITH CORRECTIONS AS MARKED				DESCRIPTION:	
		INK COLORS		LENGTH						Label	
		Black		6.00"		AUTHORIZED BY		DATE		REVISION LEVEL G	
				CORNER RADIUS						DESIGNER Joel Ortega	
				.125"						CHECKED BY	
										DATE 02/23/11	