

[Siemens.com/mobility](http://Siemens.com/mobility)

## QBT3 Relay

A dc biased, tractive armature, track relay

### General data

Contact Arrangement:	2F 2B
Nominal Rated Voltage:	0.65 V dc
Minimum Percentage Release:	68%
Approximate Weight:	1.63 kg

Note: Refer to the following data sheets:

- 7-1-1 for general information and contact raings.
- 7-2-1 for dimensions.
- 8.2 for tools.
- 8.3 for plugboard and connector details.

Refer overleaf for specific data.




Typical Single Coil Relay

### Description

The operation of the relay is dependent on the polarity of the coil current

## Contact layout viewed from rear



## Packaging

Q-Relays are packed in a carton holding ten relays; the same container is used for quantities of four to nine relays. Quantities less than four are packed individually in cardboard boxes, as are all train-carried relays. Each container has a bar-coded label affixed to the outside, stating details of the packaged relay(s) and the quantity therein.

## EMC Compliance

Q-Relays comply with the relevant emission requirements of EN 55014. It is considered that these relays have inherent immunity to in-service electro-magnetic disturbance.


A Technical Certificate for EU Directive on EMC (89/336/EEC) has been obtained.

## Technical data

SIEMENS Part No. (PAD No.)	CONTACT ARRANGEMENT	RATED VOLTAGE (V dc)	PIN CODE	COIL RES (OHMS)	WDG SPEC 1/108/-	MAX FULL OP. (V dc)	MIN REL (V dc)	PLUGBOARD	REQD No. OF CONNECTORS J4137/3	REMARKS
B18575/1	2F 2B	0.65	XYAGH	4	176	160 MAX OP 140	68% OF ACT OP	J4138/402	10	



Un-drilled plugboard  
Part No. E7218/1



Representation of Relay,  
Plugboard and Retaining clip  
(Clip Part No. J4136/1)