



Curved Glass Corners

CURVED GLASS CORNERS

PRODUCT BROCHURE

ISSUED 2024 06 06





A SLEEK, SOFT LOOK

Take the edge off with a curved glass elevation that seamlessly integrates with the rest of the DIRT Construction System. Get a signature curve with the look you want. Use our modular approach to building to get rapid installation and long-term adaptability. Whether you're streamlining your look or making a statement, our curved glass will change the way you look at construction.





STYLISH SOPHISTICATION

Round out your look and set yourself apart. As people reconsider their relationship to the built environment, curved glass corners offer a distinctive way to define your space. Carve out meaningful collaboration in a curved meeting room or use it as a showcase to create an unforgettable impression.




LET THE LIGHT IN

Glass doesn't just give a sense of visual connection. It allows the transmission of daylight. Lighten the space and elevate the mood. Curved glass corners offer a transparent solution and an acoustic barrier, giving you a clear way to distinguish your environment.



CURVES, NATURALLY

From reduced stress levels to improved productivity, the benefits of biophilic design are well known. Creating space with a variety of shapes and patterns has a direct impact on people using it. Using curved corners to veer away from the straight and narrow offers a refreshing sensory experience.



Curved Glass Corners

SYSTEM FEATURES

01	Choose from Classic Glass rectilinear and sleek Inspire™ extrusions
02	Curves available in a variety of signature radius measurements
03	Get a framed or seamless look
04	Components are precision manufactured to accommodate base building conditions
05	Curved Glass Corners integrate seamlessly with the DIRT™ Construction System
06	Header can attach directly to ceiling, soffit, bulkhead, or structure
	Sleek, non-generational design serves your space today and into the future
	Modularity supports adaptive reuse and future flexibility
	Limit transfer of smoke with our non-rated, smoke partition
	SCS Indoor Advantage Gold certified

01



02



02



02




03



04



05



06



Technical Overview

SIZE

Wall thickness	Inspire: 2" (51 mm) Classic rectilinear: 4" (102 mm)
Maximum Wall Height	Inspire: 10' (3.0 m) Classic rectilinear: 10' (3.0 m)
Glass Thickness	3/8" (10 mm)
	* Frame assemblies that exceed module maximums must be validated by DIRT™ to confirm they meet building code

CURVE RADIUS

Inspire	24" (610 mm), 36" (914 mm), or 48" (1.22 m)
Classic rectilinear	36" (914 mm) or 48" (1.22 m)

TOLERANCES

Wall height adjustability	Inspire: -1/2" (12 mm) +1/2" (15 mm)
	Classic rectilinear: -3/8" (10 mm) +1 1/8" (29 mm)

DOOR TYPES

Swing Door
Sliding Door
Pivot Door

EXTRUSION FINISH OPTIONS

Powder coat

GLASS OPTIONS

Tempered	Clear or low-iron glass
Laminated	Clear or low-iron glass

DOOR OPTIONS

Frameless Glass
Aluminum Framed Glass
Solid Core Wood



BUILD DYNAMIC SPACES

dirtt.com ↗