



**SIEMENS**

*Ingenuity for life*

## Difficult just got easy

**We provide the industry with high-quality elevator cables, backed by decades of experience in the Australian market.**

Our cables have been developed to provide optimum performance, maximum safety and extended life for applications requiring power and control.

Features include ease of installation for high levels of efficiency, and options for maintenance, service and modernisation.

For more information visit:  
[www.siemens.com.au/auto-cables](http://www.siemens.com.au/auto-cables)

### **DCS16 CAT 7- PVC Flat Travelling Cable**

- Compatible with all current cat 7 compliant connecting hardware
- Industry compatible construction & design
- Applications such as CCTV, swipe cards, security, card readers, telephone and display screens
- Capacity to provide application to multiple devices in one single cable
- Adheres to CAT 6 and CAT 7 wiring codes
- AUSTEST AS/CA S008:2010 Approvals

[www.siemens.com.au/auto-cables](http://www.siemens.com.au/auto-cables)

Siemens Part Number	106188332	
Cable	DCS16	
Suspension Device	FCSD-3 100205441	

<b>Specification</b>		DCS16 - 4 (4x2x0.14) + steel support	
<b>Standard reference</b>		EN 50214-2006, GB/T5023.6-2006, IEC /EN60227-6	
<b>Strain bearing member</b>		2x1.8mm steel rope	
<b>Data elements</b>	Type		Cat.7
	Quantity		4
	Conductor	mm <sup>2</sup>	0.14
	Loop resistance	Ω/km	Max 250 @20°C
	Insulation		Foam-PE
	Colour		Pair 1:white-blue, pair 2:white-orange Pair 3:white-green, pair 4:white-brown
	Shield		AL/PET foil around each pair, Tinned copper braid overall pairs.
	Mutual capacitance	nF/km	Nom. 43 @ 800 MHz
	Characteristic impedance	Ω	(100 ± 15) @ (1-100 MHz)
	Velocity of propagation	%	approx. 79
<b>Jacketing</b>	Material		PVC
<b>Jacketing Completed cable</b>	Normal thickness		See drawing
	Approximate weight	kg/km	415
<b>Completed cable</b>	Free suspension length	m	≤80
	Max. travelling height	m	≤150
	Max. travelling speed	m/s	≤6.3 (Acc. EN50214)
	Nominal diameter	mm	36.6 x8.4
	Min. Bending radius	mm	Static application 10x cable thickness
	Bending Test		Min 30000 bending cycles according to EN50214
	Test voltage		750V for data elements
	Operating temperature	°C	-20 to +70
	Acceleration	m/s <sup>2</sup>	< 1.2