



REVISION	DATE	BY	DATE	BY
		DRAWN	08/01/07	CY
		CHEK'D		
		VERIF'D		

Confidential - Property of Siemens Industry, Inc. Building Technologies Division		
CUSTOMER		
ORDER NO.	DWG. NO.	
	1D1Y015FTP1	SH 1 OF 2

SIEMENS

CATALOG NO. 1D1Y015FTP1
 SERIAL NO. SERIES H
15 kVA **60** Hz **1** PHASE
6 % IMP AT **135** °C
115 °C RISE °C AVG. AMBIENT
220 °C TEMP CLASS °C MAX. AMBIENT
 PRIMARY (H1 H3 H2 H4) **240X480** V
 SECONDARY(X4 X2 X3 X1) **120/240** V
 WINDING MATERIAL **AL**
 ENCLOSURE TYPE NEMA-3R WEIGHT 175 LBS
 ENERGY EFFICIENCY NEMA TP 1-2002


SPACINGS BETWEEN ENCLOSURE AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 6 INCHES
 LISTED DISTRIBUTION TRANSFORMER 77US TYPE F
 LR 3902
 E112313
 SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS DO NOT INSTALL IN AREAS ACCESSIBLE TO PUBLIC FOR INSTALLATION SEE INSTRUCTION MANUAL
 NEMA Class **ANN** Dry Type Transformer Siemens Industry, Inc. Norcross, GA




PRIMARY VOLTS	CONNECTION LINES TO	INTER-CONNECT
480	H1,H4	1-H2,2-H3,H2-H3
456	H1,H4	2-H3,3-H2,H2-H3
432	H1,H4	3-H2,4-H3,H2-H3
240	H1,H4	1-H2,2-H3,H1-H3,H2-H4
216	H1,H4	3-H2,4-H3,H1-H3,H2-H4
SECONDARY VOLTS	CONNECTION LINES TO	INTER-CONNECT
240	X1,X4	X2-X3
120/240	X1,X2,X4	X2-X3
120	X1,X2	X2-X4,X1-X3



FRONT VIEW



SIDE VIEW



All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of
Siemens Industry, Inc.
 Building Technologies Division

REVISION	DATE	BY	DATE	BY
		DRAWN	08/01/07	CY
		CHEK'D		
		VERIF'D		

CUSTOMER		
ORDER NO.	DWG. NO.	
	1D1Y015FTP1	SH 2 OF 2

0.1 root 2011/01/11 10:09