



Totally Integrated Power

Fixed-Mounted Circuit-Breaker Switchgear Type NXPLUS up to 40.5 kV, Gas-Insulated



When it comes to medium-voltage power distribution, Siemens has developed a broad realm of products and solutions, based on experience, innovation, and reliability.

The factory-assembled, type-tested, and metal-enclosed NXPLUS switchgear impresses with the advantages of the proven vacuum switching technology – a technology that made gas insulation economical in its class.



Hermetically tight, welded switchgear vessels made of stainless steel as well as single-pole solid insulation make the parts of the primary circuit under high voltage of NXPLUS switchgear insensitive to certain aggressive ambient conditions such as saline air, air humidity, dust, and condensation. The hermetically sealed primary enclosure is independent of environmental effects such as pollution, humidity and small animals. Furthermore, the application is independent of the site altitude.

The use of digital secondary systems and combined protection and control devices ensures clear integration in process control systems, flexible and highly simplified adaptation to new system conditions and thus to cost-efficient operation. A thoroughly convincing switchgear concept that will, under

normal operating conditions, be expected to have a service life of at least 35 years, probably 40 to 50 years, taking the tightness of the enclosed high-voltage part into account. As an option resistance against shock, vibration, and earthquakes can be provided.

The gas-insulated switchgear NXPLUS is a prime choice for use in transformer and switching substations, e.g. in power supply companies, power stations, cement industry, automobile industry, iron and steel works, rolling mills, mining industry, textile, paper and food industries, chemical and petroleum industry, pipeline and offshore installations and so on. It is also commonly used in traction power supply systems.


Your advantages

- Independent of environment and climate
- Maintenance-free
- Compact
- Safe for operators
- Cost-efficient
- Ecological
- Reliable and safe operation



NXPLUS, Medium-Voltage Switchgear

Product range (The following selection is not complete)







Technical data of NXPLUS

Rated		Busbar system	
		Single, double	Single
Voltage	up to	36 kV	40.5 kV
Frequency	Hz	50/60	50/60
Short-duration power-frequency withstand voltage	kV	70	85
Lightning impulse withstand voltage	kV	170	185
Short-circuit breaking current	max. kA	31.5	31.5
Short-time withstand current, 3 s	max. kA	31.5	31.5
Short-circuit making current	max. kA	80/82	80/82
Peak withstand current	max. kA	80/82	80/82
Normal current for busbar	max. A	2,500	2,000
Normal current for feeders	max. A	2,500	2,000

Performance features

- Type-tested according to IEC 62271-200
- Sealed pressure system with SF₆ filling for the entire service life
- Safe-to-touch enclosure and standardized connections for plug-in cable terminations
- Separate 3-pole gas insulated modules for busbar with three-position disconnecter, and for circuit-breaker
- Interconnection of modules with 1-pole insulated and screened module couplings
- Operating mechanisms and transformers are arranged outside the switchgear vessels and are easily accessible
- Metal-enclosed, partition class PM
- Loss of service continuity category for switchgear: LSC 2
- Internal arc classification: IAC A FLR 31.5 kA, 1 s
- No gas work during installation or extension
- Optionally with horizontal pressure relief duct

Dimensions of NXPLUS

NXPLUS switchgear with single busbar				NXPLUS switchgear with double busbar			
							
Dimensions				Dimensions in mm			
Width (spacing)	W1	Feeders up to 2,000 A		600			
	W2	Feeders up to 2,300 A		900			
	W2	Feeders up to 2,500 A		1,200			
Height	H1	Single-busbar switchgear		2,450			
	H2	Double-busbar switchgear		2,600			
Depth	D1	Single-busbar switchgear		1,585			
	D2	Double-busbar switchgear		1,825			

© 2015 Siemens. All rights reserved.
The information provided in this brochure contains descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

Subject to change without prior notice

Siemens AG
Energy Management
Medium Voltage & Systems
Postfach 3240
91050 Erlangen, Germany
www.siemens.com/NXPLUS

Article No. IC1000-G320-A253-V1-7600
Printed in Germany
04.15 1.0 | 1400 / 66213

Read the
QR code
to see further
typicals of this
switchgear!

