



siemens.com/mobility

Velaro Turkey High-Speed Train

for TCDD


The new Velaro® family member is a unique success story: after Spain, China and Russia, the Velaro returned back to Europe as the Velaro D for the Deutsche Bahn (German Railways). Now the Velaro has been chosen in Turkey.

The TCDD (Turkish Railways) granted Siemens a contract in May 2013 for a first train based on Velaro D and over six eight-unit high-speed trains. The agreements also contained up to a seven-year maintenance agreement including spare parts and the delivery of a driving simulator.

For the fulfillment of the first contract, a Velaro was taken from current production and prepared and delivered to Turkey within 180 days. A new Siemens train control system (ETCS) was integrated and changes were made, e.g. in the pantographs as well as the external electricity supply. In the second project, the 6HST Turkey Velaro project, the interior was restructured, and the restaurant area was adjusted to the TCDD's demanding catering design. Furthermore, the 6HST is designed as a pure 25 kV single system vehicle.

Technical Data

Top speed	300 km/h
Train length	200 m
Electricity supply	AC 25 kV / 50 Hz
Traction performance	8,000 kW
Brakes	Generator, pneumatic
Track width	1,435 mm
Number of axles	32 (16 driven)
Wheel arrangement	Bo'Bo'+2'2'+Bo'Bo'+2'2'+2'2'+ Bo'Bo'+2'2'+Bo'Bo'
Number of bogies	16
Max. axle load	17 t
Number of cars / train	8
Number of seats	more than 500
Environmental temperature	-25 °C to +40 °C
Train control systems	ETCS



The 6HST trains are also based on the current and globally most variable Velaro high-speed platform, and will be deployed on the Konya–Ankara–Eskisehir route by 2017. With an output of 8,000 kW, the 200 m long multiple unit trains reach a top speed of 300 km/h. Thanks to Siemens' long experience with the Velaro, the company can draw on a large stock solution and characterized using a high level of proven technology. The 25 kV traction system is derived, for example, from multi-system traction of the Velaro platform.

The train layout offers three comfortable travel classes and a spacious restaurant and bistro area. Each train has 45 seats in First Class and 426 seats in Economy Class and Business Class in three compartments, each with four comfortable seats. The new EMU's are fitted with innovative communications and entertainment systems which will provide on-board internet and video on demand to passengers in the future. A CCTV system with outdoor and indoor cameras is used to monitor the passenger compartment, the train driver space, the distance in front of and behind the vehicle and entry areas. The galley has custom equipment to provide hot and cold meals on board, meeting the high standards of Turkish hospitality. Passengers' special requests can be met with the use of multifunctional devices.

EMU's with amazing transport efficiency – flexible and comfortable


As with all its previous successful predecessors, the Velaro Turkey is a pure EMU in which the entire drive unit and equipment modules are distributed underfloor throughout the train. Thus the entire train is available to the passengers. As compared to conventional trains with locomotives, the Velaro platform vehicles have about 20% more useful space in the passenger areas with the same length, and thus a much higher number of seats.

The EMU design has now secured a high level of customer acceptance due to its advantages, and has been implemented globally. The Velaro has been continuously improved since the first generation in reliability and drivability.

Its advantages in daily operation include the following:

- High adhesion during acceleration because 50% of the axles are driven
- Capability to run steeper route sections of up to 40 per thousand
- Due to equal weight distribution over the whole EMU, there is less weight on individual wheelsets. This protects the railroad embankment, lowers maintenance expenses to the chassis and provides excellent running performance.

The Velaro Turkey has four identical and independent traction units. If one traction unit fails, this can be switched off without affecting the remaining units. The train can reach its destination with 75% of maximum traction power.



Environmentally-friendly energy efficiency

Knowledge has been systematically gathered and assessed on aerodynamics from the Velaro fleets in Germany, China, Spain and Russia. New aerodynamic measures were tested in the wind tunnel and on the Velaro in China. This led to a further development of the Velaro platform and thus to the fourth stage of evolution which can be seen on the outside with the new Velaro: The covers on roof equipment, bogies and vehicle transitions reduce energy consumption. A high roof from the middle portion of the end car reduces sonic boom in tunnels, improves the driving friction and reduces exterior noise. Roof structures such as pantographs and air conditioning systems are fully covered. Nose and front spoilers were aerodynamically optimized. The Velaro demonstrates energy efficiency in its braking system: Since the first generation, its recovery of braking energy has returned energy to the grid. The effect: 10% energy saved, and reduced mechanical wear. The intelligent energy manager in the Velaro Turkey ensures that the rail systems are operated at optimum efficiency. This leads to reduced, saved CO₂ emissions of 14 g/passenger-km. In comparison, the average CO₂ emission of aircraft with the same payload is 136 g/passenger-km.

Good entertainment

The attractiveness of high-speed trains is based in particular on providing a comprehensive entertainment and information program in addition to fast travel speeds and the centrally positioned railway stations. Passengers in Velaro Turkey trains receive e-books, online browser games, news tickers and IPTV (Internet Protocol Television) in addition to music, videos and travel information. Touch displays integrated in the seats in first and business class as well as the mobile devices brought by the passengers and working with WLAN (Wireless Local Area Network) provide access to these offerings and information. A satellite connection for data transmission to and from the land-side and UMTS (Universal Mobile Telecommunications System) are available in order to provide powerful and interruption-free communication.

In Summary

The Velaro Turkey is a further development which incorporates the findings from the operating fleet, integrating the current requirements of TCDD customers. It sets the current benchmark for high-speed trains with its benefits in capacity and comfort.



Siemens AG
Mobility Division
Nonnendammallee 101
13629 Berlin, Germany
siemensrailssystemcontact.ic@siemens.com

© Siemens AG 2014

Printed in Germany
TH 166-140630 DB 08140.5
Dispo 21704
Order No.: A19100-V800-B829-X-7600
Velaro® is a registered trademark of Siemens AG.

The information in this document contains general descriptions of the technical options available, which do not always have to be present in individual cases. The required features should therefore be specified in each individual case at the time of closing the contract.

www.siemens.com/mobility