

# blueplanet 137 TL3

Transformerless, three-phase string inverter

## The trendsetter among inverters



- Optimized for solar power plants with 1500 volt modules
- Extensive grid management functions
- Special properties for extreme climatic conditions
- Farsighted technical features for future requirements
- Lean commissioning and maintenance via remote services

### Technical Data

<b>DC input data</b>	<b>137 TL3</b>
Max. recommended PV generator power	205 500 W
MPP range	875 – 1300 V
Operating range	875 – 1450 V
Rated DC voltage / start voltage	900 V / 1000 V
Max. no-load voltage	1500 V
Max. input current	160 A
Max. short circuit current $I_{sc\ max}$	300 A
Number of MPP tracker	1
Connection per tracker	1 - 2
<b>AC output data</b>	<b>137 TL3</b>
Rated output	137 000 VA
Max. power	137 500 VA
Line voltage	600 V (3P+PE)
Voltage range (Ph-Ph)	480 – 760 V
Rated frequency (range)	50 Hz / 60 Hz (45 – 65 Hz)
Rated current	3 x 132,3 A
Max. current	3 x 132,3 A
Reactive power / cos phi	0 – 100 % $S_{nom}$ / 0,30 ind. – 0,30 cap.
Max. total harmonic distortion (THD)	≤ 3 %
Number of grid phases	3

<b>General data</b>	<b>137 TL3</b>
Max. efficiency	99.2 %
Europ. efficiency	99.1 %
CEC efficiency	99.0 %
Standby consumption	< 10 W
Circuitry topology	transformerless
<b>Mechanical data</b>	<b>137 TL3</b>
Display	LEDs
Control units	webserver, supports mobile devices
Interfaces	Ethernet (Modbus TCP, Sunspec) RS485 (Modbus RTU, Sunspec, KACO-protocol) USB, optional: 4-DI, WIFI
Fault signalling relay	potential-free NOC max. 30 V / 1 A
DC connection	cable lug, max. 240 mm <sup>2</sup> (0.372 in <sup>2</sup> ) Cu or Al
AC connection	cable lug, max. 240 mm <sup>2</sup> (0.372 in <sup>2</sup> ) Cu or Al
Ambient temperature	-25 °C – +60 °C ①
Humidity	0 – 100 %
Max. installation elevation (above MSL)	3000 m
Min. distance from coast	500 m
Cooling	temperature controlled fan
Protection class	IP66 / NEMA 4X
Noise emission	59.2 db (A)
H x W x D	719 x 699 x 450 mm
Weight	78.2 kg
<b>Certifications</b>	<b>137 TL3</b>
Safety	UL62109-1, UL1741 SA, CSA-C22.2 No. 62109-1, CSA-C22.2 No. 62109-2, CSA-C22.2 No. 107.1 IEC 62109-1/-2, EN 61000-6-1/-2/-3, EN 61000-3-11/-12
Grid connection rule	overview see homepage / download area

① Power derating at high ambient temperatures

Versions	S	XL
Number of DC inputs	1 - 2	1 - 2
DC switch	–	✓
DC SPD	Type 1 + 2	Type 1 + 2
AC SPD	○	○
RS485 interface SPD	○	○
Ethernet interface SPD	○	○
PID Set	○	○

standard = ✓ upgradeable = ○

#### Published by Siemens Industry, Inc. 2020

Siemens Industry, Inc.  
3617 Parkway Ln.  
Peachtree Corners, GA 30092

For more information, including service or parts,  
please contact our Customer Support Center.  
Phone: +1 (800) 333-7421

usa.siemens.com/eMobility  
Article No. SIDS-T40055-00-4AUS  
Printed in USA  
All Rights Reserved  
© 2020, Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.