


WEP Series: Ring Style, EUSERC Compliant

Uni-PAK Metering

Data Sheet



Features:

- Individual split covers
- UL Listed for 60 / 75°C conductors. See equipment markings for applications
- For small apartment buildings, small professional and commercial buildings
- Completely self-contained meter centers
- Two to six 125A and 225A breaker positions
- Outdoor surface mounted enclosures
- Compact, pre-bussed, easy to handle, hang and wire
- Barriercd, sealable compartment for unmetered current-carrying parts
- Al/Cu lay-in lugs, except two socket units
- Top or bottom feed
- Bottom and rear branch wiring exits (Neutral and ground at bottom only)
- ANSI #61 light gray electrodeposited paint on zinc-coated G90 steel
- Meets EUSERC specifications when NEMA stud kit and flushing ring (if required) is field added

Ring Style Uni-PAK 120/240V 1 Phase, 3 Wire EUSERC Compliant

Max. Tenant Main ^①	Bus Amperage	Meter Positions Per Pak	Old Catalog Number	NEW Catalog Number	Breaker Provision	Max. AIC	Dimensions ^①			5th Jaw ^① Assembly	Line Lugs Wire Range ^①	Semi-Flush Kit No.	EUSERC Drawing #342 ^②		
							Height	Width	Depth						
125	200	2	SP2211	WEP2211	QP, QPH, HQP, MP-T, MP-HT, MP-MT	65,000	32.52	13.80	7.56	ECMF5 6:00 or 9:00	#6-300 kcmil	WPFK1	Figure 1		
	300	3	SP3311	WEP3311			38.75	25.42			#2-600 kcmil	WPFK2	Figure 3		
	400	4	SP4411	WEP4411			47.75	38.94			1/0-750 kcmil CU-AL or (2) 1/0-250 AL or (2) 1/0-3/0 CU	WPFK3	Figure 3		
		5	SP4511	WEP4511			38.75				WPFK4	Figure 3			
	500	4	SP5411	WEP5411			47.75	31.28			(2) #2-600 kcmil	WPFK12	Figure 3		
	400	6	SP4611	WEP4611			38.75	44.82				WPFK5	Figure 3		
600	5	SP6511	WEP6511	QP, QPH, HQP, MP-T, MP-HT, MP-MT, QS, QSH, QSHH, HQS, HQSH	100,000	29.75	28.53	7.56	ECMF5 6:00 or 9:00	1/0-750 kcmil CU-AL or (2) 1/0-250 AL or (2) 1/0-3/0 CU	WPFK6	Figure 2			
225	400	3	SP4212							WEP4212	38.75	34.41	WPFK7	Figure 3	
		4	SP4312							WEP4312	47.75		WPFK8	Figure 3	
600	6	5	SP6412							WEP6412	38.75	51.04	(2) #2-600 kcmil	WPFK9	Figure 3
		5	SP6512							WEP6512			(2) 1/0-750 kcmil or (4) 1/0-250 AL or (4) 1/0-3/0 CU	WPFK10	Figure 3
800	6	SP8612	WEP8612 ^③							38.75	51.04	(3) #2-500 kcmil		WPFK11	NA
1000	NA	WEP10612 ^③	56.56	56.56	NA										

NEMA Stud Kits

Catalog Number	Ameperage
WPSK400	400A
WPSK600	600A
WPSK800	800A
WPSK1000	1000A

Installer is responsible for ensuring utility approval.

① Dimensions shown are representative of outside box length, width, and depth and do not include allowances for mounting bumps, endwalls, covers, hubs or hardware protrusions. Dimensions are subject to change.

② Dimensions, ratings, and technical information shown are for WP series PAK only. Consult 2007 - 2008 Speedfax for information on SP series.

③ Please note the EUSERC standard currently only covers up to 600amp devices. Please consult utility prior to installation.

Siemens Industry, Inc.
5400 Triangle Parkway
Norcross, GA 30092

1-800-241-4453
info.us@siemens.com

Order No.: RPFL-UPWEP-0814 | Printed in USA |
© 2014, Siemens Industry, Inc.

www.usa.siemens.com/residential

The information provided in this flyer contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.