


# SIEMENS



## Take a step into the future with **SIMOCODE pro**

The motor management system for safety,  
transparency and efficiency. Connected to the Cloud.  
[siemens.com/simocode](https://www.siemens.com/simocode)



People today use the word SIMOCODE to mean **“motor management and control devices”** because, among specialists, SIMOCODE has long since become a generic term for this technology.

Because SIMOCODE pro is uncomplicated and easy to use. Because you can rely on SIMOCODE pro over many, many years. And because SIMOCODE pro always leads the field from a technological viewpoint. As it is doing now with its interface to the Cloud.





# Flexible, modular, integrated.

## The way modern motor management should be.

For 30 years now, SIMOCODE pro has been controlling and monitoring low-voltage, constant-speed motors all over the world. Wherever motors keep things running in the process industry, SIMOCODE is there. Many thousands of times over. Now even more powerful thanks to connection to the Cloud.

### The highlights of SIMOCODE pro

- Extensive protection, monitoring and control functions, independent of the automation system
- Detailed operational, service and diagnostics data – at any time or place
- Safe shutdown of motors
- Scalable, flexible solutions for all plant configurations
- Versatile, open communication via various bus systems and protocols
- Integration in process control systems such as SIMATIC PCS 7
- Supports PROFINET system redundancy and dynamic reconfiguration

SIMOCODE pro offers multifunctional, solid-state full motor protection. The motor management system monitors, protects and controls constant-speed motors and enables the implementation of predictive maintenance. It does not wait for a problem to occur before shutting down the motor, but establishes a level of transparency in advance. This avoids plant standstills and improves economic efficiency.


SIMOCODE pro delivers detailed operating, service and diagnostic data from across the entire process. The engineering is simple and likewise the integration into process control systems. SIMOCODE pro communicates via PROFIBUS and PROFINET, Modbus, EtherNet/IP and OPC UA. It implements simple and economical motor management.







With both the SIMOCODE pro General Performance and SIMOCODE pro High Performance device classes, we offer scalable, flexible solutions for industrial controls and plant optimization in the context of Industrie 4.0.


# SIMOCODE pro.

## A really strong family.

Two functionally graded device series form the core of the multifunctional SIMOCODE pro motor management system: General Performance and High Performance. The devices in both series incorporate all essential motor protection, monitoring and control functions – including data transparency through the Cloud connection. SIMOCODE pro General Performance is your entry into modern motor management and addresses standard motor applications. SIMOCODE pro High Performance features up to five expansion modules and offers additional measured variables. Find out how you you can take advantage of the two SIMOCODE pro device series in all areas of the process industry.



	PROFINET IO/OPC UA	ETHERNET/IP/OPC UA	PROFIBUS	MODBUS RTU	
High Performance	SIMOCODE pro V PN 	SIMOCODE pro V EIP 	SIMOCODE pro V PB 	SIMOCODE pro V MR 	Current/voltage measuring module
					Operator panel with display
					Max. 5/7 expansion modules
					Safety
General Performance	SIMOCODE pro V PN GP 		SIMOCODE pro S 		Extended control functions (e.g. positioner, pole-changing starter)
					Current measuring module
					Operator panel
					1 expansion module
				Basic control functions (e.g. direct-on-line/reversing start)	



### SIMOCODE pro – General Performance:

#### Ideal for the entry level

The smart and compact motor management system for direct-on-line, reversing, and star-delta (wye-delta) starters or for controlling a motor starter protector or soft starter. The basic system includes a current measuring module and the basic unit for overload or thermistor motor protection, for example. Communication with the automation level takes place via PROFIBUS/PROFINET. Optional additions include an operator panel and an expansion module that allows additional inputs/outputs, ground-fault detection and temperature measurement to be realized.

### SIMOCODE pro – High Performance: The fully professional solution for every motor

The SIMOCODE pro High Performance motor management system is variable, intelligent and can be adapted individually to suit every requirement. The basic system includes a module for measuring current (and optionally also voltage), as well as a basic unit, and is suitable for removing pump blockages, for example. Communication with the automation level takes place via PROFIBUS or Modbus RTU, via Ethernet with the PROFINET or EtherNet/IP protocols, and also via OPC UA. The optional expansions available include separate current/voltage measuring modules for dry-running protection, an operator panel with display, a ground-fault module, a temperature module, standard digital modules, fail-safe digital modules and an analog module.

### SIMOCODE pro Safety: Fail-safe expansion modules

Various modules are available for SIMOCODE pro for the extended protection of personnel, machines and the environment. These guarantee the safety-related shutdown of motors and meet all the requirements of the standards.

### The advantages:

- Functional switching and fail-safe shutdown without manual wiring or additional effort
- Safety function parameters can be flexibly configured
- Transfer of meaningful diagnostic data to the control system
- Logging of errors for detailed evaluation
- Fail-safe shutdown via PROFIsafe



Say goodbye to blocked pumps with SIMOCODE pro – the modular, compact motor management system that tackles the challenge by automatically reversing the pump. Another benefit: SIMOCODE pro can be retrofitted in existing plants.

## Remove pump blockages and increase availability.

### SIMOCODE pro – The advantages at a glance


- Minimized downtimes – with less maintenance work
- Energy and cost savings over the entire plant life cycle
- Simple use
- Scalable solution
- A choice of networked or autonomous configuration

Every water utility is familiar with the problems of a blocked pump – and the possible consequences: environmental harm, damage due to flooding, and dangers to health as a result of lifting and cleaning pumps. This is compounded by the financial impact of plant downtimes. SIMOCODE pro monitors the current and active power of the pump motor – and derives the pump status from them. If a defined threshold value is exceeded, SIMOCODE pro autonomously reverses the rotational direction of the pump in order to dislodge deposits on the impeller blades, for example.



# Reliable monitoring. Dry-running protection reconceptualized.

Reliable dry-running protection is a must in many applications in the chemical industry. SIMOCODE pro reliably prevents the dry running of centrifugal pumps in order to preclude hazardous situations – and completely redefines dry-running protection for pumps in hazardous areas with an innovative solution.



Sensors on centrifugal pumps in hazardous areas are often prone to fault and are thus high-maintenance. The solution: Using active power-based dry-running detection, SIMOCODE pro monitors the active electrical power consumption of the pump motor and thus the status of the pump – without the need for additional monitoring devices or sensors to be installed. The new technology ensures reliable explosion protection in accordance with ATEX and IECEx criteria and saves costs and time for commissioning and maintenance.

## Your benefits through active power-based dry-running protection

- Earlier fault detection
  - Direct conclusions concerning the flow rate can be drawn from the active power consumption of the pump motor
  - Reliable prevention of dry running of the pump and therefore less damage to the pump
- Cost and time savings
  - No maintenance effort due to the elimination of mechanical wear of the sensors
  - No additional sensor required
- Reduction of hardware
  - No need for additional sensors and mechanical components
  - Simplified engineering
- Reliable monitoring of the system
  - Compliance with ATEX and IECEx criteria
  - Reliable and automatic pump shutdown in the event of inadmissible operating conditions

# SIMOCODE pro speaks to everyone. Including the Cloud.

With the OPC UA industrial M2M communication protocol, SIMOCODE pro provides an additional communication interface that is independent of the automation system.

## Digitalization for more economical operation: SIMOCODE pro with OPC UA

The open and supplier-independent communication via OPC UA guarantees the direct exchange of data with HMI panels or SCADA systems. Motor, process and plant data is therefore available without any losses, wherever it is needed: At the switchboard, but also in the control room for diagnostic purposes. As part of the digital revolution and the efforts to evaluate vast quantities of data even more quickly, all feeder data from SIMOCODE pro can be transmitted by the most direct route to the Cloud using OPC UA.


The data can then be used more intensively and in a targeted fashion – without the need for any intervention in the control.

The result: Plant availability and economy are increased, because you can run analyses, improve energy consumption, or even optimize the entire process.

## Benefits

Thanks to OPC UA, SIMOCODE facilitates simple and convenient integration into Cloud-based solutions, e.g. Siemens MindSphere – with so many advantages:

- Data provision in the Cloud for cross-plant, reliable diagnostics
- Convenient and reliable process optimization
- Plant-wide access to control data, process values and readings without complex engineering effort
- Predictive maintenance, energy data management and resource optimization
- Effective protection against manipulation (security)








**For diagnostics and simple configuration, including in the TIA Portal: [SIMOCODE ES](#)**

SIMOCODE ES provides you with the software for the configuration, startup, operation and diagnosis of SIMOCODE pro. The software is based on the central Totally Integrated Automation Portal (TIA Portal) engineering framework, providing an integrated, efficient and intuitive solution for all automation tasks. SIMOCODE ES offers you a host of advantages, including convenient configuration in the device view, graphical commissioning using drag and drop functions, mass engineering, presentation of signal states online, or clear measurement curves for diagnostic purposes.



**The convenient way to optimum process guidance: The integration of [SIMOCODE pro](#) into [SIMATIC PCS 7](#)**

Using standardized blocks and faceplates, SIMOCODE pro can very easily be integrated into the SIMATIC PCS 7 process control system. This makes it extremely easy to integrate service and diagnostic data from the motor management system into higher-level process control systems, for example.

The result: A high level of transparency throughout the plant, enabling faults to be detected at an early stage or prevented from occurring altogether. In general, the greater density of information in the control system enables you to achieve not only greater transparency, but also higher process quality.


Support of redundance mechanisms and dynamic reconfiguration (device extension during ongoing operation) increases the plant availability.

## Benefits

SIMOCODE pro is your reliable data supplier for maximum process quality. The motor management system offers:

- Data analysis and simulation
- Secure data storage and transmission
- Visualization and recommendation(s)
- Increased availability of components
- Optimization of energy consumption
- Maximization of process efficiency
- Support of PROFINET system redundance and dynamic reconfiguration

# SIMOCODE pro system overview – General Performance



## Basic units

### SIMOCODE pro S

• 24 V DC	3UF7020-1AB01-0
• 110 ... 240 V AC/DC	3UF7020-1AU01-0

### SIMOCODE pro V PN GP<sup>1)</sup>

• 24 V DC, 2 ports	3UF7011-1AB00-1
• 110 ... 240 V AC/DC, 2 ports	3UF7011-1AU00-1
• 24 V DC, 1 port	3UF7011-1AB00-2
• 110 ... 240 V AC/DC, 1 port	3UF7011-1AU00-2

## Expansion modules

### SIMOCODE pro S multifunction modules

Monostable relay outputs, input voltage	
• 24 V DC	3UF7600-1AB01-0
• 110 ... 240 V AC/DC	3UF7600-1AU01-0

## Connection cables

3UF793x-0AA00-0 connection cables available in various versions from 0.025 m – 0.5 m

## Current measuring modules

Straight-through transformers	0.3 ... 3 A	45 mm	3UF7100-1AA00-0
	2.4 ... 25 A	45 mm	3UF7101-1AA00-0
	10 ... 100 A	55 mm	3UF7102-1AA00-0
	20 ... 200 A	120 mm	3UF7103-1AA00-0
Busbar connections	20 ... 200 A	120 mm	3UF7103-1BA00-0
	63 ... 630 A	145 mm	3UF7104-1BA00-0

## Expansion modules

### Digital modules


Relay outputs	Input voltage		
	• Monostable	24 V DC	3UF7300-1AB00-0
		110 ... 240 V AC/DC	3UF7300-1AU00-0
Ground-fault module			3UF7510-1AA00-0
Temperature module			3UF7700-1AA00-0

## Operator panel

• Titanium gray	3UF7200-1AA01-0
-----------------	-----------------

<sup>1)</sup> During an interim phase it is necessary to add -Z141 when ordering the new FW version V3.0.0 which comprises PROFINET system redundancy and dynamic reconfiguration.

# SIMOCODE pro system overview – High Performance



## Basic units

### SIMOCODE pro V PROFIBUS

• 24 V DC	<b>3UF7010-1AB00-0</b>
• 110 ... 240 V AC/DC	<b>3UF7010-1AU00-0</b>

### SIMOCODE pro V PROFINET <sup>1)</sup>

• 24 V DC	<b>3UF7011-1AB00-0</b>
• 110 ... 240 V AC/DC	<b>3UF7011-1AU00-0</b>

### SIMOCODE pro V Modbus RTU

• 24 V DC	<b>3UF7012-1AB00-0</b>
• 110 ... 240 V AC/DC	<b>3UF7012-1AU00-0</b>

### SIMOCODE pro V EtherNet/IP <sup>2)</sup>

• 24 V DC	<b>3UF7013-1AB00-0</b>
• 110 ... 240 V AC/DC	<b>3UF7013-1AU00-0</b>

## Current / voltage measuring modules

Straight-through transformers	0.3 ... 4 A	45 mm	<b>3UF71□0-1AA01-0</b>
	3 ... 40 A	45 mm	<b>3UF71□1-1AA01-0</b>
	10 ... 115 A	55 mm	<b>3UF71□2-1AA01-0</b>
	20 ... 200 A	120 mm	<b>3UF71□3-1AA01-0</b>
Busbar connection	20 ... 200 A	120 mm	<b>3UF71□3-1BA01-0</b>
	63 ... 630 A	145 mm	<b>3UF71□4-1BA01-0</b>

Standard version — **1**  
 Dry-running protection — **2**

<sup>1)</sup> During an interim phase it is necessary to add –Z141 when ordering the new FW version V3.0.0 which comprises PROFINET system redundancy and dynamic reconfiguration.

<sup>2)</sup> During an interim phase it is necessary to add –Z141 when ordering the new FW version V2.0.0 which comprises additionally OPC UA communication.

## Expansion modules

### Digital modules

Relay outputs	Input voltage	
• Bistable	24 V DC	<b>3UF7310-1AB00-0</b>
	110 ... 240 V AC/DC	<b>3UF7310-1AU00-0</b>
Analog module		<b>3UF7400-1AA00-0</b>

### Fail-safe expansion modules

DM-F Local fail-safe digital module	Rated control supply voltage	
• 24 V DC		<b>3UF7320-1AU00-0</b>
• 110 ... 240 V AC/DC		<b>3UF7320-1AU00-0</b>
DM-F PROFIsafe fail-safe digital module*	Rated control supply voltage	
• 24 V DC		<b>3UF7330-1AB00-0</b>
• 110 ... 240 V AC/DC		<b>3UF7330-1AU00-0</b>

\*Possible with SIMOCODE pro V PROFIBUS / PROFINET basic unit

### Operator panels with display

Languages: English / German / French / Spanish / Portuguese / Italian / Polish / Finnish	<b>3UF7210-1AA01-0</b>
Languages: English / Chinese / Russian / Korean	<b>3UF7210-1BA01-0</b>



# Software

## SIMOCODE ES (TIA Portal) V18 Basic

Basic functional scope including Professional Trial License  
Both software and documentation can be downloaded for free, see:  
<https://support.industry.siemens.com/cs/ww/en/view/109811683>

## SIMOCODE ES (TIA Portal) V18 Professional

### Floating license for one user

• License key on USB flash drive, SW on DVD	<a href="#">3ZS1322-6CC16-0YA5</a>
• License key and software download	<a href="#">3ZS1322-6CE16-0YB5</a>
Upgrade for SIMOCODE ES 2007 Premium	<a href="#">3ZS1322-6CC16-0YE5</a>
Software Update Service	<a href="#">3ZS1322-6CC00-0YL5</a>

## SIMOCODE pro block library for SIMATIC PCS 7 Version V9.1 with Advanced Process Library (APL)

Engineering software V9.1 (OSD)	<a href="#">3ZS1632-1XE04-0YA0</a>
Runtime license V9.1 (OSD)	<a href="#">3ZS1632-2XE04-0YB0</a>
Upgrade for PCS 7 block library SIMOCODE pro V8 or V9.0 (OSD)	<a href="#">3ZS1632-1XE04-0YE0</a>
Upgrade for PCS 7 block library SIMOCODE pro V7 (without APL)	<a href="#">3ZS1632-1XE04-0YF0</a>

## SIMOCODE pro block library for SIMATIC PCS 7 Version V9.0 with Advanced Process Library (APL)

Engineering software V9.0 (OSD)	<a href="#">3ZS1632-1XE03-0YA0</a>
Runtime license V9.0 (OSD)	<a href="#">3ZS1632-2XE03-0YB0</a>
Upgrade for PCS 7 block library SIMOCODE pro V8	<a href="#">3ZS1632-1XX03-0YE0</a>

## SIMOCODE pro block library for SIMATIC PCS 7 without Advanced Process Library (APL)

Engineering software V7	<a href="#">3UF7982-0AA10-0</a>
Runtime license V7	<a href="#">3UF7982-0AA11-0</a>
Engineering software migration V7–V9 for PCS7 V8.0/V8.1/V8.2/V9.0 as Software download (OSD)	<a href="#">3UF7982-0AA20-1</a>
Engineering software migration V7–V9 for PCS7 V9.1 as Software download (OSD)	<a href="#">3UF7982-0AA30-1</a>

### Published by Siemens AG

Smart Infrastructure  
Electrical Products  
Werner-von-Siemens-Str. 48–50  
92224 Amberg  
Germany

### For the U.S. published by Siemens Industry Inc.

100 Technology Drive  
Alpharetta, GA 30005  
United States

Article No. SIEP-B10327-00-7600  
Printed in Germany  
WS 09221.0 Dispo 25600

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

SIMOCODE is a registered trademark of Siemens AG. Any unauthorized use is prohibited. All other designations in this document may represent trademarks whose use by third parties for their own purposes may violate the proprietary rights of the owner.

© Siemens 2022