

# SIEMENS

## VersiCharge Ultra 175™ DC Charger

[usa.siemens.com/versichargeultra](http://usa.siemens.com/versichargeultra)



### Features

- Easy to install
- Liquid cooled
- Low maintenance
- Cable management
- 10" screen
- CCS1
- CHAdeMO
- Brandable exterior
- Optional credit card reader
- IP65

# VersiCharge Ultra 175™

## Technical Data



User Unit	
Connectors	Single: CCS   Dual: CCS and CHAdeMO
Connector Type(s)	US & Canada: CCS1 or CCS1 and CHAdeMO
Output Voltage	200V - 920V DC
Output Current	CCS: up to 350A CHAdeMO: up to 200A
IP Rating	IP65 (NEMA 3R)
IK Rating	IK 10 (IK8 Screen)
Efficiency	98.5% at full load (350A, 500V)
Operating Temperature	-30 °C to 50 °C (-22 °F to 122 °F)
Storage Temperature	-55 °C to 80 °C (-67 °F to 176 °F)
Credit Card Reader	Optional
RFID Reader	Fitted standard
Dimensions	2,011mm (6'7") (H) x 993mm (3'3") (W) x 532mm (1'9") (D) Note: Width excludes plugs
Weight	260kg (573lb)
Shipping Weight	310kg (683lb) (estimate)
Authentication / Payment	RFID only OR Credit Card Reader with RFID
Cable Length	4.1m reach (13'5" reach)
Cable Management	Fitted standard
Compliance	UL NRTL certification FCC Class A

# VersiCharge Ultra 175™

## Technical Data

Isolated Power Unit	
Input Voltage	US: (480VAC): 480VAC 3ph ±10%   60Hz ±10%   225A nominal   250A maximum (at low line level) Canada: (600VAC): 600VAC 3ph ±10%   60Hz ±10%   180A nominal   200A maximum (at low line level)
Input Overvoltage Category	Category III
Output Voltage   Power	950V DC   Up to 178kW
Isolation Between AC Mains & EV	Reinforced Isolating transformer with double/reinforced insulation
Efficiency	96% at full load
Power Factor	>0.99
Total Harmonic Distortion (THD)	<5%
Operating Temperature	-10°C to 50°C (14°F to 122°F) 5% to 95% RH Non Condensing (without optional cold kit) -30°C to 50°C (-22°F to 122°F) 5% to 95% RH Non Condensing (with optional cold kit)
Storage Temperature	-55°C to 80°C (-67°F to 176°F) 5% to 95% RH Non Condensing
Network Connection	Ethernet to dispenser unit
Weight	With transformer: 988kg (2178lb)
Shipping Weight	With transformer: 1078kg (2377lb)
Dimensions	2,147mm (7'1") (H) x 650mm (2'2") (W) x 1,055mm (3'6") (D)
IK Rating	IK10
IP Rating	IP55 (NEMA 3R)
Wireless Uplink	3G/4G cellular communications with failover redundancy
Wired Uplink	Ethernet
Power Supply	Battery-backed UPS functionality for reliable telemetry at all times
Software Support	OCPP v1.6J support for management and billing
Security	SSH with EC keys and unique password for manufacturer diagnostics
Power Control	Supports OCPP charging profiles (OCPP v1.6J)
Control Platform	Included in the Power Unit
Power Sharing (Optional)	Configurable site-level power demand management

EMC			
EMC	USA:	FCC	Immunity: Class A Emissions: Class A

# VersiCharge Ultra 175™

## Technical Data

AC Grid Interface	
<b>Voltage</b>	US: (480VAC): 480VAC 3ph ±10% Canada: (600VAC): 600VAC 3ph ±10%
<b>Frequency</b>	US & Canada: 60Hz ±10%
<b>Maximum Current At Low Line Level (Nominal Voltage -10%) And Pf = 0.99</b>	US: (480VAC): 250A Canada: (600VAC): 200A
<b>Over Current Protection Device Required (Ocpd) In Site Distribution Board</b>	US: (480VAC): 320A UL Listed Circuit Breaker (recommended) (The circuit breaker nominal rating MUST not exceed 320A in order to maintain primary protection for the LV transformer in the IPU)  Canada: (600VAC): 250A UL Listed Circuit Breaker (recommended) (The circuit breaker nominal rating MUST not exceed 250A in order to maintain primary protection for the LV transformer in the IPU)
<b>Fault Current Limiting Fuses In Site Distribution Board</b>	Current limiting fuses or a UL recognised current limiting circuit breaker MUST be installed if available fault current exceeds 18kA  Note: The IPU has an option to upgrade the SCCR to 100kA
<b>Residual Current Monitoring In Site Distribution Board (Optional)</b>	If a residual current monitoring device is required by local regulation it shall be of time delay type
<b>Under-Voltage Relay In Site Distribution Board (Optional)</b>	The isolated power unit includes circuitry to locally isolate the charger's power circuit if the safety loop monitoring the door switches and tilt sensors is triggered.  The IPU can also be isolated upstream in the event of a safety loop trigger event by including an under-voltage relay coil on the feeder circuit breaker in the site distribution board.  Tritium Veefil chargers should only be installed by a licensed contractor and a licensed electrician, in accordance with all local and national codes and standards to meet current NEC and NFPA 70E requirements. This may include additional, lockable disconnect mechanisms within line of sight of the supplied equipment.
<b>Minimum Buried Cable Size For AC Link</b> (Length of AC link cables and system efficiency should be considered when sizing cables)	US: (480VAC): Twin 3/0 Cu for L1, L2, L3 Single 3/0 Cu for PE  Canada: (600VAC): Twin 1/0 Cu for L1, L2, L3 Single 1/0 Cu for PE
<b>Maximum Length Of Buried Cables For Minimum Ac Link Cable Size Specified</b>	200m (656ft) (To maintain feeder voltage drop below 3%)

Catalog Number	Description
US2:VSCULT175DUSAG	Dispenser Unit
US2:VSCULT175PUSAG	Transformer
US2:VSCULT175CB	Custom Branding Dispenser

### Published by Siemens Industry, Inc. 2020

Siemens Industry, Inc.  
3617 Parkway Ln  
Peachtree Corners, GA 30092  
  
Phone: +1 (800) 333-7421  
info.us@siemens.com  
usa.siemens.com/emobility

Article No. SIDS-T40085-00-4AUS  
Printed in USA  
All Rights Reserved  
© 2020, Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters and, therefore, should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.