



3B5M300D16 - Three-Phase Ventilated-USA-DOE

PRODUCT DETAILS			
KVA:	300.00	Enclosure:	NEMA 3R Ventilated
UPC#:		Phase:	Three-Phase
Line Voltage	208V-Delta	Load Voltage	480Y/277V
E/S Shielded:	No	Windings:	Aluminum
Temp. rise:	150°	Hertz:	60 Hz
Taps:	1 - 5% FCAN; 2 - 5% FCBN	Approvals:	UL, cUL, DOE
		Wall Bracket:	n/a
WEIGHT AND DIMENSIONS			
Height(A):	46.00"	Width(B):	35.00"
Depth(C):	37.00"	Shipping Weight:	1755 lbs
ADDITIONAL INFORMATION			
How to Buy: Contact Siemens Distributor, Siemens Sales Rep or Configure in COMPAS Configuration Tool			


Wiring Diagram

Dimensional Drawing

T208G Wiring Diagram & Connections*

Wiring Diagram

Primary: 208 Volts Delta
Secondary: 480Y/277 Volts



Connections

Primary Volts	On Each Coil Jumper Taps To	Primary Lines Connect To
218	1	X1, X2, X3
208	2	X1, X2, X3
198	3	X1, X2, X3
187	4	X1, X2, X3
Sec. Volts	Secondary Lines Connect To	
480	H1, H2, H3	
277	Between H0 and H1 or H2 or H3	
1 Phase		

Figure 24

