

SENTRON, measuring device, 7KM PAC3100, LCD, L-L: 480 V, L-N: 277 V, 3-phase, Modbus RTU, active/reactive energy, class 1 acc. to IEC 61557-12 & 62053-21, wide-range power sup. unit AC/DC, screw terminals



Model	
Product brand name	SENTRON
Product designation	7KM PAC3100
Design of the product	basic
Product type designation	Measuring instrument
Type of measured value detection	complete
Design of the power supply	Wide-range power supply
General technical data	
Cutout width	92 mm
Cutout height	92 mm
Size of Power Monitoring Device / company-specific	size 96
Operating mode for measured value detection	
<ul style="list-style-type: none"> • automatic line frequency detection 	Yes
<ul style="list-style-type: none"> • set at 50 Hz 	No
<ul style="list-style-type: none"> • set to 60 Hz 	No
Pulse duration	
<ul style="list-style-type: none"> • initial value 	30 ms
<ul style="list-style-type: none"> • Full-scale value 	500 ms

Voltage curve	Sinusoidal or distorted
Measurable line frequency / initial value	45 Hz
Measurable line frequency / Full-scale value	65 Hz
Measuring procedure / for voltage measurement	TRMS
Reference code / acc. to DIN 40719 extended according to IEC 204-2 / acc. to IEC 750	P

Supply voltage

Type of voltage / of the supply voltage	AC/DC
Measuring category / for supply voltage	CATIII
Supply voltage frequency / rated value	
• minimum	45 Hz
• maximum	65 Hz
Apparent power consumption	
• without expansion module / typical	10 V·A
Relative symmetrical tolerance / of the supply voltage	10 %

Protection class

Protection class IP	
• on the front	IP65
• Rear side	IP20
Operating resource protection class / when installed	II

Current

Measurable current	
• 1 / at AC / Rated value	5 A

Suitability

Suitability for operation	Installation in stationary control panels in closed rooms
Adjustable time period / minimum	10 ms

Product function

Product function	
• Illuminance of display backlighting adjustable	No
• Time-controlled reduction of the illuminance of display backlighting possible	Yes
• reactive power measurement	Yes
• frequency measurement	Yes
• pulse measurement	No
• Display contrast adjustable	Yes
• voltage measurement	Yes
• Current measurement	Yes
• active power measurement	Yes

Display and operation

Design of the display	LCD
-----------------------	-----

Number of keys	4
Color / of the background of the display	white
National language / on the display screen / is supported	ger, en, fr, spa, ita, por, tur, chi
Product function / Display can be inverted (positive <=> negative mode)	Yes
Horizontal image resolution	128
Vertical screen resolution	96
Refresh time / on display	
• minimum	0.33 s
• maximum	3 s

Communication

Protocol	
• is supported	Modbus RTU
Transfer rate	
• minimum	4.8 kbit/s
• maximum	38.4 kbit/s

Fault limits

Reference condition / for metering accuracy	according to IEC61557-12 (K55)
Formula for relative total measurement inaccuracy	
• for measured variable reactive energy	Class 3 according to IEC61557-12 and IEC62053-23
• for measured variable reactive power	+/- 3 %
• for measured variable output	+/- 1.0 %
• for measured variable output factor	+/- 1 %
• for measured variable voltage	+/- 1.0 %
• for measured variable current	+/- 1.0 %
• for measured variable active energy	Class 1 according to IEC 61557-12 and IEC62053-21
• for measured variable active power	+/- 1 %

Inputs Outputs

Input voltage / at digital input	
• at DC / maximum	30 V
Number of digital outputs	2
Number of digital inputs	2
Digital output version	switching or pulse output function
Design of the switching input	Self-supplied
Type of switching output	bidirectional
Type of electrical connection	
• at the digital inputs	screw-type terminals
• at the digital outputs	screw-type terminals
Input current / at digital input	
• initial value for signal<1>-recognition	2.5 mA

<ul style="list-style-type: none"> • Full-scale value for signal<0> recognition • for signal <1> / minimum 	0.5 mA 2.5 mA
Output current	
<ul style="list-style-type: none"> • at digital output / with signal <0> / maximum • at digital output / for signal <1> / minimum • at digital output / for signal <1> / maximum • at the digital outputs / at DC / limited to 100 ms / maximum • at the digital outputs / at DC / maximum 	0.2 mA 10 mA 27 mA 130 mA 30 mA
Output delay / at digital output	
<ul style="list-style-type: none"> • for signal <0> to <1> / maximum • for signal <1> to <0> / maximum 	5 ms 5 ms
Operating conditions for digital inputs / external voltage supply	No
Operating voltage / as output voltage / at DC / maximum permissible	30 V
Property of the output / Short-circuit proof	Yes
Input delay time / at digital input	
<ul style="list-style-type: none"> • for signal <0> to <1> / maximum • for signal <1> to <0> / maximum 	30 ms 30 ms
Internal resistance / at the digital outputs	55 Ω
Load resistance / at digital input	
<ul style="list-style-type: none"> • initial value for signal<0>-recognition • Full-scale value for signal<1> recognition 	100 000 Ω 1 000 Ω
Measuring category / for digital signals	CATI
Switching frequency / at digital output / maximum	17 Hz

Measuring inputs

Outer conductors and neutral conductors internal resistance / for voltage measurement	0.84 MΩ
Measurable supply voltage	
<ul style="list-style-type: none"> • between (PE)N and L / at AC / minimum • between (PE)N and L / at AC / maximum • between (PE)N and L / at AC / maximum rated value • between the outer conductors / at AC / minimum • between the outer conductors / at AC / maximum • between the outer conductors / at AC / maximum rated value 	11.5 V 277 V 277 V 20 V 480 V 480 V
Voltage measuring range extension / with external voltage transformers	Yes

Current measuring range extension / with external current transformers	Yes
Measuring category / for voltage measurement	CATIII
Supply voltage / between the outer conductors / at AC / maximum permissible	576 V
Consumed active power / for current measurement / per phase	500 mW
Continuous current / at AC / maximum permissible	10 A
Measuring category / for current measurement	CATIII
Zero-point suppression / for current measurement	10 mA
<ul style="list-style-type: none"> • for neutral conductor current 	45 mA
Relative measurable current / at AC	
<ul style="list-style-type: none"> • minimum 	0.2 %
<ul style="list-style-type: none"> • maximum 	120 %
Apparent power consumption / for current measurement	
<ul style="list-style-type: none"> • with measuring range 5 A / per phase 	0.5 V·A
Measuring procedure / for current measurement	TRMS

Connections

Type of electrical connection	
<ul style="list-style-type: none"> • at the inputs for supply voltage 	screw-type terminals
<ul style="list-style-type: none"> • at the measurement inputs for voltage 	screw-type terminals
<ul style="list-style-type: none"> • at the measurement inputs for current 	screw-type terminals

Mechanical Design

Height	96 mm
Height / of the display	54 mm
Width	96 mm
Width	
<ul style="list-style-type: none"> • of the display 	72 mm
Depth	56 mm
Installation depth	51 mm
Mounting type / panel mounting	Yes
Mounting position	vertical
Material thickness / of the control panel	
<ul style="list-style-type: none"> • maximum 	4 mm
Net weight	469 g

Environmental conditions

Installation altitude / at height above sea level / maximum	2 000 m
Standard	
<ul style="list-style-type: none"> • for EMC for industrial sector 	IEC 61000-6-2 respectively IEC 61326-1:2005, table 2
<ul style="list-style-type: none"> • for EMC against unloading 	IEC 61000-4-2

<ul style="list-style-type: none"> • for EMC against high frequency fields 	IEC 61000-4-3
<ul style="list-style-type: none"> • for EMC against conducted disturbance variables via HF fields 	IEC 61000-4-6
<ul style="list-style-type: none"> • for EMC against magnetic fields with power engineering frequencies 	IEC 61000-4-8
<ul style="list-style-type: none"> • for EMC against quick, transient electrical disturbances 	IEC 61000-4-4
<ul style="list-style-type: none"> • for EMC against voltage drops and interruptions 	IEC 61000-4-11
<ul style="list-style-type: none"> • for EMC against surge voltages 	IEC 61000-4-5
<ul style="list-style-type: none"> • for pulse emitter 	according to IEC62053-31
<ul style="list-style-type: none"> • for cyclic, environmental damp heat check 	IEC 60068-2-30
<ul style="list-style-type: none"> • for environmental coldness check 	IEC 60068-2-1
<ul style="list-style-type: none"> • for environmental dry heat check 	IEC 60068-2-2
Ambient temperature / during operation	
<ul style="list-style-type: none"> • minimum 	-10 °C
<ul style="list-style-type: none"> • maximum 	55 °C
Ambient temperature / during storage	
<ul style="list-style-type: none"> • minimum 	-25 °C
<ul style="list-style-type: none"> • maximum 	70 °C

Certificates

Certificate of suitability	
<ul style="list-style-type: none"> • as EC declaration of conformity 	IEC 61010-1: 2001 (2nd Ed.) with Corr. 1, EN 61010-1: 2001 (2nd Ed.) and DIN EN 61010-1:2002 with "Berichtigung 1"
<ul style="list-style-type: none"> • as approval for Canada 	UL 61010-1, 2nd Ed. CAN/CSA-C22.2 NO. 61010-1-04
<ul style="list-style-type: none"> • as approval for USA 	UL 61010-1, 2nd Ed. CAN/CSA-C22.2 NO. 61010-1-04
<ul style="list-style-type: none"> • Approval Australia 	Yes
Reference code	
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 	P

General Product Approval	Declaration of Conformity	other
--------------------------	---------------------------	-------



[Confirmation](#)

[Manufacturer Declaration](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7KM3133-0BA00-3AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/7KM3133-0BA00-3AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7KM3133-0BA00-3AA0

CAx-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



