


Dimension Prints for Above NEMA Motors ANSS-60000-0403

**Type CGG – Horizontal – Totally Enclosed Water to Air Cooled
 Sleeve Bearing – Direct Connected
 Frames 1122 / 1124 – 4 Pole & Slower**



Standard Dimensions in Inches

TYPE ¹¹	SHAFT				KEY		BA	1122 FRAME				1124 FRAME			
	U	R ²	N-W	V ⁴	S ³	ES		B	C	2F	Approx. Ship Wt. (Lbs.)	B	C	2F	Approx. Ship Wt. (Lbs.)
I	6.5	5.662	11.00	10.60	1.50	9.00	17.25	88.0	121.0	76.0	32,000	96.0	129.0	84.0	38,400
II	7.0	6.014	11.75	11.35	1.75	9.75	17.25	88.0	121.7	76.0	32,000	96.0	129.7	84.0	38,400
III	7.5	6.521	12.50	12.10	1.75	10.50	19.00	88.0	125.8	76.0	32,000	96.0	133.8	84.0	38,400
IV	8.0	6.873	13.25	12.85	2.00	10.75	19.00	88.0	126.6	76.0	32,000	96.0	134.6	84.0	38,400
V	8.5	7.381	14.00	13.60	2.00	11.50	19.00	88.0	127.3	76.0	32,000	96.0	135.3	84.0	38,400

Notes

- See Section 3 for selection of main terminal box.
- R = Bottom of key to opposite side of shaft.
- S = Width of keyseat.
- V = Length of shaft available for coupling.
- Jackscrew holes and dowel holes are provided at each foot.
- Shims may be necessary under motor feet for direct connection.
- All machines may rotate in one direction only.
- Rotor end float = 0.5"
- End float of LEF coupling = 0.19"
- For motors equipped with provisions for proximity probes use print in Part 3 of this section.
- Some shaft types are not available for all HP combinations. Consult factory.

Lubrication Per Bearing
4 Pole & Slower
290-350 SUS @ 100°F
Oil capacity per bearing 8.5 qt. for Shaft Types I & II 13.7 qt. for Shaft Types III, IV, & V

Certification

Customer _____ P.O. _____ S.O. _____ Item _____

HP _____ RPM _____ FRAME _____ PH/HZ/Volts _____

Rotation Facing Shaft Extension CW CCW Either

By _____ Date _____

Not for construction, installation or application purposes unless certified.