



SIEMENS

Ingenuity for life

Bangkok BTSC Green Line

22 four-car metro trains


In May 2016, Bangkok Mass Transit System Public Company (BTSC) placed an order with a consortium comprising Siemens and the Turkish public transportation vehicle manufacturer Bozankaya for the delivery of 22 four-car metro trains. In addition, Siemens will take over their service and maintenance for 16 years.

The project follows the successful delivery of 35 three-car units for Bangkok's first metro, Skytrain, in 1999. Another contract for 19 three-car units was awarded to Siemens in 2002 for the new MRTA metro system in Bangkok.

The Siemens scope for the Green Line Extension trains includes the bogies, traction and braking systems, and auxiliary systems as well as the project management, development, construction, and commissioning of the trains. The trains will be manufactured at the Bozankaya factory in Ankara, Turkey.

Starting with the delivery of the first metro trains by mid 2018, the project is scheduled to be finished one year later. The trains will operate on the existing BTS (Skytrain) system and the Green Line extensions and will help boost the capacity of the lines to over one million passengers per day.

There was a strong focus on reducing lifecycle costs in the design phase. The carbodies are made of lightweight stainless-steel, which reduces energy consumption. The optimized interior layout increases passenger capacity. Four electrically powered 1,400 mm-wide outside sliding doors are arranged on each side of the cars to allow passengers to board and leave the train rapidly, reducing the time the trains spend in the stations. This increases overall system capacity.



Technical data	
Train configuration	Mc+T+T+Mc
Wheel arrangement	Bo'Bo'+2'2'+2'2'+Bo'Bo'
Carbody material	Stainless steel
Track gauge	1,435 mm
Length over coupler	86,600 mm
Width of car	3,120 mm
Floor height above top of rail	1,160 mm
Maximum axle load	Approximately 15 t
Number of seats per train	112
Passenger capacity per train (6 pass./m ²)	1,208 passengers
Passenger doors per car	2 x 4 exterior sliding doors
Door width	1,400 mm
Maximum operating speed	80 km/h
Line voltage	750 V DC, third rail

The passengers' comfort is enhanced by an extremely effective high-performance air-conditioning system, which responds to weather conditions, prevailing high temperatures, and humidity levels.

Highlights

- Reliable operation thanks to proven technology and high redundancies in the traction system – one converter drives two motors
- Maintainability of the trains has been optimized based on Siemens' long-term experience in Bangkok
- Low-wear mechanical brake and high stopping accuracy thanks to dynamic braking to standstill

- A lightweight stainless-steel carbody and state-of-the-art traction technology reduce energy consumption
- Interior and exterior LED lights reduce maintenance costs and energy consumption
- The redesigned interior increases passenger capacity compared with predecessor vehicles
- An innovative air diffuser system has been implemented for an efficient and comfortable air supply; it also prevents water condensation
- High safety level according to latest standards EN 50126, 50128, 50129 and IEC 61508
- Fire safety according to NFPA 130/EN 45545

Published by
Siemens AG 2018

Mobility Division
Otto-Hahn-Ring 6
81739 Munich, Germany

contact.mobility@siemens.com

TH 325-180565 DA 0618

Subject to changes and errors.
The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.