




REVISION	DATE	BY	DATE	BY
		DRAWN	05/07/13	GR
		CHEK'D		
1	06/01/04	GR	VERIF'D	


Confidential - Property of <b>Siemens Industry, Inc.</b> Building Technologies Division		
CUSTOMER		
ORDER NO.	DWG. NO.	1
	1D1Y025CTP1	SH 1 OF 2

<h1 style="margin: 0;">SIEMENS</h1>	
CATALOG NO. 1D1Y025CTP1 SERIAL NO. SERIES H <b>25</b> kVA <b>60</b> Hz <b>1</b> PHASE <b>5.6</b> % IMP AT <b>170</b> °C <b>150</b> °C RISE °C AVG. AMBIENT <b>220</b> °C TEMP CLASS °C MAX. AMBIENT PRIMARY ( H1 H3 H2 H4 ) <b>240X480V</b> V SECONDARY(X4 X2 X3 X1 ) <b>120/240V</b> V WINDING MATERIAL <b>CU</b> ENCLOSURE TYPE NEMA-3R WEIGHT <b>295</b> LBS ENERGY EFFICIENCY NEMA TP 1-2002	<div style="display: flex; justify-content: space-between;"> <div style="width: 45%;"> <p>LISTED DISTRIBUTION TRANSFORMER 77US TYPE F</p>  LR 3902 E112313         </div> <div style="width: 45%; text-align: center;">  </div> </div> <div style="margin-top: 10px;"> <p>SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS          DO NOT INSTALL IN AREAS ACCESSIBLE TO PUBLIC          FOR INSTALLATION SEE INSTRUCTION MANUAL</p> <p>NEMA Class <b>ANN</b> Dry Type Transformer Siemens Industry, Inc. Norcross, GA</p> </div>
	

1.1 Jwen 2010/01/21 13:27

1D1Y025CTP1

dsu0082e1



All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED  
SUITABLE FOR #14-2 CU/AL  
CONDUCTORS  
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED  
SUITABLE FOR #2/0-6 CU/AL  
CONDUCTORS  
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of  
**Siemens Industry, Inc.**  
Building Technologies Division

REVISION	DATE	BY	DATE	BY	CUSTOMER
			05/07/13	GR	
1	06/01/04	GR			
					ORDER NO.
					DWG. NO.
					1
					1D1Y025CTP1
					SH 2 OF 2

1.1 Jwen 2010/01/21 13:27