



METER SOCKET COVER	NO. OF JAWS	FACTORY INSTALLED BYPASS	MAIN BUS RATING	BRANCH RATING	NO. OF POSITIONS	CATALOG NUMBER	DIMENSION "A"	DIMENSION "B"	SEMI-FLUSH MOUNTING KIT NO.	120/240VAC, 1Ø 3 WIRE OR 208Y/240VAC, 1Ø 3 WIRE (5TH JAW REQUIRED)		BRANCH LUG WIRE SIZES (AWG-KCML)	
										LINE LUG WIRE SIZES (AWG/KCML)	PHASE AND NEUTRAL	PHASE	NEUTRAL & SERVICE GROUND
RING-TYPE	4	NONE	600A	200A	5	SP6512	38.43"	14.13"			(2) #2 - 600 CU-AL	#6 - 250	#12 - 2/0
RINGLESS	5	NONE	600A	200A	5	SP6512RJ	38.43"	14.13"					
RINGLESS	5	HORN	600A	200A	5	SP6512RJ.B	38.43"	14.13"					
RING-TYPE	4	NONE	600A	200A	6	SP6612	38.43"	14.13"	SP6562FK				
RINGLESS	5	NONE	600A	200A	6	SP6612RJ	38.43"	14.13"					
RINGLESS	5	HORN	600A	200A	6	SP6612RJ.B	38.43"	14.13"					




IF HUB IS REQUIRED THE CATALOG NOS. LISTED BELOW MAY BE USED


3".....S56856-2  
 3-1/2".....S56857-2  
 4".....S56858-2  
 Cover Plate.....S56933






RINGLESS STYLE METER SOCKET COVER WITH BARREL LOCK PROVISIONS (SUPPLIED WITH STAINLESS STEEL LATCH & HASP WITH PROVISIONS FOR PADLOCKING)



RING STYLE METER SOCKET COVER (INCLUDES ALUMINUM SNAP SEALING RING)



TOP LEFT POSITION OMITTED ON 5 GANG



- NOTES:
1. FINISH: ANSI 61 GRAY BAKED POWDER COAT PAINT OVER G-90 GALVANIZED, PHOSPHATIZED STEEL
  2. UL LISTED - FILE E10703
  3. SUITABLE ONLY FOR USE AS SERVICE EQUIPMENT
  4. SHORT CIRCUIT CURRENT RATING OF METER CENTER IS EQUAL TO THE RATING OF THE LOWEST INSTALLED TENANT SERVICE DISCONNECT.
  5. MAIN CONNECTION POINTS RIGIDLY BOLTED WITH BOLT THAT HAS A MINIMUM MAJOR DIAMETER EQUAL TO OR GREATER THAN BUS THICKNESS WITH A CONICAL/SRING WASHER AND HEX NUT.
  6. 5TH JAW IS FACTORY INSTALLED ON RINGLESS ENCLOSURES

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

TOLERANCES:  
 .XX  
 .XXX

HOLE DIAMETER  
 ANGULAR  
 UNDIMENSIONED 90° ANGLES

DWN BDD  
 CHK AGP  
 APVD

DATE 3-6-2003  
 DATE 3-7-2003

SIZE B  
 ISSUE RELEASE NO. DWG NO. SP6X12

SCALE DO NOT SCALE DRAWING SHEET 1 OF 1

REV A

-CONFIDENTIAL-PROPERTY OF  
 Siemens Energy & Automation, Inc.  
 Residential Products Division

UNI-PAK/ALL-IN-ONE METERING EQUIPMENT  
 NEMA TYPE 3R ENCLOSURE  
 600A MAXIMUM TENANT CIRCUIT BREAKERS