

# SIEMENS

*Ingenuity for life*

## SITRANS LVL100/LVL200

Reliable liquid detection

[usa.siemens.com/level](http://usa.siemens.com/level)

### SITRANS LVL100 and LVL200 for liquid level applications

SITRANS LVL100 and LVL200 are vibrating liquid level switches for high, low, and demand level alarms and pump protection for liquid applications. These compact switches are reliable, easy-to-use, and are unaffected by changing conditions such as conductivity, dielectric, vapors, or bubbles.

They can be connected to most process, alarm, and control systems used in storage and processing applications.

These switches are insensitive to external vibrations and are exceptionally durable. They are easy to set up and feature a uniquely threaded piezo drive that increases reliability and performance in high temperature applications.

SITRANS LVL100 and LVL200 both have a failsafe function that alerts the user if the electronics detect damage or corrosion to the instrument.

#### SITRANS LVL100

- Low maintenance
- Ideal for confined space applications a pipelines down to DN25 or (1 inch)
- Hygienic process connections
- High pressure up to 64 bar g (928 psi g)
- High process temperature up to 150 °C (302 °F)
- Advanced fault monitoring
- Function test outside enclosure

#### SITRANS LVL200

- SIL 2 qualified for high level and dry run applications
- Hygienic process connections
- High pressure to 64 bar g (928 psi g)
- High process temperature up to 250 °C (482 °F)
- Advanced fault monitoring





	SITRANS LVL100	SITRANS LVL200
<b>Power</b>		
	<ul style="list-style-type: none"> <li>• 10 to 55 V DC (Transistor PNP)</li> <li>• 20 to 253 V AC, 50/60 Hz; 20 to 253 V DC (non-contacting)</li> </ul>	<ul style="list-style-type: none"> <li>• 20 to 253 V AC, 50/60 Hz; 20 to 72 V DC (Relay DPDT)</li> <li>• 20 ... 253 V AC, 50/60 Hz, 20 ... 253 V DC (contactless)</li> <li>• For connection to an amplifier according to NAMUR IEC 60947-5-6, approx. 8.2 V (Namur)</li> </ul>
<b>Performance</b>		
<b>Minimum material density</b>	<ul style="list-style-type: none"> <li>• Density 0.7 to 2.5 g/cm<sup>3</sup> (0.025 to 0.09 lbs/in<sup>3</sup>)</li> <li>• Viscosity: 0.1 to 10,000 mPa s</li> </ul>	<ul style="list-style-type: none"> <li>• Density 0.5 to 2.5 g/cm<sup>3</sup> (0.018 to 0.09 lb/in<sup>3</sup>)</li> <li>• Viscosity: 0.1 to 10,000 mPa s</li> <li>• High and low sensitivity switch sets density value from 0.5 to 0.7 g/cm<sup>3</sup></li> </ul>
<b>Accuracy</b>	<ul style="list-style-type: none"> <li>• Hysteresis approx. 2 mm (0.08") with vertical installation</li> <li>• Frequency 1200 Hz</li> </ul>	<ul style="list-style-type: none"> <li>• Hysteresis approx. 2 mm (0.08") with vertical installation</li> <li>• Frequency 1200 Hz</li> </ul>
<b>Interface</b>		
<b>Alarm output</b>	Signal LED, Contactless electronic switch, Transistor PNP	<ul style="list-style-type: none"> <li>• Relay output (DPDT)</li> <li>• Two-wire NAMUR output</li> <li>• Contactless</li> </ul>
<b>Switching Delay</b>	Approx. 500 ms	Approx. 500 ms
<b>Mechanical</b>		
<b>Enclosure</b>	Housing: 316L and plastic PEI	Aluminum die-cast powder coated
<b>Process connections*</b>	<ul style="list-style-type: none"> <li>• Threaded: G ¾" A PN64, G 1" A PN64, ¾" NPT, 1" NPT</li> <li>• Hygienic: Tri-clamp 1", 1½", 2"</li> <li>• Bolting: DN25 PN40, DN40 PN40, SMS</li> </ul>	<ul style="list-style-type: none"> <li>• Threaded: G ¾" A, G 1" A, G 1½" A, ¾" NPT, 1" NPT, 1½" NPT</li> <li>• Hygienic: Tri-clamp 1", 1½", 2", 2½", 3"</li> <li>• Flanged: Conus DN25, DN40 PN40, SMS, Tuchenhagen Varivent DN50 PN10</li> </ul>
<b>Sensor</b>	<ul style="list-style-type: none"> <li>• Tuning fork: 316L</li> <li>• Process seal Klingersil C-4400</li> <li>• Process connection 316L</li> </ul>	<ul style="list-style-type: none"> <li>• Tuning fork: 316L, Hastelloy® C4 (2.4610)</li> <li>• Process connection: 316L, 316L with Hastelloy C4 plated, 316L with ECTFE coated, 316L with PFA coated</li> </ul>
<b>Process conditions</b>		
<b>Pressure rating (vessel)</b>	-1 to 64 bar g (-14.5 to 928 psi g)	-1 to 64 bar g (-14.5 to 928 psi g) dependent on process connection, e.g. flange
<b>Temperature rating</b>	<ul style="list-style-type: none"> <li>• Standard: -40 to 100 °C (-40 to 212 °F)</li> <li>• High temperature: -40 to 150 °C (-40 to 302 °F)</li> </ul>	-50 to 250 °C (-58 to 482 °F)
<b>Approvals</b>		
	CE, Shipping approvals, Overfill protection (WHG)	CE, FM, SIL 2, FDA, 3A, Shipping approvals, EHEDGE, Overfill protection (WHG), ATEX

**Siemens Industry, Inc.**  
 100 Technology Drive  
 Alpharetta, GA 30005  
 1-800-365-8766  
 info.us@siemens.com

Subject to change without prior notice.  
 Order No.: PIFL-5KB03-1016  
 All rights reserved  
 Printed in the USA  
 © 2016 Siemens Industry, Inc.

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.