

DISTRIBUTION WIRE CONNECTOR 6 CABLES 3 PCS.
ACCESSORY FOR: 3VA5 125



| Model | |
|---------------------|-------------|
| Product brand name | SETRON |
| Product designation | accessories |

| Connections according IEC | |
|--------------------------------------------------------------------------------------------------|-------------------------------------------------------------|
| Connectable conductor cross-section | |
| <ul style="list-style-type: none"> • for copper cable / solid / minimum | 1.5 mm ² |
| <ul style="list-style-type: none"> • for copper cable / solid / maximum | 16 mm ² |
| <ul style="list-style-type: none"> • for copper cable / finely stranded / minimum | 1.5 mm ² |
| <ul style="list-style-type: none"> • for copper cable / finely stranded / maximum | 25 mm ² |
| <ul style="list-style-type: none"> • for copper cable / stranded / minimum | 1.5 mm ² |
| <ul style="list-style-type: none"> • for copper cable / stranded / maximum | 35 mm ² |
| <ul style="list-style-type: none"> • for aluminum cable / solid / minimum | 4 mm ² |
| <ul style="list-style-type: none"> • for aluminum cable / solid / maximum | 16 mm ² |
| <ul style="list-style-type: none"> • for aluminum cable / stranded / minimum | 4 mm ² |
| <ul style="list-style-type: none"> • for aluminum cable / stranded / maximum | 35 mm ² |
| Wire stripping length | 12 / 24 / 38,5 mm |
| Tightening torque / when using copper cables | |
| <ul style="list-style-type: none"> • solid | <= 10 mm ² : 6.2 Nm, > 10 mm ² : 7 Nm |

- stranded
- finely stranded






<= 10 mm²: 6.2 Nm, > 10 mm²: 7 Nm

<= 10 mm²: 6.2 Nm, > 10 mm²: 7 Nm

Connections according UL

| | |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------|
| Wire stripping length | 0.5 / 0.9 / 1.5 in |
| Connectable conductor cross-section | |
| <ul style="list-style-type: none"> • for copper cable / solid / minimum • for copper cable / solid / maximum • for copper cable / stranded / minimum • for copper cable / stranded / maximum • for copper cable / finely stranded / minimum • for copper cable / finely stranded / maximum • for aluminum cable / solid / minimum • for aluminum cable / solid / maximum • for aluminum cable / stranded / minimum • for aluminum cable / stranded / maximum | 14 AWG 10 AWG 14 AWG 2 AWG 14 AWG 2 AWG 12 AWG 10 AWG 12 AWG 2 AWG |
| Tightening torque / when using copper cables | |
| <ul style="list-style-type: none"> • solid • stranded • finely stranded | <= 8 AWG: 55 lb-in, > 8 AWG: 65 lb-in <= 8 AWG: 55 lb-in, > 8 AWG: 65 lb-in <= 8 AWG: 55 lb-in, > 8 AWG: 65 lb-in |

Certificates

| General Product Approval | EMC | Declaration of Conformity | other |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|  |  |  |  |
| | |  | Miscellaneous |

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9133-0JF60>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9133-0JF60>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)







http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9133-0JF60

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/20/2017