





| REVISION | DATE | BY      | DATE     | BY |
|----------|------|---------|----------|----|
|          |      |         |          |    |
|          |      | DRAWN   | 16/01/21 | PP |
|          |      | CHEK'D  |          |    |
|          |      | VERIF'D |          |    |

Confidential – Property of  
Siemens Industry, Inc.


|           |                           |
|-----------|---------------------------|
| CUSTOMER  |                           |
| ORDER NO. | DWG. NO.                  |
|           | 3F3Y015FCLN3D16 SH 1 OF 2 |

SIEMENS

|  |  |  |     |   |     |   |     |   |     |   |     |   |     |   |     |   |
|--|--|--|-----|---|-----|---|-----|---|-----|---|-----|---|-----|---|-----|---|
| <p>CATALOG NO. 3F3Y015FCLN3D16</p> <p>SERIAL NO. SERIES H</p> <p>15 kVA 60 Hz 3 PHASE</p> <p>3.9 % IMP AT 135 °C</p> | <p>115 °C RISE 30 °C AVG. AMBIENT</p> <p>220 °C TEMP CLASS 40 °C MAX. AMBIENT</p> <p>PRIMARY ( H1 H2 H3 ) 480V V 10kV BIL</p> <p>SECONDARY( X0 X1 X2 X3 ) 208Y/120V V 10kV BIL</p> <p>WINDING MATERIAL CU</p> <p>ENCLOSURE TYPE 3R WEIGHT 215 LBS</p> <p>ENERGY EFFICIENCY EXCEEDS CSA DOE 10 CFR PART 431:2016 C802.2-2012</p> <p>SPACINGS BETWEEN ANY VENTILATED ENCLOSURE, PANEL AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 3 INCHES</p> <p>SOUND LEVEL IS 3 DB LOWER THAN NEMA ST20 REQUIRMENTS</p> |  <p>VOLTS CONNECT</p> <table style="margin-left: 20px;"> <tr><td>504</td><td>1</td></tr> <tr><td>492</td><td>2</td></tr> <tr><td>480</td><td>3</td></tr> <tr><td>468</td><td>4</td></tr> <tr><td>456</td><td>5</td></tr> <tr><td>444</td><td>6</td></tr> <tr><td>432</td><td>7</td></tr> </table>   | 504 | 1 | 492 | 2 | 480 | 3 | 468 | 4 | 456 | 5 | 444 | 6 | 432 | 7 |
| 504  | 1  |  |     |   |     |   |     |   |     |   |     |   |     |   |     |   |
| 492  | 2  |  |     |   |     |   |     |   |     |   |     |   |     |   |     |   |
| 480  | 3  |  |     |   |     |   |     |   |     |   |     |   |     |   |     |   |
| 468  | 4  |  |     |   |     |   |     |   |     |   |     |   |     |   |     |   |
| 456  | 5  |  |     |   |     |   |     |   |     |   |     |   |     |   |     |   |
| 444  | 6  |  |     |   |     |   |     |   |     |   |     |   |     |   |     |   |
| 432  | 7  |  |     |   |     |   |     |   |     |   |     |   |     |   |     |   |
|  |  | <p>TYPE K</p> <p> LISTED</p> <p> DRY TYPE TRANSFORMER 7705 E112313</p> <p> LR 3902</p> <p>SEISMIC QUALIFICATIONS, FLOOR MOUNT ONLY<br/>OSP-0136-10 IBC 2012/ASCE 7-10<br/>SDS&lt;=2.0g Z/h=1 Ip=1.5</p> |     |   |     |   |     |   |     |   |     |   |     |   |     |   |



3F3Y015FCLN3D16



All Dimensions in inches

ENCLOSURE COLOR : ANSI-61 GREY PAINT OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED  
SUITABLE FOR #14-2 CU/AL  
CONDUCTORS  
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED  
SUITABLE FOR #14-2 CU/AL  
CONDUCTORS  
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential - Property of  
Siemens Industry, Inc.

| REVISION | DATE | BY | DATE    | BY       | CUSTOMER                  |
|----------|------|----|---------|----------|---------------------------|
|          |      |    | DRAWN   | 16/01/21 | PP                        |
|          |      |    | CHEK'D  |          |                           |
|          |      |    | VERIF'D |          |                           |
|          |      |    |         |          | ORDER NO.                 |
|          |      |    |         |          | DWG. NO.                  |
|          |      |    |         |          | 3F3Y015FCLN3D16 SH 2 OF 2 |