# **SIEMENS**



### **PROCESS INSTRUMENTATION**

# Series 760 P/E Valve Positioners

Pneumatic valve positioners for cost-effective valve control

## www.usa.siemens.com/positioners

The Series 760 Valve Positioners provide a cost effective, universal approach to your valve control. Their modular concept allows all models to be built on the base pneumatic unit model 760P. The electro-pneumatic model 760E is created by installing an I/P Transducer into the base. A wide range of accessories is easily installed inside the unit.

The 760 base pneumatic unit provides split ranging, direct or reverse action, and single or double action without requiring additional parts. The mechanical linkage and characterized cam can be replaced in the field to configure the positioner for use with either a linear or rotary actuator. Key design features include non-interaction of the zero and span adjustments.

Series 760 Valve Positioners include provisions for internal limit switch mounting and position feedback devices without requiring additional housings. Thus, the need tpositionersngs that impede access to the main enclosure is eliminated.

#### **Features and Benefits**

- Universal design and choice of interchangeable NAMUR IEC 534-6 rectilinear VDI/VDE 3845 rotary mountings provide wide application flexibility
- Double-acting or single-acting service and split ranging afford application versatility in a single unit
- Non-interaction of the zero and span adjustments and CAMLOC™ cam locking mechanism significantly reduce the calibration and setup time
- Modular design reduces inventory because it allows interchangeable spare parts
- Comes standard with 3 cams-linear, quick opening, and equal % for application versatility

# Functional specifications

Temperature Range:	
760P without options	40°C to +85°C (-40°F to +185°F)
760P with high temperature option	29°C to +149°C (-20°F to +300°F), Viton® input diaphragm
760E without options	40°C to +75°C (-40°F to +167°F)
760P or E with Option Kit	
Ingress	·
Connections:	
Pneumatic	
Gauge	
Electrical	
Exhaust	
Finish	
Output Configuration	S S
Action	
Supply Pressure	150 psig maximum
Air Consumption:	
Standard Spool	0.5 scfm
Low Gain Spool	
High Flow Capacity Spool	
nigii riow Capacity Spool	1.0 Scilli typical
Flow Capacity (at 60 psi with 25% drop)	
Standard Spool	9 scfm ( $Cv = 0.3$ )
Low Flow Spool	9 scfm ( $Cv = 0.3$ ) (1/2 pressure gain of standard)
High Flow Spool	· · · · · · · · · · · · · · · · · · ·
Input Signal	
760P	
760E	4-20 mA
Mechanical Feedback	
Rotary	90 degree standard
Linear	
Cam Characterization	The state of the s
	160%/% @ 60 psi supply standard, 80%/% with high temp option
Span	
Zero	
	• • • • • • • • • • • • • • • • •
Performance	
Linearity:	
760P	0.5% of normal span <sup>1)</sup> (typical)
760E	0.75% of normal span <sup>1)</sup> (typical)
Hysteresis:	
760P	0.75% of normal span <sup>1)</sup> (typical)
760E	· • • • • • • • • • • • • • • • • • • •
Deadband	· · · · · · · · · · · · · · · · · · ·
Repeatability	
	Less than 0.2% of span <sup>2)</sup> for a 5 psi change in supply pressure
	1

#### **Hazardous Area Class Approvals**

FM / CSA / ATEX / CE Refer to product manual for details

<sup>&</sup>lt;sup>1)</sup>Normal span is 12 psig (760P) or 16 mA (760E)


<sup>2)</sup> Valve span travel

Valve Positioner Base Model	760									
Input Signal										
4 to 20 mA <sup>1)</sup>		E1								
3 to 15 psig		P1								
3 to 27 psig		P2								
20 to 100 kPa		P4								
0.2 to 1 Bar		P5								
0.2 to 1.0 kg/cm2		P6								
Action										
1/2-inch to 4-inch stroke (with 3, 60° cams)			1	1						
2-inch to 6-inch stroke (with 3, 60° cams)			2	]						
1/4-turn, 1/2-inch square shaft (with 3, 90° cams)			3	1						
1/2-inch to 2-inch stroke (with 3, 60° cams)			4	1						
1/4-turn, NAMUR style shaft (with 3, 90° cams)			5	1						
1/4-turn 1/2-inch square shaft (with 3, 60° cams)			7							
1/2-inch to 4-inch stroke lever (with 1, 90° linear cam)			Е							
2-inch to 6-inch stroke lever (with 1, 90° linear cam)			F	1						
1/4-turn NAMUR shaft (with 3, 60° cams)			S	]						
Enclosure Type with 4X/IP65 with 3/4-Inch NPT Conduit Connection										
Standard				Α						
With Beacon Indicator –for Action selections with 90° cams 1)				В						
With Flat Indicator – for Action selections with 60° cam 1)				J						
With Flat Indicator – for Action selections with 90° cam 1)				K						
Enclosure Type 4X/IP65 with M25 Conduit Connection 3)										
Standard				Е						
With Beacon Indicator (For Action selections with 90° cams 1)				F						
With Flat Indicator – for Action selections with 60° cam <sup>1)</sup>				N						
With Flat Indicator – for Action selections with 90° cam 1)				Р						
Flow Capacity										
Standard capacity spool valve assembly (Cv = 0.3)					Α					<u> </u>
High flow capacity spool valve assembly (Cv = 0.6)					В					
Low flow gain spool valve assembly (approximately 1/2 standard flow gain) 4)					С					
Environmental Construction										<u> </u>
Std. temp. 760P: -40°C to +85°C (-40°F to +185°F); 760E: -40°C to +75°C (-40°F to +167°F)						Α				
High temperature (760P with no electrical options and no approvals) -29°C to +149°C (-20°F to +300°F)						С				
Ozone resistant with Viton® fluoroelastomer and iso-elastomeric spring						Е				
Ozone resistant with Viton® fluoroelastomer and standard spring						F				
Gauges										
Not Required							N			
Gauges, 3 <sup>1)</sup>							G			
Limit Switch Boards 1)										
Not Required								N		
Mechanical								1		
Proximity Switches (NAMUR Standard)								2		

Valve Positioner Base Model	760						
Output Options 1)							
Not Required					N		
Potentiometer 1K Ohm					1		
4-20 mAdc Feedback					2		
Potentiometer, 1K Ohm with Stainless Steel Feedback Gear					3		
4-20 mA Feedback with Stainless Steel Feedback Gear					4		
Design Level						D	
Electrical Certification Non-Approved							N
FM / CSA / ATEX / CE <sup>1)</sup>							6

- 1) Not available with High Temperature Option.
- 3) For 3/4NPT to M25 conduit adapter, order TGX:16300-1439.
- 4) Used on small volume actuators (i.e., piston diameter less than 4" (10mm)

#### **Dimmensional Drawings**



#### Legal Manufacturer

Siemens Industry, Inc. 100 Technology Drive Alpharetta, GA 30005 United States of America Telephone: +1 (800) 365-8766

usa.siemens.com/pi Order No.: PIBR-0760B-0322

This document contains a general description of available technical options only, and its effectiveness will be subject to specific variables including field conditions and project parameters. Siemens does not make representations, warranties, or assurances as to the accuracy or completeness of the content contained herein. Siemens reserves the right to modify the technology and product specifications in its sole discretion without advance notice.