



- NOTES**
- 1) TERMINALS RECOMMENDED ARE PRE-INSULATED & MUST BE CRIMPED USING APPROVED TOOLING. AMP PJDG OR PLASTI GRIP FUNNEL ENTRY (RING TONGUE) FOR M4 FIXING STUD.
 - 2) FOR OUTLINE & PANEL DRILLING, SEE 29395X10004 (A4).
 - 3) CONNECTIONS TO THIS COMMUNICATIONS FACILITY IS BY SCREENED, TWISTED PAIR CABLE, ON SITE. WHEN WIRING OTHER FACILITIES ENSURE THAT THESE TERMINALS ARE NOT OBSCURED BY OTHER WIRE RUNS.
 - 4) CONTACTS SHOWN THUS  ARE INTERNAL RELAY CASE ASSEMBLY CONTACTS AND CLOSE WHEN THE RELAY CHASSIS IS WITHDRAWN FROM THE CASE.
 - 5) FOR THE RELAY CASE ASSEMBLY SEE 2436G40046

ABBREVIATIONS

I	CURRENT INPUTS
BI	BINARY INPUTS
BO	BINARY OUTPUTS
CO	CHANGE OVER BINARY OUTPUT CONTACTS
NO	NORMALLY OPEN BINARY OUTPUT CONTACTS
NC	NORMALLY CLOSED BINARY OUTPUT CONTACTS


COMMUNICATIONS IDENTIFICATION

COM1	RS485 (ON BLOCK 'B' TERMINALS 14,16,18 & 20)
COM2	USB TYPE 'B' PORT (ON RELAY FRONT LABEL)





CONNECTOR 1 CONNECTOR 2

FOR INTERNAL USE ONLY
UNCONTROLLED COPY
NOT SUBJECT TO UPDATE



COMMS MODULE



COLOUR	TOLERANCE (MIN/MAX)
0/4/0	0/1
6/2/0	0/2
9/2/0	0/2
30/2/0	0/2

Rev	1/A	Change	Date	Drawn By	AMAR	Checked By	AMAR
				DRN BY	AMAR	CHKD BY	JOHNSF
				APPD BY	JAVANT J	EM EA PRO R&D	
				Siemens Ltd			
				Material		NTS	
				Title		TERMINAL ID & WIRING DIAGRAM FOR 7SR17 4CT+3BI+5BO(2CO+3NO), 8 RTD	
				Document No		2436W40051	
				Part No		7SR17	
				Sheet		1 of 1	