

SETRON PAC3120 LCD 96X96 mm Power Monitoring Device  
 Controll panel instrument for electrical values protocol: Modbus RTU  
 with graphics display U rated input: 690/400V 45-65Hz IE rated input:  
 X/1A oder X/5A AC Power supply: 24 ... 60 V -20/+10 % DC screw  
 connections



Figure similar

Model	
Product brand name	SETRON
Design of the product	basic
Product type designation	Measuring instrument
Type of measured value detection	complete
Design of the power supply	Extra-low voltage power supply unit
General technical data	
Cutout width	92 mm
Cutout height	92 mm
Size of Power Monitoring Device / company-specific	size 96
Operating mode for measured value detection	
• automatic line frequency detection	Yes
• set at 50 Hz	No
• set to 60 Hz	No
Pulse duration	
• initial value	30 ms
• Full-scale value	500 ms

Voltage curve	Sinusoidal or distorted
Measurable line frequency / initial value	45 Hz
Measurable line frequency / Full-scale value	65 Hz
Measuring procedure / for voltage measurement	TRMS

#### Supply voltage

Type of voltage / of the supply voltage	DC
Measuring category / for supply voltage	CATIII
<b>Apparent power consumption</b>	
<ul style="list-style-type: none"> <li>without expansion module / typical</li> </ul>	4 V·A

#### Protection class

Protection class IP	
<ul style="list-style-type: none"> <li>on the front</li> </ul>	IP65
<ul style="list-style-type: none"> <li>Rear side</li> </ul>	IP20

#### Current

Measurable current	
<ul style="list-style-type: none"> <li>1 / at AC / Rated value</li> </ul>	1 A
<ul style="list-style-type: none"> <li>2 / at AC / Rated value</li> </ul>	5 A

#### Suitability

Suitability for operation	Installation in stationary control panels in closed rooms
Adjustable time period / minimum	10 ms

#### Product function

Product function	
<ul style="list-style-type: none"> <li>Illuminance of display backlighting adjustable</li> </ul>	No
<ul style="list-style-type: none"> <li>Time-controlled reduction of the illuminance of display backlighting possible</li> </ul>	Yes
<ul style="list-style-type: none"> <li>reactive power measurement</li> </ul>	Yes
<ul style="list-style-type: none"> <li>frequency measurement</li> </ul>	Yes
<ul style="list-style-type: none"> <li>pulse measurement</li> </ul>	Yes
<ul style="list-style-type: none"> <li>Display contrast adjustable</li> </ul>	Yes
<ul style="list-style-type: none"> <li>voltage measurement</li> </ul>	Yes
<ul style="list-style-type: none"> <li>Current measurement</li> </ul>	Yes
<ul style="list-style-type: none"> <li>active power measurement</li> </ul>	Yes

#### Display and operation

Design of the display	LCD
Number of keys	4
Color / of the background of the display	white
Product function / Display can be inverted (positive <=> negative mode)	Yes
Horizontal image resolution	128
Vertical screen resolution	96

Communication	
Number of active connections / at the Ethernet interface	3
Protocol	Modbus RTU
<ul style="list-style-type: none"> <li>• is supported</li> </ul>	
Transfer rate	
<ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>	4.8 kbit/s 115.2 kbit/s
Fault limits	
Reference condition / for metering accuracy	In accordance with IEC61557-12, IEC62053-22 and IEC62053-23
Formula for relative total measurement inaccuracy	
<ul style="list-style-type: none"> <li>• for measured variable reactive energy</li> <li>• for measured variable output</li> <li>• for measured variable output factor</li> <li>• for measured variable voltage</li> <li>• for measured variable current</li> <li>• for measured variable active energy</li> </ul>	Class 2 according to IEC61557-12 and/or IEC62053-23 +/- 0,5 % +/- 0,5 % +/- 0,2 % +/- 0,2 % Cl. 0.5 acc. to... IEC62053-22
Inputs Outputs	
Input voltage / at digital input	
<ul style="list-style-type: none"> <li>• at DC / maximum</li> </ul>	30 V
Number of digital outputs	2
Number of digital inputs	2
Digital output version	switching or pulse output function
Type of switching output	bidirectional
Type of electrical connection	
<ul style="list-style-type: none"> <li>• at the digital inputs</li> <li>• at the digital outputs</li> </ul>	screw-type terminals screw-type terminals
Input current / at digital input	
<ul style="list-style-type: none"> <li>• initial value for signal&lt;1&gt;-recognition</li> </ul>	7 mA
Output current	
<ul style="list-style-type: none"> <li>• at the digital outputs / at DC / limited to 100 ms / maximum</li> </ul>	130 mA
Operating conditions for digital inputs / external voltage supply	Yes
Operating voltage / as output voltage / at DC / maximum permissible	30 V
Property of the output / Short-circuit proof	Yes
Internal resistance / at the digital outputs	55 Ω
Switching frequency / at digital output / maximum	17 Hz
Measuring inputs	
Outer conductors and neutral conductors internal resistance / for voltage measurement	1.5 MΩ

Measurable supply voltage	
<ul style="list-style-type: none"> <li>• between (PE)N and L / at AC / minimum</li> </ul>	11.5 V
<ul style="list-style-type: none"> <li>• between (PE)N and L / at AC / maximum</li> </ul>	480 V
<ul style="list-style-type: none"> <li>• between (PE)N and L / at AC / maximum rated value</li> </ul>	400 V
<ul style="list-style-type: none"> <li>• between the outer conductors / at AC / maximum rated value</li> </ul>	690 V
Voltage measuring range extension / with external voltage transformers	Yes
Current measuring range extension / with external current transformers	Yes
Measuring category / for voltage measurement	CATIII
Supply voltage / between the outer conductors / at AC / maximum permissible	831 V
Continuous current / at AC / maximum permissible	10 A
Measuring category / for current measurement	CATIII
Zero-point suppression / for current measurement	0 ... 10 %
Relative measurable current / at AC	
<ul style="list-style-type: none"> <li>• minimum</li> </ul>	1 %
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	100 %
Apparent power consumption / for current measurement	
<ul style="list-style-type: none"> <li>• with measuring range 5 A / per phase</li> </ul>	0.3 V·A
Measuring procedure / for current measurement	TRMS

## Connections

### Type of electrical connection

- |   |                      |
|---|----------------------|
| <ul style="list-style-type: none"> <li>• at the inputs for supply voltage</li> </ul>      | screw-type terminals |
| <ul style="list-style-type: none"> <li>• at the measurement inputs for voltage</li> </ul> | screw-type terminals |
| <ul style="list-style-type: none"> <li>• at the measurement inputs for current</li> </ul> | screw-type terminals |

## Mechanical Design

Height	96 mm
Height / of the display	54 mm
Width	96 mm
Width	
<ul style="list-style-type: none"> <li>• of the display</li> </ul>	72 mm
Depth	56 mm
Installation depth	51 mm
Mounting type / panel mounting	Yes
Mounting position	vertical
Material thickness / of the control panel	
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	4 mm
Net weight	325 g

## Environmental conditions

Installation altitude / at height above sea level / maximum	2 000 m
<b>Standard</b> <ul style="list-style-type: none"><li>• for pulse emitter</li></ul>	according to IEC62053-31
Ambient temperature / during operation <ul style="list-style-type: none"><li>• minimum</li><li>• maximum</li></ul>	-25 °C 55 °C
Ambient temperature / during storage <ul style="list-style-type: none"><li>• minimum</li><li>• maximum</li></ul>	-25 °C 70 °C

## Certificates

Certificate of suitability <ul style="list-style-type: none"><li>• Approval Australia</li></ul>	Yes
---	-----

### Declaration of Conformity

other

[Manufacturer Declaration](#)



EG-Konf.

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7KM3120-1BA01-1EA0>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/7KM3120-1BA01-1EA0>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=7KM3120-1BA01-1EA0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7KM3120-1BA01-1EA0)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



