

SIEMENS

Modular Bussed Elbow

Catalog Number

BE4, BE412

Enclosure

Type 1

Module Rating:

1200 Amps, Max.

208Y/120 Volts~, 3 Phase, 4 Wire

240/120 Volts~, 3 Phase, 4 Wire, Delta
(B Phase is High Leg)

For installation by Qualified Person in accordance with all local electrical codes and/or the National Electrical Code ®.

Important: Do not allow petroleum based (hydrocarbon) sprays, chemicals, solvents or any paint to contact interior components. Petroleum based chemicals can cause degradation of electrical insulating materials.

Connect Modules Using:

Quick Connect

Cat. No.

QC4

Torque

400-440 lb-in (35-36 ft.-lb.)

Short Circuit Current Rating

This device has a maximum short circuit current rating of 100,000 amps RMS symmetrical at 240 Volts ~ when used with modules listed below.

IMPORTANT - for use with:

Module

Main Breakers

Switches

Tap/Terminal Boxes

Pull Boxes

Meter Module

Meter Combinations

Extension Box

Bussed Elbow

For Use With Siemens Series#

(W)MC, WB, WEB, WXB, WBT

WMP, WMS, WS, WES

WMTB, WTB, WET, WT_PU

WMMB

(W)MM, WxMM, (W)MT, (W)ML, (W)MK, (W)MLZ(F)

WC, WCL, WCT

WMEX, WSP, WSPD

BE, WELB

Siemens Industry, Inc. Norcross, Georgia U.S.A.

DH1

40901474 0101 Rev.A

® The National Electrical Code is a registered trademark of the National Fire Protection Association.

© 2016 Copyright Siemens Industry, Inc.