

Nuremberg, June 7, 2018

Achema hall 11, booth C3

First pressure transmitters for remote commissioning of functional safety

- **Remote commissioning of SIL devices saves time and effort**
- **Maintenance costs reduced due to increased proof test interval**
- **High accuracy and fast response time increases process efficiency**

Siemens presents Sitrans P320/420, the first pressure transmitter on the market to feature remote safety handling reducing commissioning time in applications requiring functional safety. Via Simatic Process Device Manager (PDM) the safety integrity level (SIL) devices will be commissioned: rather than manually attending to each individual device across the facility, operators can commission transmitters from the control room. This next generation of pressure transmitters was developed according to IEC 61508 standard for the use in SIL 2/3. Significantly lowering maintenance costs could be expected as these transmitters have an increased proof test interval over other devices on the market.

The HART7 Sitrans P transmitters are ready for plant digitalization, giving users in-depth control and analysis through new data logging functions and event control. The devices' reduced response time increases process efficiency by speeding up the control system's response to changing process conditions.

Sitrans P320/420's user-friendly features also include a new larger and improved display, showing users the device's status at a glance. Setup is convenient and quick thanks to four-button programming, Namur NE107 support and a quick start wizard.

With measuring ranges from 20 mbar to 700 bar, depending on the device, these new additions to Siemens pressure portfolio provide reliable results even under extreme conditions. The devices are especially suited for applications where safety is critical: in

industries such as chemical, oil and gas, and power generation. The Sitrans P320/420 can also be implemented in all other industries.



Siemens presents Sitrans P320/420, the first pressure transmitter on the market to feature remote safety handling reducing commissioning time in applications requiring functional safety.

This press information document and a press photo can be downloaded from <http://www.siemens.com/press/PR2018060199PDEN>

Further information is available at www.siemens.com/pressure

Further information on Siemens at Achema 2018 is available at www.siemens.com/achema and www.siemens.com/press/achema2018

Contact for journalists

Dr. David Petry

Phone: +49 (9131) 7-26616; E-mail: david.petry@siemens.com

Follow us on **social media**:

Twitter: <http://www.twitter.com/MediaServiceInd> and www.twitter.com/siemens_press

Blog: <https://blogs.siemens.com/mediaservice-industries-en>

Siemens AG (Berlin and Munich) is a global technology powerhouse that has stood for engineering excellence, innovation, quality, reliability and internationality for 170 years. The company is active around the globe, focusing on the areas of electrification, automation and digitalization. One of the world's largest producers of energy-efficient, resource-saving technologies, Siemens is a leading supplier of efficient power generation and power transmission solutions and a pioneer in infrastructure solutions as well as automation, drive and software solutions for industry. With its publicly listed subsidiary Siemens Healthineers AG, the company is also a leading provider of medical imaging equipment – such as computed tomography and magnetic resonance imaging systems – and a leader in laboratory diagnostics as well as clinical IT. In fiscal 2017, which ended on September 30, 2017, Siemens generated revenue of €83.0 billion and net income of €6.2 billion. At the end of September 2017, the company had around 377,000 employees worldwide. Further information is available on the Internet at www.siemens.com.