

# SIEMENS

Ingenuity for life

## SIPROTEC 7SK82

Motor Protection

[www.siemens.com/siprotec](http://www.siemens.com/siprotec)

### Description

The SIPROTEC 7SK82 motor protection has been designed specifically for a cost-optimized and compact utilization of small-sized to medium-sized motors. With its flexibility and the high-performance DIGSI 5 engineering tool, SIPROTEC 7SK82 offers future-oriented solutions for protection, control, automation, monitoring, and Power Quality – Basic. For motors in explosive environments, the SIPROTEC 7SK82 is also available with EN 60079-14 or VDE (Verband der Elektrotechnik, Elektronik und Informationstechnik) 0165, Part 1 (ATEX) certification.

Main function	Motor protection for small to medium-sized motors (100 kW to 2 MW)
Inputs and outputs	4 current transformers, 4 voltage transformers (optional), 11 or 23 binary inputs, 9 or 16 binary outputs
Hardware flexibility	Different hardware quantity structures for binary inputs and outputs are available in the 1/3 base module. Adding 1/6 expansion modules is not possible; available with large or small display
Housing width	1/3 × 19 inches

### Applications

- Protection against thermal overload of the stator from overcurrent, cooling problems or pollution
- Protection against thermal overload of the rotor during startup due to frequent startups, excessively long startups or blocked rotor
- Monitoring for voltage unbalance or phase outage
- Monitoring the thermal state and the bearing temperatures with temperature measurement
- Detection of idling drives of pumps and compressors, for example
- Detection of ground faults in the motor



SIPROTEC 7SK82 Motor Protection

- Protection against motor short circuits
- Protection against instability due to undervoltage
- Detection and recording of power quality data in the medium voltage and subordinate low voltage power system

### Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Motor protection functions: Startup time monitoring, thermal overload protection for stator and rotor, re-start inhibit, unbalanced-load protection, load-jam protection
- Stator and bearing temperature monitoring via temperature sensors with optional temperature inputs or with external RTD unit.
- Sensitive ground-fault protection (non-directional, directional) to detect stator ground faults
- Directional and non-directional overcurrent protection (shortcircuit protection) with additional functions
- Detection of ground faults of any type in compensated or isolated electrical power systems using the following functions: 3I0>, V0>, transient ground fault,  $\cos \phi$ ,  $\sin \phi$ , dir. detection of intermittent ground faults, harmonic detection, and admittance measurement

# Safe and efficient

- Ground-fault detection using the pulse-detection method
- Overvoltage and undervoltage protection
- Arc protection
- Power protection, configurable as active or reactive-power protection
- Detection of current and voltage signals up to the 50th harmonic with high accuracy for selected protection functions (such as thermal overload protection) and operational measured values
- PQ - Basic: Voltage unbalance; voltage changes: overvoltage, dip, interruptions; TDD, THD, and harmonics
- Control, synchrocheck, and switchgear interlocking protection
- Graphical logic editor to create high-performance automation functions in the device
- Single-line representation in the small or large display
- Fixed integrated electrical Ethernet RJ45 interface for DIGSI 5 and IEC 61850 (reporting and GOOSE)
- 2 optional pluggable communication modules, usable for different and redundant protocols (IEC 61850, IEC 60870-5-103, IEC 60870-5-104, Modbus TCP, DNP3 serial and TCP, PROFINET IO)
- Reliable data transmission via PRP and HSR redundancy protocols
- Certification for use in environments at risk of explosion (EN 60079-14 or VDE 0165, Part 1, ATEX)
- Extensive cybersecurity functionality, such as role-based access control (RBAC), logging of security-related events, signed firmware, or authenticated IEEE 802.1X network access.
- Simple, fast, and secure access to the device via a standard Web browser -to display all information and diagnostic data, vector diagrams, single-line and device display pages
- Secure serial protection communication, also over great distances and all available physical media (optical fiber, twowire connections, and communication networks)
- Detecting operational measured variables and protectionfunction measured values to evaluate of the systems, to support commissioning, and to analyze faults
- Integrated RTD inputs (optional) for thermal motor monitoring
- Phasor Measurement Unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- High-performance fault recording (buffer for a max. record time of 80 s at 8 kHz or 320 s at 2 kHz)
- Auxiliary functions for simple tests and commissioning

## Benefits

- Compact and low-cost motor protection
- Safety due to powerful protection functions
- Purposeful and easy handling of devices and software thanks to a user-friendly design
- Cybersecurity in accordance with NERC CIP and BDEW Whitepaper requirements
- Highest availability even under extreme environmental conditions by standard coating of the modules
- Full compatibility between IEC 61850 Editions 1, 2.0, and 2.1



Siemens 2020  
Smart Infrastructure  
Digital Grid  
Humboldtstrasse 59  
90459 Nuremberg,  
Germany

For the U.S. published by  
Siemens Industry Inc.

100 Technology Drive  
Alpharetta, GA 30005  
United States

Customer Support: <http://www.siemens.com/csc>

© Siemens 2020. Subject to changes and errors.  
SIPROTEC 7SK82\_Profile V1.docx\_12.20

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit ([www.openssl.org](http://www.openssl.org)), cryptographic software written by Eric Young ([ey@cryptsoft.com](mailto:ey@cryptsoft.com)) and software developed by Bodo Moeller.