

Assembly instructions



Figure 1
Completely assembled display

Safety switch display

Assembly instructions

1. Slide the two supporting feet (A & B) onto the bottom of face board. Make sure the engraved figure 8-like section is facing upward.
2. Place the figure 8 cutout (C) into the engraved area to connect the two feet.
3. Place the legs (D & E) into the slots on the feet.
4. Secure the legs from the bottom slots with the two wedges (F & G)
5. Insert the square top stabilizing joint (H) between the two legs.
6. Install 1/4-20 bolt from behind the face board and loosely install washer and wing nut on the front.
7. Install a 30 amp fusible Siemens safety switch (from distributor's stock) onto the 1/4-20 bolt. See Figure 1.
8. Align the holes in the safety switch through the face board clearance holes (K & L) and the pre-drilled holes on the legs.
9. Install the 2 screws through the bottom mounting holes of the safety switch into the face board and the two legs. Do not over-tighten.
10. Tighten the wing nut in top switch mounting hole to complete the switch installation.




Figure 2
Side view




Figure 3
Back view



Figure 4
Bottom view

Siemens Industry, Inc.
Building Technologies Division
5400 Triangle Parkway
Norcross, GA 30092
1-800-964-4114

info.us@siemens.com

www.usa.siemens.com/switches

Subject to change without prior notice.
Order No: SSFL-PHVLT-0410
All rights reserved.
Printed in USA
©2010 Siemens Industry, Inc.

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.