


1 IF IN DOUBT ASK  
2 DO NOT SCALE

3 4 5 6 7 8



PANEL CUT-OUT

4 HOLES - Ø3.6  
(SEE NOTE)

25mm MIN. CLEARANCE FOR TERMINAL WIRING  
70mm MIN. CLEARANCE FOR F/O COMMS CABLE

**NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED**

NOTE:  
THE Ø3.6 HOLES ARE FOR M4 THREAD FORMING (TRILOBULAR) SCREWS.  
THESE ARE SUPPLIED AS STANDARD AND ARE SUITABLE FOR USE IN  
FERROUS/ALUMINIUM PANELS 1.6mm THICK AND ABOVE. FOR OTHER  
PANELS, HOLES TO BE M4 CLEARANCE (TYPICALLY Ø4.5) AND RELAYS  
MOUNTED USING M4 MACHINE SCREWS, NUTS AND LOCKWASHERS  
(SUPPLIED IN PANEL FIXING KIT).

**EU EXPORT CONTROLS** ECEN: N AL: N  
**This document is not Export Controlled unless sending to Critical Countries.**

Copyright © 2019 Siemens PLC. Hebburn

1	08/08/19	CHANGE NOTED
ISSUE	DATE	NOTED

Dimensions in millimetres : Surface texture in micrometres.

Machine where marked ✓

For explanation of dimensions, tolerances, notes etc. see B.S.308.

Limit on untoleranced unmachined dimensions ± \_\_\_\_\_

Limits on untoleranced machined dimensions to B.S.4500:

i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;

over 6 to 30±0.2; over 120 to 315±0.5;

General unmachined angular tolerance ± \_\_\_\_\_

Finish:

Title:

OVERALL DIMENSIONS AND PANEL DRILLING  
FOR 7SR5 S6 CASE.

Treatment:

Original Scale:

1 : 2

Drq. No.

2518X10006

First used on:

Similar Articles:

Supersedes:

DRAWN J.BURNETT CHECKED \_\_\_\_\_

APPROVED N.C

DATE 08/08/19

IE

OPS

PCP

Purch.Spec. TQ

EAC

CE

STD

A3