




REVISION	DATE	BY	DATE	BY
		DRAWN	08/03/19	CY
		CHEK'D		
		VERIF'D		

Siemens Industry, Inc. Building Technologies Division		
CUSTOMER		
ORDER NO.	DWG. NO.	
	1D1Y025FTP1	SH 1 OF 2

SIEMENS

CATALOG NO. 1D1Y025FTP1 SERIAL NO. 25 kVA 60 Hz 1 PHASE 3.2 % IMP AT 135 °C 115 °C RISE °C AVG. AMBIENT 220 °C TEMP CLASS °C MAX. AMBIENT PRIMARY (H1 H3 H2 H4) 240X480 V SECONDARY(X4 X2 X3 X1) 120/240 V WINDING MATERIAL AL ENCLOSURE TYPE NEMA-3R WEIGHT 315 LBS ENERGY EFFICIENCY NEMA TP 1-2002	SERIES H 1 PHASE °C AVG. AMBIENT °C MAX. AMBIENT 240X480 V 120/240 V AL NEMA-3R 315 LBS NEMA TP 1-2002	 HAM1006																																				
<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="width: 15%;">VOLTS</th> <th style="width: 85%;">INPUT LINE ON H1 & H4 CONNECT</th> </tr> </thead> <tbody> <tr> <td>504</td> <td>H2-1, H3-2</td> </tr> <tr> <td>492</td> <td>H3-2, H2-3</td> </tr> <tr> <td>480</td> <td>H2-3, H3-4</td> </tr> <tr> <td>468</td> <td>H3-4, H2-5</td> </tr> <tr> <td>456</td> <td>H2-5, H3-6</td> </tr> <tr> <td>444</td> <td>H3-6, H2-7</td> </tr> <tr> <td>432</td> <td>H2-7, H3-8</td> </tr> <tr> <td>252</td> <td>H2-1, H3-2</td> </tr> <tr> <td>240</td> <td>H2-3, H3-4</td> </tr> <tr> <td>228</td> <td>H2-5, H3-6</td> </tr> <tr> <td>216</td> <td>H2-7, H3-8</td> </tr> </tbody> </table> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="width: 15%;">VOLTS</th> <th style="width: 35%;">CONNECT</th> <th style="width: 50%;">OUTPUT LINE</th> </tr> </thead> <tbody> <tr> <td>120</td> <td>X1-X3, X2-X4</td> <td>X1-X4</td> </tr> <tr> <td>240</td> <td>X2-X3</td> <td>X1-X4</td> </tr> <tr> <td>240/120</td> <td>X2-X3</td> <td>X1-X2-X4</td> </tr> </tbody> </table>			VOLTS	INPUT LINE ON H1 & H4 CONNECT	504	H2-1, H3-2	492	H3-2, H2-3	480	H2-3, H3-4	468	H3-4, H2-5	456	H2-5, H3-6	444	H3-6, H2-7	432	H2-7, H3-8	252	H2-1, H3-2	240	H2-3, H3-4	228	H2-5, H3-6	216	H2-7, H3-8	VOLTS	CONNECT	OUTPUT LINE	120	X1-X3, X2-X4	X1-X4	240	X2-X3	X1-X4	240/120	X2-X3	X1-X2-X4
VOLTS	INPUT LINE ON H1 & H4 CONNECT																																					
504	H2-1, H3-2																																					
492	H3-2, H2-3																																					
480	H2-3, H3-4																																					
468	H3-4, H2-5																																					
456	H2-5, H3-6																																					
444	H3-6, H2-7																																					
432	H2-7, H3-8																																					
252	H2-1, H3-2																																					
240	H2-3, H3-4																																					
228	H2-5, H3-6																																					
216	H2-7, H3-8																																					
VOLTS	CONNECT	OUTPUT LINE																																				
120	X1-X3, X2-X4	X1-X4																																				
240	X2-X3	X1-X4																																				
240/120	X2-X3	X1-X2-X4																																				
SPACINGS BETWEEN ENCLOSURE AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 6 INCHES TYPE F  LR 3902 LISTED DISTRIBUTION TRANSFORMER 77US E112313 SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS DO NOT INSTALL IN AREAS ACCESSIBLE TO PUBLIC FOR INSTALLATION SEE INSTRUCTION MANUAL NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA dsu0082e1																																						





All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #2/0-6 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR 250MCM-6 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Siemens Industry, Inc.
Building Technologies Division

REVISION	DATE	BY	DATE	BY
		DRAWN	08/03/19	CY
		CHEK'D		
		VERIF'D		

CUSTOMER

ORDER NO.

DWG. NO.

1D1Y025FTP1

SH 2 OF 2

0.0 jwen 2010/01/21 13:27