



- Notes:**
- Main conduit box is free standing and must be supported from below by customer. Main conduit box is not level with motor feet. A removable bottom plate is supplied on the FS2 and FS3 conduit boxes. A 3.0" spacer with a 1.125" adapter is supplied on both frames for the FS2 and FS3 conduit boxes.
 - C = Length of motor from drive end of shaft to end of non-drive end of motor.
 - $V = (N-W) - 0.25$ = length of shaft available for coupling.
 - Adding the low noise side ducts requires a 12.0" spacer on both frames for the FS2 and FS3 conduit boxes. Please note that the 3.0" spacer and the 1.125" adapter, already shown, will not be provided. Adding the low noise oversized side ducts requires an 18.0" spacer on both frames the FS2 and FS3 conduit boxes. Please note that the 3.0" spacer and the 1.125" adapter, already shown, will not be provided. All associated free standing conduit box dimensions will change accordingly.
 - Shims may be necessary under motor feet for direct connection.
 - Short shaft is for direct connection.
 - Adding a rotating labyrinth seal to the drive end decreases N by: 6 Pole & Slower: 0.40"
 - Adding a ground brush increases BA and C by: 6 Pole & Slower: 2.50"
 - Adding a ground brush with rotating labyrinth seal increases BA and C by: 6 Pole & Slower: 2.75"

Standard Dimensions in Inches

Shaft	Frame	Speed	B	BA _{8,9}	C _{2,8,9}	E	2F	K	N ₇	(N-W)	R	S	U	V ₃	ES	Approx. Ship Wt. (Lbs)
Short	6811	6 Pole & Slower	61.0	11.50	80.6	13.50	50.0	11.0	10.45	9.25	4.169	1.250	5.375	9.00	8.0	12000
Short	6813	6 Pole & Slower	74.0	11.50	93.6	13.50	63.0	12.5	10.45	9.25	4.169	1.250	5.375	9.00	8.0	14700

Certification: Customer _____ P.O. _____ S.O. _____ Item _____
 HP _____ RPM _____ Frame _____ PH/HZ/Volts 3/_____/_____
 By _____ Date _____ Terminal Box Size FS2 FS3
 Comments _____
 Not for construction, installation or application purposes unless certified.