



TEL (915) 590-8500
FAX (915) 590-8510

6.25"

Cat. No. HUN364 **Non-Fusible Heavy Duty Safety Switch** **Type VB II**
200 Amps Maximum **600 Volts AC (V~) Maximum** **600 Volts DC (V=) Maximum**
Type 1 **Indoor**

Horsepower Ratings	240 VAC 1Ø	240 VAC 3Ø	480 VAC 1Ø	480 VAC 3Ø	600 VAC 1Ø	600 VAC 3Ø	250 VDC	600 VDC
Max. HP	15	60	50	125 ⁷	50	150 ⁷	40	50

Suitable for use as Service Equipment when used with ground bar kit **HG61234M** on 3 phase, 3 wire systems or when used with **HN64M** neutral kit on 1 phase, 3 wire or 3 phase, 4 wire systems.

Fuse and Short Circuit Information

This switch is suitable for use on a circuit capable of delivering not more than 200,000 amperes, RMS symmetrical, **600** volts maximum when protected by class J, R or T fuses rated **200** amperes maximum.

Danger - Unless Type FD6 or JD6 circuit breakers or Class J, R or T fuses are used to protect this switch, it may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes, RMS symmetrical.

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, RMS symmetrical, **600** volts maximum, when protected by Class K fuses, Class H fuses or a UL Listed Circuit Breaker rated for 10,000 amperes, RMS symmetrical, **600** volts maximum.

This switch is suitable for use on a circuit capable of delivering not more than 18,000 amperes, rms symmetrical, when protected by Type FD6 or JD6 circuit breakers rated **200** amperes maximum.

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, **600** volts DC maximum, when protected by fuses marked with an interrupting rating of 10,000 amperes, **600** volts DC.

Danger - Unless fuses marked for an interrupting rating of 10,000 amperes at **600** volts DC are used to protect this switch, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes.

	⚠ DANGER
	<p>Hazardous voltage. Will cause death or serious injury.</p> <ul style="list-style-type: none"> • Disconnect and lock out power supplying this switch before working on this switch. • Turn off switch before removing or installing fuses if so equipped. • Always use a properly rated voltage sensing device on all fuse clips (Fusible) or all load side terminals (Non-Fusible) to confirm switch is off. • Close or replace cover before turning power on.

8.75"

Terminal & Wire Information **USE 75°C COPPER OR ALUMINUM WIRE**

Description	Wire Range	Wire Tightening Torque ⁵	Lug Mounting Torque ⁵
Line, Load & Main Neutral	6 AWG - 300 kcmil	275 lb-ins.	135 lb-ins.
Service Ground	14-1/0 AWG	35 lb-ins. 14-10 AWG / 40 lb-ins. 8 AWG 45 lb-ins. 6-4 AWG / 50 lb-ins. 3-1/0 AWG	80 lb-ins.

Inspection record number:

Accessories

Aux. Switch (1NO - 1NC)	HA161234M	Neutral	HN64M
Aux. Switch (2NO - 2NC)	HA261234M	Ground Lug Kit (Wire Range 14-4 AWG)	HG61234M

Replacement Parts

Line Base	HNB64	Wire Grip Kit (AL)	HL64	Handle / Handle Guard	HH64
Mechanism	HM64				

Protected by one or more of the following US Patents: 6,134,979, 5,945,650, 5,990,439.

⁵ When tightening or replacing connectors, refer to lug mounting torque in Terminal & Wire Information Table.

⁷ Not for use as a motor controller over 74.6 kW (100 hp).

For questions on this device please call 1-800-964-4114



Murray Electrical Products
Siemens Industry, Inc.
Norcross, GA 30092 USA
<http://www.murrayelectrical.com>
Assembled in Mexico

Pc. No. 506123G07
0202



R .125"
X4

COMPANY NAME		Due to the variances among computer monitors and printers, the depictions of the colors you see may not be a true representation of the final color job, these colors are only for proofing. If close color matching is a requirement of the job, then you must let us know at the beginning of the job and specify PMS colors or otherwise provide color samples.									
SIEMENS INDUSTRY/MTR		JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.					PART NO. 506123G07				
THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.	MATERIAL		SIZE		<input type="checkbox"/> OK TO PRINT AS IS		<input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF		DWG NO. 500443; 501010 41P		
	Semi-Gloss		WIDTH		<input type="checkbox"/> OK TO PRINT WITH CORRECTIONS AS MARKED		DESCRIPTION: INTERIOR LABEL				
	Lamination: No		6.25"		AUTHORIZED BY		DATE		REVISION LEVEL 41P		
	INK COLORS		8.75"						DESIGNER Joel Ortega		
Black Red 185		ROUND CORNER RADIUS						CHECKED BY			
								DATE 07/05/12			