



## 3B5M150D16 - Three-Phase Ventilated-USA-DOE

Product Details	
KVA	150.00
UPC#	
Enclosure	NEMA 3R Ventilated
Phase	Three-Phase
Line Voltage	208V-Delta
Load Voltage	480Y/277V
E/S Shielded	No
Windings	Aluminum
Temp. rise	150°
Frequency	60 Hz
Taps	1 - 5% FCAN; 2 - 5% FCBN


Product Details	
Efficiency Type	DOE-2016
Minimum Efficiency (35%)	98.83
Approvals	UL, cUL, DOE

Weight & Dimensions (Imperial / Metric)		
A	42.00"	106.68 cms
B	33.00"	83.82 cms
C	32.50"	82.55 cms
D	30.00"	76.2 cms
E	21.00"	53.34 cms
Est Ship Wt	1125.00 lbs	510.29 kg

### T208G Wiring Diagram & Connections

#### Wiring Diagram


Primary: 208 Volts Delta  
Secondary: 480Y/277 Volts



#### Connections

Primary Volts	On Each Coil Jumper Taps To	Primary Lines Connect To
218	1	X1, X2, X3
208	2	X1, X2, X3
198	3	X1, X2, X3
187	4	X1, X2, X3
Secondary Volts	Secondary Lines Connect To	
480	H1, H2, H3	
277 1 Phase	Between H0 and H1 or H2 or H3	

Figure 24



#### Additional Information

**How to Buy:** Contact Siemens Distributor, Siemens Sales Rep or Configure in COMPAS Configuration Tool

All specifications subject to change. Contact Factory for certified drawings. © 2019 Jefferson Electric, Inc.