

ATC 2070-1C CPU Module

CPU module description


The Linux-based 2070-1C module is a versatile CPU that brings the power of the next generation ATC controller to the 2070 platform while giving a scalable, cost-effective upgrade alternative for all model 2070 controllers compliant to TEES 2002 and TEES 2009.

Benefits include

- The 2070-1C provides an inexpensive and functional data security option for added support and convenience, leveraging existing investments
- Compatible with current NEMA, ITS and CALTRANS TEES 2002 and 2009 specifications

Features

- Open architecture Linux 2.6.39 operating system
- Network security with web interface management console
- Compatible with current approved TEES 2002 and TEES 2009 2070 hardware
- Capable of running multiple applications
- Environmentally hardened
- Board support package available for third party software development
- Flexible data storage options via USB, Datakey and SDHC memory devices



Highlights

- Open Architecture ensures compatibility with off-the-shelf products
- Standard Linux operating system
- Standard software modules from multiple sources
- Multitasking – each 2070-1C unit can control multiple applications
- High speed serial communications to CPU
- The ATC Engine board is a low-power design and particularly resistant in tough environmental conditions

Operating system features

- Embedded real time Linux Kernel
- All Linux drivers compliant to AASHTO, ITE and NEMA ATC standard version 5.2b with support for much of ATC 6
- Embedded software utilities:
 - Flash drive
 - RAM drive
 - MFIT validation suite for self-testing per ATC standard 5.2b

Technical specifications

- NXP MPC8309 333 MHz PowerQUICC™ II Pro embedded microprocessor
- Linux version 2.6.39
- 256 Megabytes of DRAM
- 512 Megabytes of FLASH
- 2 Megabytes of SRAM
- 2 Internal QUICC SDLC ports
- 2 Internal UART ports
- 3 External Zilog Z85230 UART/SDLC ports
- Supports 1 removable SDHC Memory card
- 4 IEEE 802.3-2002 10/100 Base-T Ethernet ports with auto switching capability
- 3 back haul ports
- 1 local port
- 2 Ethernet switches
- Supports 1 USB 2.0 high-speed devices
- Supports 5V and 3.3V Datakeys up to 32 Megabits
- Includes C/C++ Libraries: libstdc++.so.6.0.17 and glibc 2.19
- Caltrans TEES 2002/2009 compliant D type 25 pin C13S port
- Operating ambient temperature from -37 °C to +74 °C

Ordering information

- Part Number: AAD15753-002

Siemens Industry, Inc.
 9225 Bee Cave Road
 Building B, Suite 101
 Austin, TX 78733

1.512.837.8300

Subject to change without prior notice
 Order No.: DAT-70C-0117
 Printed in USA
 © 2017 Siemens Industry, Inc.

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.