



ORDER SUPPORT

3KC remote transfer switching equipment (RTSE)

End-to-end safety for user and systems






The 3KC transfer switching equipment provides secure switching between the main and an alternate network, even in case the main network is unavailable. Switching is handled via the off position. 3KC remotely operated transfer switching equipment (RTSE) guarantees high reliability of the power supply in systems that already have a separate control unit.



Product	Rated uninterrupted current I_u [A]	Article No.	Additional versions
3KC remote transfer switching equipment (RTSE)			
	Box terminal, 4-pole		
	40	3KC3424-2AA22-0AA3	
	63	3KC3426-2AA22-0AA3	
	80	3KC3428-2AA22-0AA3	
	100	3KC3430-2AA22-0AA3	
	125	3KC3432-2AA22-0AA3	
	160	3KC3434-2AA22-0AA3	
	Flat terminal, 3- and 4-pole		Number of poles 3 3-pole 4 4-pole
	250	3KC4 38-0CA21-0AA3	
	400	3KC4 42-0DA21-0AA3	
	630	3KC4 46-0EA21-0AA3	
	800	3KC4 48-0FA21-0AA3	
	1000	3KC4 50-0FA21-0AA3	
	1250	3KC4 52-0GA21-0AA3	
	1600	3KC4 54-0HA21-0AA3	
	2000	3KC4 56-0JA21-0AA3	
	2500	3KC4 58-0JA21-0AA3	
	3200	3KC4 60-0JA21-0AA3	
For the complete quotation, see Catalog LV 10, Chapter 9			

[siemens.com/switching-devices](https://www.siemens.com/switching-devices)

SIEMENS

Product	Version	Article No.	Additional versions	
Auxiliary switches				
	1 CO contact for each switching position O, I and II		↓ Contacts 1 with separate contacts 6 with linked common contacts	
	For 40 ... 160 A	3KC9603-□		
	1 CO contact for each switching position I and II			
	For 250 ... 630 A	3KC9803-1		
	For 800 ... 1600 A	3KC9803-2		
	For 2000 ... 3200 A	Included in the basic unit		
Auxiliary conductor terminal, scope of supply: 2 units				
	For 40 ... 160 A	3KC9622-2		
Phase barriers				
	For 250 ... 400 A	3KC9808-□	↓ Number of poles/quantity 1 3-pole/2 units 6 4-pole/3 units	↓ Number of poles/quantity 2 3-pole/2 units 7 4-pole/3 units
	For 630 A	3KC9808-□		
Terminal covers				
	4-pole, scope of supply: 2 units, 1 unit covers 4 poles		↓ Scope of supply (1 unit covers 1 pole) 1 3 units 2 4 units	↓ Scope of supply (1 unit covers 1 pole) 3 3 units 4 4 units
	For 40 ... 160 A	3KC9604-2		
	3 or 4 units, 1 unit covers 1 pole			
	For 250 ... 400 A	3KC9804-□		
	For 630 A	3KC9804-□		
Terminal plate				
	For 250 ... 400 A	3KC982 □ -1	↓ Number of poles 7 3-pole 8 4-pole	
	For 630 A	3KC982 □ -2		
	For 800 ... 1250 A	3KC982 □ -3		
	For 1600 A	3KC982 □ -4		
	For 2000 ... 3200 A	3KC982 □ -5		
Bridging bar for the load-side connection of the terminals				
	4-pole		Copper bar connection kit for bridging bars from 2000 A see catalog	
	For 40 ... 125 A	3KC9618-2		
	For 160 A	3KC9618-3		
	1-pole			
	For 250 A	3KC9818-2		
	For 400 A	3KC9818-3		
	For 630 A	3KC9818-4		
	For 800 ... 1000 A	3KC9818-5		
	For 1250 A	3KC9818-6		
	For 1600 A	3KC9818-7		
Dual power supply				
	For 40 ... 3200 A	3KC9625-1		
Autotransformer (AC 400 V/230 V)				
	40 ... 160 A	3KC9624-1		
	250 ... 3200 A	3KC9824-1		

All 3KC remote transfer switching equipment (RTSE) meet the standards of IEC 60947-6-1 and IEC 60947-3.
For the complete quotation, see Catalog LV10, Chapter 9

All 3KC remote transfer switching equipment (RTSE) meet the standards of IEC 60947-6-1 and IEC 60947-3.
For the complete quotation, see Catalog LV10, Chapter 9