



SIEMENS

PROCESS INSTRUMENTATION

Cost-efficient solutions for water consumption

Siemens Measurement solution helps manage our most precious resource

usa.siemens.com/pi



Benefits

Water metering is essential for the irrigation industry. As governments turn increasing attention towards the environment and how to protect valuable natural resources, new legislation targets water consumption in order to secure a reliable supply of water in the future.

For the irrigation industry, keeping a close eye on water consumption is more important than ever. It is necessary for several reasons, such as custody transfer, leakage protection, distribution purposes and much more.

As a dependable partner in the irrigation industry, Siemens has developed a broad range of instrumentation for precise measurements of flow, level and pressure.

By using Siemens instrumentation solutions, you can easily optimize the daily management of the irrigation cycle or district water supply. Efficient and reliable metering has the potential to provide cost benefits as processes are optimized and water use and waste are reduced.

- **Reliable.** Siemens instruments are truly fit-and-forget solutions for long term reliable measurement of our valuable water resource.

- **Single supplier.** With multiple technologies and solutions that meet all the needs of the irrigation industry, Siemens is a one-stop-shop for metering instrumentation.

- **Low total cost of ownership.** An investment in process instrumentation from Siemens pays off in the long run, as each meter is designed for longevity, precision and reliability.

- **Interface options.** Siemens meters have easy-to-use interface options that allow connection to third party GSM and satellite solutions.

- **Low flow metering.** Unlike mechanical meters that typically measure very low flow inaccurately or not at all; electronic meters from Siemens can easily handle such flow rates.

- **Siemens has global presence.** With offices and production spread around the world, we provide local sales and services close to where you are.

Water management made easy



SITRANS F M MAG 8000

Battery or mains powered electromagnetic flowmeter. Specially engineered for stand-alone applications, including revenue metering and irrigation.

SITRANS F M MAG 5100 W

Electromagnetic pulsed sensor for all water and wastewater applications. Increased low flow accuracy for water leakage detection.

SITRANS FS230

Clamp-on ultrasonic flow meter is suitable for virtually any liquid application, equipped with high accuracy of 0.5 to 1% of flow rate required to run your processes at peak efficiency.

SITRANS FS220

Basic but versatile clamp-on ultrasonic flowmeter. Compact design for easy installation. Available in single or dual channel configurations.

SITRANS Probe LU240

2-wire loop powered ultrasonic transmitter for level, volume and flow monitoring of liquids in open channels.

HydroRanger 200

Ultrasonic level controller for up to six pumps. Provides control, differential control and open channel flow monitoring.

SITRANS LUT440

High accuracy open channel monitor, which also provides a full suite of advanced level, volume and pump controls and data logging.

SITRANS P200

Is a compact, fixed range transmitter for measuring pressure with accurate monitoring of feed pump and pressure pump control.

Ultrasonic Level and Pressure



Product name	SITRANS Probe LU240	SITRANS LT500/ HydroRanger	SITRANS LUT440	SITRANS P200
Product category	Ultrasonic level	Level and open channel flow	Ultrasonic level and open channel flow	Pressure
Sensor Size	2" NPT	Radar sensor 1" or 1.50" NPT	Transducer dependent	½" NPT
Accuracy	± 0.15% of range	±0.25 of range	±1 mm plus 0.17 of measured range	Typically ±0.25%
Power Supply	24 V DC	12-30 V DC 100-230 V AC	10-32 V DC 100-230 V AC	10-36 V DC
Enclosure Rating	IP67 (NEMA 6) IP68 (NEMA 6)	IP54 (NEMA 3) panel version IP65 (NEMA 4X) wall version	IP65 (NEMA 4X)Wall mount	IP65 (NEMA 4X)
Data Output	HART, 4-20 mA	Up to 6 relays 4-20 mA HART, Modbus RTU, Profibus PA, Profibus DP, ProfiNet	3 Relays 4-20 mA Hart	2 wire, 4 to 20 mA 3 wire, 0 to 10 volts
Sensor Pipe Material	PVDF ETFE	PVDF	Kynar	316 stainless steel ceramic diaphragm
Approvals	Intrinsically safe Non-incendive General purpose	General purpose, CSA, FM, UL, CSA _{US}	CSA, FM, UL CSA Class I, Div. 2	n/a



Flow



Product name	SITRANS F M MAG 8000	SITRANS F M MAG 5100 W	SITRANS FS230	SITRANS FS220
Product category	Electromagnetic	Electromagnetic	Ultrasonic clamp-on	Ultrasonic clamp-on
Sensor Size	1" to 24"	1" to 48"	¼" to 394"	¼"to 394"
Accuracy	±0.4% of flow rate	±0.25% of flow rate	±0.5 to 1% of flow rate	±0.5-1% of flow rate
Power Supply	Mains powered Battery powered	12-24 V AC/DC 115-230 V AC	24 to 90 V DC, 100 to 240 V AC (universal power supply)	9 -36 V DC 100-240 V AC
Enclosure Rating	IP68 (NEMA 6P)	IP67 (NEMA 4X/6) IP68 (NEMA 6P)	IP66/67 (NEMA 4X)	IP65 (NEMA 4)
Data Output	2 pulse MODBUS RTU	1 current 1 digital 1 relay	2 temperature	2 current 1-2 relays (optional)
Sensor Pipe Material	Steel Concrete PVC	Steel Concrete PVC	All materials	All materials
Approvals	All water approvals OIML R49 MI-001	All water approvals OIML R49 MI-001	FM, FMc, ATEX, IECEx	UL ULC

One supplier is all you need

Designed for ease of use and lifelong reliability an investment in Siemens instrumentation equipment is an investment in the future.



As legislation constantly targets water consumption and the protection of valuable natural resources, knowing how much water is consumed is imperative for the district water and irrigation industries.

Efficient metering demand reliable products that do not get in the way of daily business. Customers want solutions that are easy to install and use.

Whether a need exists at the reservoir, field, or residential level, Siemens has an efficient and reliable solution that ensures precise metering with direct impact on your bottom line.

With our complete range of instrumentation devices including electromagnetic flow, ultrasonic flow, open channel flow, ultrasonic level and pressure technologies, Siemens has an answer for all of your irrigation needs.

Regardless of pipe type or size and the number of devices, we offer instruments for a wide range of applications, projects and installations throughout your irrigation network, including:

- large intake pipes
- distribution pipes
- individual pumps
- pumping stations
- on-farm metering

Contact your local sales office to see the difference Siemens instrumentation equipment makes.

Legal Manufacturer

Siemens Industry, Inc.
100 Technology Drive
Alpharetta, GA 30005
United States of America
Telephone: +1 (800) 365-8766
usa.siemens.com/pi
Order No.: PIBR-00049-0123

This document contains a general description of available technical options only, and its effectiveness will be subject to specific variables including field conditions and project parameters. Siemens does not make representations, warranties, or assurances as to the accuracy or completeness of the content contained herein. Siemens reserves the right to modify the technology and product specifications in its sole discretion without advance notice.