

BOX TERMINAL 3 PCS. ACCESSORY FOR: 3VA5 250



Model

Product brand name	SENTRON
Product designation	accessories

Connections according IEC

Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / finely stranded / minimum 	35 mm ²
<ul style="list-style-type: none"> • for copper cable / finely stranded / maximum 	150 mm ²
<ul style="list-style-type: none"> • for copper cable / stranded / minimum 	25 mm ²
<ul style="list-style-type: none"> • for copper cable / stranded / maximum 	185 mm ²
Wire stripping length	19 mm
Tightening torque / when using copper cables	
<ul style="list-style-type: none"> • stranded 	<= 35 mm ² : 6 Nm, >= 50 mm ² : 12 Nm
<ul style="list-style-type: none"> • finely stranded 	<= 35 mm ² : 6 Nm, >= 50 mm ² : 12 Nm

Connections according UL

Wire stripping length	0.75 in
Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / stranded / minimum 	4 AWG
<ul style="list-style-type: none"> • for copper cable / stranded / maximum 	350 kcmil

- for copper cable / finely stranded / minimum
- for copper cable / finely stranded / maximum






4 AWG
350 kcmil

Tightening torque / when using copper cables

- stranded
- finely stranded

<= 1 AWG: 70 lb-in, >= 1/0 AWG: 140 lb-in
<= 1 AWG: 70 lb-in, >= 1/0 AWG: 140 lb-in

Certificates

General Product Approval	EMC	Declaration of Conformity	other
 CSA	 UL	 EAC	 RCM
		 EG-Konf.	Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9233-0JA12>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9233-0JA12>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9233-0JA12

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/20/2017