



**Analytical Products and Solutions** 

## Flare Measurement

The Perfect Combination – Calorimeter and Process GC Continuous BTU for fast Fuel and Steam Control Speciation for fine Control and Quantification

usa.siemens.com/pa-environmental

The objective of the refinery sector rule or the upcoming olefin and chemical sector rule is to satisfy the regulatory requirements with high certainty, lowest cost and a simple and maintainable measurement system. Flare monitoring needs the speed to control the heat value for maximum combustion efficiency and to control auxiliary steam to minimize flare visibility. A calorimeter provides that speed but lacks the desirable speciation. A Process Gas Chromatograph (GC) provides the speciation to fine tune waste gas composition dependent steam addition, prevents over steaming, locates waste gas source and quantifies emission. Either technology alone could satisfy the regulatory requirements but does not provide the most reliable and best control scheme. The winning combination are both together. Over many years and hundreds of analyzers installed on flares, the relatively simple, long-term repeatable and reliable measurement systems have been proven successfully. By backing up each other, uninterrupted control and data availability is provided. Known technologies, often with on-site know-how available ensures independent and quick maintainability. A winning combination!







WIM Compas - On-line Heat Value for Fast Measurement

## **Continuous Speciated Measurement** On-line Process Gas Chromatograph MAXUM II®

Measurement:	H <sub>2</sub> (<1 min) N <sub>2</sub> (<1.5min) Air, C1-C3+ (1 min) Air, C1-C4+ (2 min) H <sub>2</sub> , O <sub>2</sub> , N <sub>2</sub> , CO <sub>2</sub> , C1-C5+ (3 min) H <sub>2</sub> O <sub>2</sub> N <sub>2</sub> CO <sub>2</sub> H <sub>2</sub> S (1-C5+
Related Measurements:	(Paraffine & Olefins) (7.5 min) H <sub>2</sub> S (0-300ppm) (3-5 min) Total Sulfur (3 min) Benzene (4 min)
Measurement Range: Linearity: Validation: Auxiliary Gas: Sample Temperature: Untime:	up to 0-100% 99.9% over 5 Magnitudes 3-point auto validation $H_2$ or He, Control Air 60° C up to 110° C typical >98 5%
External Standards:	typical 3

- Known technology widely in use
- Reliable and forgiving diaphragm valve
- Robust Thermal Conductivity Detector
- Utilizing known parallel chromatography with simple backflush only simplifies maintenance
- Single Validation cylinder for Low, Mid or High point

## Sample Conditioning System (Probe, Sample Transport, Blowback) Can be common for Process GC and Calorimeter

Design: Temperature: Auto Validation:

Traditional or Smart 60° C up to 120° C Typical 3 inlets

System Integration: 3-sided, Cabinet, Shelter Analyzer System Management System Monitoring:

Published by Siemens Industry, Inc. 1-800-964-4114

Process Industries and Drives 100 Technology Drive Alpharetta, GA 30005

Subject to change without prior notice Order No.: PIAFL-00082-0819 All rights reserved

case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are currency or completeness of the content contained herein. If with respect to any customer's particular applications. Our company reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.

## **Continuous Heat Value Measurement** On-line Calorimeter WIM Compas F®

Measurement:	BTU (5 to 30 sec)
Related Measurement:	Specific Gravity H <sub>2</sub>
Measurement Range:	0-3000 BTU
	0-100% H <sub>2</sub>
Т90:	5 sec
Validation:	Zero & Span or 3-point validation
Auxiliary Gas:	Instrument Air
	N <sub>2</sub> for H <sub>2</sub> measurement
Sample Temperature:	60° C up to 150° C
Uptime:	>99%

Uptime:

- Known technology widely in use
- Result update every 5 to 30 seconds
- Minimized Maintenance
- Single Validation cylinder for Low, Mid or High per calibration point

The refinery sector and the expected olefin and chemical rule provide analytical options. Calorimeter providing fast waste gas heat value measurement to control heat value and auxiliary steam addition. However, because steam addition depends also on the waste gas composition, Process GC provides the speciation to prevent over steaming.

- The key for long term measurement is simplicity and robustness. Calorimeter and Process GC designs are widely utilized and well known.
- · Common sample system design based on long time experience together with forgiving injection valves minimizing liquids or steam condensate intrusion greatly reducing prolonged off-line time and loss of data.
- Simplicity and known design enable on-site technicians to perform quick vendor independent maintenance preventing waiting for external support and prolonged down time.
- Only 3 external reference standards minimize operational costs and possibility of erroneous validation.

With hundreds of analyzers on flares, MAXUM® and WIM Compas<sup>®</sup> provide a proven, repeatable and maintainable turn-key analytical flare monitoring system to satisfy the most rigorous regulatory requirements. The simple known analytical solutions are typically maintainable by on-site technicians and utilize 3 external standards only. Complementing speed with speciation, validating and backing each other up to generate uninterrupted results for confident flare control. A winning combination!

For more information, please contact: Siemens Industry, Inc. 5980 West Sam Houston Parkway North Suite 500 Houston, TX 77041 Phone: 713-939-7400 Email: ProcessAnalyticsSales.industry@siemens.com usa.siemens.com/pa-environmental