



REVISION	DATE	BY	DATE	BY
		DRAWN	08/07/02	CY
		CHEK'D		
		VERIF'D		

Confidential - Property of <b>Siemens Industry, Inc.</b> Building Technologies Division		
CUSTOMER		
ORDER NO.	DWG. NO.	
	1D1Y025FCTP1	SH 1 OF 2

SIEMENS

<p>CATALOG NO. 1D1Y025FCTP1</p> <p>SERIAL NO. SERIES H</p> <p>25 kVA 60 Hz 1 PHASE</p> <p>3.5 % IMP AT 135 °C</p> <p>115 °C RISE °C AVG. AMBIENT</p> <p>220 °C TEMP CLASS °C MAX. AMBIENT</p> <p>PRIMARY ( H1 H3 H2 H4 ) 240X480 V</p> <p>SECONDARY(X4 X2 X3 X1 ) 120/240V V</p> <p>WINDING MATERIAL CU</p> <p>ENCLOSURE TYPE NEMA-3R WEIGHT 350 LBS</p> <p>ENERGY EFFICIENCY NEMA TP 1-2002</p> <p>SPACINGS BETWEEN ENCLOSURE AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 6 INCHES</p> <p>SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS DO NOT INSTALL IN AREAS ACCESSIBLE TO PUBLIC FOR INSTALLATION SEE INSTRUCTION MANUAL</p> <p>NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA</p>	<p>UL LR 3902</p> <p>UL F E112313</p> <p>LISTED DISTRIBUTION TRANSFORMER 77US TYPE F</p>	 <p style="text-align: center;">HAM1006</p>																								
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th style="width: 15%;">VOLTS</th> <th style="width: 85%;">INPUT LINE ON H1 &amp; H4 CONNECT</th> </tr> <tr> <td>504</td> <td>H2-1, H3-2</td> </tr> <tr> <td>492</td> <td>H3-2, H2-3</td> </tr> <tr> <td>480</td> <td>H2-3, H3-4</td> </tr> <tr> <td>468</td> <td>H3-4, H2-5</td> </tr> <tr> <td>456</td> <td>H2-5, H3-6</td> </tr> <tr> <td>444</td> <td>H3-6, H2-7</td> </tr> <tr> <td>432</td> <td>H2-7, H3-8</td> </tr> <tr> <td>252</td> <td>H2-1, H3-2</td> </tr> <tr> <td>240</td> <td>H2-3, H3-4</td> </tr> <tr> <td>228</td> <td>H2-5, H3-6</td> </tr> <tr> <td>216</td> <td>H2-7, H3-8</td> </tr> </table>			VOLTS	INPUT LINE ON H1 & H4 CONNECT	504	H2-1, H3-2	492	H3-2, H2-3	480	H2-3, H3-4	468	H3-4, H2-5	456	H2-5, H3-6	444	H3-6, H2-7	432	H2-7, H3-8	252	H2-1, H3-2	240	H2-3, H3-4	228	H2-5, H3-6	216	H2-7, H3-8
VOLTS	INPUT LINE ON H1 & H4 CONNECT																									
504	H2-1, H3-2																									
492	H3-2, H2-3																									
480	H2-3, H3-4																									
468	H3-4, H2-5																									
456	H2-5, H3-6																									
444	H3-6, H2-7																									
432	H2-7, H3-8																									
252	H2-1, H3-2																									
240	H2-3, H3-4																									
228	H2-5, H3-6																									
216	H2-7, H3-8																									
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th style="width: 15%;">VOLTS</th> <th style="width: 85%;">CONNECT</th> <th style="width: 10%;">OUTPUT LINE</th> </tr> <tr> <td>120</td> <td>X1-X3, X2-X4</td> <td>X1-X4</td> </tr> <tr> <td>240</td> <td>X2-X3</td> <td>X1-X4</td> </tr> <tr> <td>240/120</td> <td>X2-X3</td> <td>X1-X2-X4</td> </tr> </table>			VOLTS	CONNECT	OUTPUT LINE	120	X1-X3, X2-X4	X1-X4	240	X2-X3	X1-X4	240/120	X2-X3	X1-X2-X4												
VOLTS	CONNECT	OUTPUT LINE																								
120	X1-X3, X2-X4	X1-X4																								
240	X2-X3	X1-X4																								
240/120	X2-X3	X1-X2-X4																								





All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED  
SUITABLE FOR #2/0-6 CU/AL  
CONDUCTORS  
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED  
SUITABLE FOR 250MCM-6 CU/AL  
CONDUCTORS  
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of  
**Siemens Industry, Inc.**  
Building Technologies Division

REVISION	DATE	BY	DATE	BY	CUSTOMER
			08/07/02	CY	
			CHEK'D		
			VERIF'D		
					ORDER NO.
					DWG. NO.
					1D1Y025FCTP1
					SH 2 OF 2

0.1 jwen 2010/01/21 13:27