

SIEMENS

Ingenuity for life

Fewer Variants, More Options

SIRIUS 3RP25: The compact
multifunctional timing relay for all
common applications – worldwide

No matter how many timing relays you used to require to realize all common applications – from now on, one relay covers all needs: SIRIUS 3RP25. Thanks to its unrivalled functionality featuring up to 27 functions and wide voltage range from 12 to 240 V AC/DC, SIRIUS 3RP25 is the first choice for time-delayed switching.

Advantages at a glance

Minimum device variance

- Easy stock-keeping and logistics
- Easy configuration
- Reduced mounting and wiring costs

Modern, more compact housing

- Space savings in the control cabinet
- Versions in 17.5 and 22.5 mm width
- Removable terminals and wiring

Global applicability


- Approvals such as UL, CSA, EAC, etc.

Extended wide voltage range

- From 12 to 240 V AC/DC – consistent, in all functions


Advanced functionality

- Up to **27 time functions** according to DIN EN IEC 61812 in the multifunctional timing relay
- **Watchdog** for cycle time monitoring or attention control
- **Semiconductor output** for high switching frequencies, bounce-free and wear-free switching
- **Positively-driven contacts** for special requirements (e.g. temperature range, shock/vibration resistance and EMC) i.e. also “railway-compatible”



SIRIUS 3RP25 electronic timing relays: Wider range integrated functionality all within compact 17.5 and 22.5 mm housings

Code letter of the set function	13 functions	27 functions
	13 functions (A–M)	13 functions (A–M), 2 CO parallel switching + 13 functions (A–M), 1 CO delayed + 1 CO instantaneous switching + 1 star/wye-delta function
	1 CO 2 CO parallel switching 1 NO	1 CO + 1 CO with separate switching
A	ON delay	ON delay and <i>instantaneous switching</i>
B	OFF delay with control signal	OFF delay with control signal and <i>instantaneous switching</i>
C	ON/OFF delay with control signal	ON/OFF delay and <i>instantaneous switching</i>
D	Flashing, symmetrical, start with break	Flashing, symmetrical, start with break and <i>instantaneous switching</i>
E	Passing make contact function, interval relay	Passing make contact function, interval relay and <i>instantaneous switching</i>
F	Retriggerable interval relay with disconnected control signal (passing break contact function with control signal)	Retriggerable interval relay with disconnected control signal (passing break contact with control signal) and <i>instantaneous switching</i>
G	Passing make contact function, with control signal, not retriggerable (pulse-shaping with control signal)	Passing make contact function, with control signal, not retriggerable (pulse-shaping with control signal) and <i>instantaneous switching</i>
H	Additive ON delay, undelayed OFF with control signal	Additive ON delay, undelayed OFF with control signal and <i>instantaneous switching</i>
I	Additive ON delay with control signal	Additive ON delay with control signal and <i>instantaneous switching</i>
J	Flashing, symmetrical, start with pulse	Flashing, symmetrical, start with pulse and <i>instantaneous switching</i>
K	Pulse delay, pulse permanently set, pulse length 1s and pulse delay adjustable	Pulse delay, pulse permanently set, pulse length 1s and pulse delay adjustable and <i>instantaneous switching</i>
L	Pulse delay with control signal Pulse permanently set, pulse length 1s and pulse delay adjustable	Pulse delay, pulse permanently set, pulse length 1s and pulse delay adjustable and <i>instantaneous switching</i>
M	Retriggerable interval relay with connected control signal (watchdog)	Retriggerable interval relay with connected control signal (watchdog) and <i>instantaneous switching</i>
YΔ		Star/wye-delta function

Example: Function setting multifunctional timing relay 2 CO contacts with 27 functions	Function	Con- tacts	Time range	Rated control supply voltage U_s	Article No.
 <p>Time range selector switch Extended functional variety through time range selection and definition</p> <ul style="list-style-type: none"> • 2 CO contacts with parallel delayed switching: → left scale on the time range selector switch, or • 1 CO contact with delayed switching + 1 CO contact with instantaneous switching: → right scale on the time range selector switch <p>Function selector switch Selection of the function (see table) via setting A–M or star/wye-delta</p>	13 functions	1 CO	0.05 s – 100 h	12 – 240 V AC/DC	3RP2505-□AW30
		1 NO (SC)	0.05 s – 100 h	12 – 240 V AC/DC	3RP2505-□CW30
		2 CO ¹⁾	0.05 s – 100 h	24 – 240 V AC/DC	3RP2505-□RW30
	27 functions	2 CO	0.05 s – 100 h	12 – 240 V AC/DC	3RP2505-□BW30
	ON delay	1 CO	0.5 s – 10 s	12 – 240 V AC/DC	3RP2511-□AW30
		1 CO	1 s – 30 s	12 – 240 V AC/DC	3RP2512-□AW30
		1 CO	5 s – 100 s	12 – 240 V AC/DC	3RP2513-□AW30
		1 CO	0.05 s – 100 h	12 – 240 V AC/DC	3RP2525-□AW30
		2 CO	0.05 s – 100 h	12 – 240 V AC/DC	3RP2525-□BW30
	OFF delay with control signal	1 CO	0.05 s – 100 h	12 – 240 V AC/DC	3RP2535-□AW30
	OFF delay without control signal, non-volatile, passing make contact	1 CO	0.05 s – 600 s	12 – 240 V AC/DC	3RP2540-□AW30
		2 CO	0.05 s – 600 s	12 – 240 V AC/DC	3RP2540-□BW30
	Clock generator	1 CO	0.05 s – 100 h	12 – 240 V AC/DC	3RP2555-□AW30
	Star/wye-delta function	2 NO	1 s – 20 s (YΔ)	12 – 240 V AC/DC	3RP2574-□NW30
	2 NO	3 s – 60 s (YΔ)	12 – 240 V AC/DC	3RP2576-□NW30	

¹⁾ Positively-driven contacts
“suitable for railway applications”

Screw-type **1**
Spring-type **2**

Siemens Industry, Inc.
100 Technology Drive
Alpharetta, GA 30005
1-800-365-8766
info.us@siemens.com

Subject to change without prior notice.
Order No.: CPFL-3RP25-0119
Article No. DFCP-B10107-00-7600
All rights reserved
Printed in the USA
©2019 Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.