

**SIEMENS**

*Ingenuity for life*



# Sensing with SIRIUS 3SE Position and Safety Switches

Modular design for all applications

SIRIUS  
Command

[usa.siemens.com/limit-switches](http://usa.siemens.com/limit-switches)


# SIRIUS position switches

## Main advantages at a glance

- Reduced variance and stock-keeping costs due to modular design
- Plug-in design and a standardized interface simplify replacement and installation of the actuator heads
- All actuator heads can be rotated in 22.5° increments
- Quick-connect technology for plastic enclosures (31 mm) reduces mounting times by up to 25%
- Choice of connectors and rollers
- The entire ASIsafe electronics is integrated in a standard enclosure
- LED displays optionally available for all enclosures
- Higher degree of safety with redundant shutdown and additional signaling for versions with 3-pole contact blocks (enclosure dimensions as for 2-pole contact blocks)
- Versions with increased corrosion protection and for use down to -40 °C



The modular design of the standard position switches saves time and increases flexibility during installation of a whole range of switch versions.



Simple plug-in mounting

- 1 Open cover
- 2 Operate the locking lever
- 3 Replace the actuator head
- 4 Lock and close the cover



Quick-connect technology

- 1 Connect connection cable to terminals of contact block
- 2 Insert through slot into opening for screw connection

## Selection of basic switches

	Contacts	Plastic enclosure			Metal enclosure		
		31 mm width	40 mm width	50 mm width	31 mm width	40 mm width	56 mm width
→ Safety switch Positive opening operation according to IEC 60947-5-1							
Switching points according to ...	–	EN 50 047	EN 50 041	EN 50 047	EN 50 047	EN 50 041	EN 50 041
Mounting according to ...	–	EN 50 047	EN 50 041		EN 50 047	EN 50 041	
Degree of protection	–	IP65	IP66/IP67	IP66/IP67	IP66/IP67	IP66/IP67	IP66/IP67
Number of screw connections M20 x 1.5	–	1	1	2	1	1	3
Order number for basic switch with snap-action contacts <sup>1)</sup>	1NO/1NC	3SE5232-OCC05	3SE5132-OCA00	3SE5242-OCC05	3SE5212-OCC05	3SE5112-OCA00	3SE5122-OCA00
	1NO/2NC	3SE5232-OLC05	3SE5132-OLA00	3SE5242-OLC05	3SE5212-OLC05	3SE5112-OLA00	3SE5122-OLA00
Order number for basic switch with slow-action contacts <sup>2)</sup>	1NO/1NC	3SE5232-OBC05	3SE5132-OBA00	3SE5242-OBC05	3SE5212-OBC05	3SE5112-OBA00	3SE5122-OBA00
	1NO/2NC	3SE5232-OKC05	3SE5132-OKA00	3SE5242-OKC05	3SE5212-OKC05	3SE5112-OKA00	3SE5122-OKA00

# SIRIUS position switches: complete units

Our position switches can be ordered in a modular design or as complete units – already fitted with an actuator head. You will find further versions, such as compact switches, non-encapsulated designs or switches for ambient temperatures down to  $-40^{\circ}$  at: [siemens.com/industrial-controls/configurators](https://www.siemens.com/industrial-controls/configurators)

Plastic or metal enclosure 31 mm wide, according to EN 50 047, with snap-action contacts 1 NO/1NC



Order number, plastic	Order number, metal	Actuator	SR*	PR**
3SE5232-OCC05 →	3SE5212-OCC05 →	Rounded plunger + Teflon plunger	–	–
3SE5232-OHD03 →	3SE5212-0CD03 →	Roller plunger	–	X
3SE5232-OHE10 →	3SE5212-OCE10 →	Roller lever	–	X
3SE5232-OHF10 →	3SE5212-0CF10 →	Angular roller lever	–	X
3SE5232-OHK21 →	3SE5212-OCK21 →	Twist lever	–	X
3SE5232-OHK50	3SE5212-OCK50	Twist lever, infin. adj. length	–	X

Plastic or metal enclosure 40 mm wide, according to EN 50 041, with snap-action contacts 1 NO/1NC



Order number, plastic	Order number, metal	Actuator	SR*	PR**
3SE5132-0CB01 →	3SE5112-0CB01 →	Plain plunger, high-grade steel	–	–
3SE5132-OCC03 →	3SE5112-OCC02 →	Rounded plunger, high-grade steel	X	–
3SE5132-0CD05 →	3SE5112-0CD02 →	Roller plunger	X	–
3SE5132-OCE05 →	3SE5112-OCE01 →	Roller lever	–	X
3SE5132-0CF05 →	3SE5112-0CF01 →	Angular roller lever	–	X
3SE5132-0CJ01 →	3SE5112-0CH01 →	Twist lever	–	X
3SE5132-0CJ50	3SE5112-0CH50	Twist lever, infinitely adjustable length	–	X
3SE5132-0CJ80	3SE5112-0CH80	Rod actuator, aluminum	–	–
3SE5132-0CR01	3SE5112-0CR01	Spring rod	–	–

Plastic enclosure 50 mm wide, switching points according to EN 50 047, with snap-action contacts 1 NO/1NC



Order number, plastic	Actuator	SR*	PR**
3SE5242-OCC05 →	Rounded plunger with Teflon plunger	–	–
3SE5242-OHD03 →	Roller plunger	X	–
3SE5242-OHE10 →	Roller lever	–	X
3SE5242-OHK21 →	Twist lever	–	X
3SE5242-OHK50	Twist lever, adjustable length	–	X

Metal enclosure 56 mm wide, switching points according to EN 50 041, with snap-action contacts 1 NO/1NC



Order number, metal	Actuator	SR*	PR**
3SE5122-OCC02 →	Rounded plunger, high-grade steel	–	–
3SE5122-0CD02 →	Roller plunger	X	–
3SE5122-OCE01 →	Roller lever	–	X
3SE5122-0CH01 →	Twist lever	–	X
3SE5122-0CH50	Twist lever, infinitely adjustable length	–	X

→ = positive opening

\* – with high-grade steel roller

\*\* – with plastic roller

# Mechanical safety switches with separate actuators

Safety switches with a separate actuator are used where the position of doors, covers or protective grilles must be monitored for safety reasons. 3SE5 safety switches with a separate actuator without a locking device have the same enclosures as the 3SE5 position switches (modular system).

Safety switches with a locking device are special safety-related devices which prevent an unforeseen or intentional opening of protective doors, protective grilles or other covers for as long as a dangerous situation is present (i.e. follow-on motion of the switched-off machine).

## Safety switch with separate actuator, 5 approach directions, without locking device



Order number, plastic	Order number, metal	Enclosure/contact
3SE5232-ORV40	3SE5212-ORV40	31 mm / 1NC+1NO
3SE5232-OQV40	3SE5212-OQV40	31 mm / 2NC+1NO
3SE5132-OQV20	3SE5112-OQV10	40 mm / 2NC+1NO
3SE5242-OQV40	–	50 mm / 2NC+1NO
–	3SE5122-OQV10	56 mm / 2NC+1NO

## Safety switch with separate actuator, 5 approach directions, with locking device, position monitoring. Actuator: 1NO+2NC, magnet:1NO+2NC



Order number, plastic	Order number, metal	Enclosure width
Spring-actuated lock, with auxiliary release		54 mm
3SE5322-OSD21	3SE5312-OSD11	
Spring-actuated lock, with auxiliary release and lock		
3SE5322-OSE21	3SE5312-OSE11	
Magnetically locked		
3SE5322-OSB21	3SE5312-OSB11	

## Actuator



Article No.	Version	Length of actuator
3SE5000-0AV01	Standard metal	75.6 mm
3SE5000-0AW11	Standard plastic (not for switches with locking device)	40 mm
3SE5000-0AV02	With vertical fixing	53 mm
3SE5000-0AV03	With transverse fixing	47 mm
3SE5000-0AV05	Universal radius actuator	77 mm



### Actuators for standard position switch 3SE5 in plastic version 31 mm and 50 mm according to EN 50 047

		Order number		
			with plastic roller	with high-grade steel roller
Roller plunger	→	–	3SE5000-0AD03	3SE5000-0AD04
Roller lever with	Metal lever →	–	3SE5000-0AE10	3SE5000-0AE11
	High-grade steel lever →	–	3SE5000-0AE12	3SE5000-0AE13
Angular roller lever with	Metal lever →	–	3SE5000-0AF10	3SE5000-0AF11
	High-grade steel lever →	–	3SE5000-0AF12	3SE5000-0AF13
Spring rod with plastic plunger 143 mm (only for switches with snap-action contacts)		3SE5000-0AR01	–	–
Twist actuator +	→	+	3SE5000-0AK00 +	+
Twist lever 21 mm with	Metal lever →	–	3SE5000-0AA21	3SE5000-0AA22
	High-grade steel lever →	–	3SE5000-0AA31	3SE5000-0AA32
Adjustable-length twist lever with	Metal lever, infinitely adjustable	–	3SE5000-0AA50	3SE5000-0AA51
	Metal lever with grid bores →	–	3SE5000-0AA60	3SE5000-0AA61
Rod actuator in	Aluminum 200 mm	3SE5000-0AA80	–	–
	Plastic 200 mm	3SE5000-0AA82	–	–

### Actuators for standard position switches 3SE5, plastic version, 40 mm, according to EN 50 041

		Order number		
			with plastic roller	with high-grade steel roller
Plain plunger	→	3SE5000-0AB01	–	–
Roller plunger	→	–	3SE5000-0AD05	3SE5000-0AD06
Rounded plunger	→	3SE5000-0AC03	–	–
Roller lever with metal lever	→	–	3SE5000-0AE05	–
Angular roller lever with metal lever	→	–	3SE5000-0AF05	–
Spring rod with plastic plunger 143 mm (only for switches with snap-action contacts)		3SE5000-0AR01	–	–
Twist actuator +	→	+	3SE5000-0AH00 +	+
Twist lever, 27 mm with	Metal lever →	–	3SE5000-0AA01	3SE5000-0AA02
	High-grade steel lever →	–	3SE5000-0AA11	3SE5000-0AA12
Adjustable-length twist lever with	Metal lever, infinitely adjustable	–	3SE5000-0AA50	3SE5000-0AA51
	Metal lever with grid bores →	–	3SE5000-0AA60	3SE5000-0AA61
Rod actuator in	Aluminum 200 mm	3SE5000-0AA80	–	–
	Plastic 200 mm	3SE5000-0AA82	–	–

→ = positive opening



### Actuators for standard position switches 3SE5, metal version, 31 mm, according to EN 50 047

		Order number		
			with plastic roller	with high-grade steel roller
Plain plunger	→	3SE5000-0AB01	–	–
Roller plunger	→	–	3SE5000-0AD03	3SE5000-0AD04
Roller lever with	Metal lever →	–	3SE5000-0AE10	3SE5000-0AE11
	High-grade steel lever →	–	3SE5000-0AE12	3SE5000-0AE13
Angular roller lever with	Metal lever →	–	3SE5000-0AF10	3SE5000-0AF11
	High-grade steel lever →	–	3SE5000-0AF12	3SE5000-0AF13
Spring rod with plastic plunger 143 mm (only for switches with snap-action contacts)		3SE5000-0AR01	–	–
Twist actuator +	→	+	+	+
Twist lever, 27 mm with	Metal lever →	–	3SE5000-0AA21	3SE5000-0AA22
	High-grade steel lever →	–	3SE5000-0AA31	3SE5000-0AA32
Adjustable-length twist lever with	Metal lever, infinitely adjustable	–	3SE5000-0AA50	3SE5000-0AA51
	Metal lever with grid bores →	–	3SE5000-0AA60	3SE5000-0AA61
Rod actuator in	Aluminum 200 mm	3SE5000-0AA80	–	–
	Plastic 200 mm	3SE5000-0AA82	–	–

### Actuators for standard position switches 3SE5, metal version, 40 mm and 56 mm, according to EN 50 041

		Order number		
			with plastic roller	with high-grade steel roller
Plain plunger	→	3SE5000-0AB01	–	–
Rounded plunger with overtravel, high-grade steel	→	3SE5000-0AC02	–	–
Roller plunger, with overtravel	→	–	–	3SE5000-0AD02
Roller lever with	Metal lever →	–	3SE5000-0AE01	3SE5000-0AE02
	High-grade steel lever →	–	3SE5000-0AE03	3SE5000-0AE04
Angular roller lever with	Metal lever →	–	3SE5000-0AF01	3SE5000-0AF02
	High-grade steel lever →	–	3SE5000-0AF03	3SE5000-0AF04
Spring rod with plastic plunger 143 mm (only for switches with snap-action contacts)		3SE5000-0AR01	–	–
Twist actuator +	→	+	+	+
Twist lever, 27 mm with	Metal lever →	–	3SE5000-0AA01	3SE5000-0AA02
	High-grade steel lever →	–	3SE5000-0AA11	3SE5000-0AA12
Adjustable-length twist lever with	Metal lever, infinitely adjustable	–	3SE5000-0AA50	3SE5000-0AA51
	Metal lever with grid bores →	–	3SE5000-0AA60	3SE5000-0AA61
Rod actuator in	Aluminum 200 mm	3SE5000-0AA80	–	–
	Plastic 200 mm	3SE5000-0AA82	–	–

→ = positive opening

# SIRIUS 3SE6

## non-contact safety switches

RFID 3SE63 non-contact safety switches and 3SE66/67 magnetically operated switches comply with the highest SIL 3, PL e or Cat. 4 safety requirements for monitoring the positions of movable protective devices. The switch must be connected to a safety relay, e.g. SIRIUS 3SK1/3SK2, or a bus system, e.g. SIMATIC ET 200SP, for evaluation.



### Rectangular safety switches 25 mm x 91 mm

#### Non-contact RFID safety switches

An RFID safety switch consists of a coded RFID switch with an 8-pole M12 connection plug and an identical RFID actuator.



Order number	Description
<b>RFID safety switch</b>	
3SE6315-0BB01	Family coded
3SE6315-0BB02	Individually coded, multiple teach-in capability
<b>Actuator</b>	
3SE6310-0BC01	Standard
<b>Connection cable</b>	
3SX5601-2GA05	5 m, M12 socket, 8-pole

### Rectangular safety switch, large 25 mm x 88 mm or small 25 mm x 33 mm

#### Non-contact magnetically operated safety switch

A magnetically operated switch comprises a coded switching magnet and an identical contact block (sensor unit). The switches use reed contacts as mechanical contacts.



Order number	Description
<b>Magnetically operated switch, contact block 25x88 mm</b>	
3SE6604-2BA	With cable 3 m, 1NO+1NC
3SE6604-2BA01	With M8 plug, 4-pole, 1NO+1NC
<b>Actuator, switching magnet (coded), 25 x 88 mm</b>	
3SE6704-2BA	
<b>Magnetically operated switch, contact block 25x33 mm</b>	
3SE6605-3BA	With cable 3 m, 1NO+1NC
<b>Actuator, switching magnet (coded), 25 x 33 mm</b>	
3SE6704-3BA	
<b>Connection cable</b>	
3SX5601-3GA05	5 m, M8 socket, 4-pole

Technical information and support are available at [www.siemens.com/SIOS](http://www.siemens.com/SIOS) or in the Industry Online Support App.



Available for Android and iOS



**Siemens Industry, Inc.**

5300 Triangle Parkway  
Norcross, GA 30092

1-866-663-7324  
[info.us@siemens.com](mailto:info.us@siemens.com)

Subject to change without prior notice

Order No.: CCBR-T1812-0120

Article No.: SICP-B10007-00-7600

All rights reserved

Printed in USA

© 2020 Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.