

SIEMENS

Ingenuity for life



Energizing the evolution of eMobility

VersiCharge AC series

[siemens.com/versicharge](https://www.siemens.com/versicharge)


No application left behind

VersiCharge is the perfect fit for wherever you need charging

The VersiCharge AC charger is perfect for various applications including workplaces, retail, parking garages, multi-residential, all public charging, and home charging.

No matter where you need charging, you'll enjoy many benefits and features, such as an easy-to-use mobile app, smart building integration, flexible communication connections, faster charging and smart load management via OCPP.

Siemens VersiCharge AC chargers can be mounted to a wall or on a pedestal. The various accessories help you easily integrate it into any parking location.



Flexibility for the future

Smart building integration

VersiCharge AC chargers offer various communication interfaces for seamless integration to local and remote networks.



Modbus
Wi-Fi
Ethernet



Parent



...
9x



Children

Modular system configuration

By using the VersiCharge parent units as a communications gateway, the parent-child configuration options will help reduce investment and operational costs.

Flexible and elegant posts



ShortPole
single



ShortPole
cable
double



LongPole
cable
retract and light
single



LongPole
cable
retract
4-fold



Easy cloud
integration



Wi-Fi, Ethernet,
4G, and UMTS



easy to use
mobile app



Simple ID card
identification

Setting the stage

Benefits designed for you



Flexibility

- Modular and extend-able site configurations
- Various communication possibilities
- Wall or pole mounted



Robust and reliable

- Indoor and outdoor capable (IP56)
- Industry-leading safety features



Intuitive design

- Smart interface and easy usability
- Quick setup using the mobile app for iPhone and Android
- Integrated upstream electrical protection



State-of-the-art and Future-proof

- Tested EV interoperability
- Remote upgrade-ability
- Integrated MID metering



Integrity

- Cost-effective
- 3rd generation Versicharge AC Wallbox
- Quality made by Siemens



Making a difference

Key features

Compatibility with all common electric vehicles and applicable charging standards plus ease of use and comfort functions, such as delayed and planned charging, ensure a high degree of customer convenience.

Rugged housing suitable for outdoor applications (IP56 and IK10)

Status bar for information on identification, charging, and time delay

Integrated MID metering*

Status LEDs indicate system power, vehicle connection status, charging power, and fault indication

User authentication via RFID (Mifare classic, local whitelist and synching via OCPP)

Integrated 6 mA DC RCD protection provides installation cost savings

Amperage adjustment switch for five different current limit setting

Integrated high-performing dual band Wi-Fi

UMTS LTE / 4G connectivity for mobile network communication (parent units)

Status LEDs indicating connectivity, locked panel, and use of remote control

CE-certified for safety and interoperability

Touch-sensitive button for desired time delay and power level

Protective cover

Available with either a type 2 socket or a 7-m cable with a type 2 plug

RS485 Modbus RTU and Modbus TCP

*ERK compliant metering in development



More than charging

Experience the peace of mind

Siemens Versicharge Chargers have been standing for superior quality, ruggedness, and proven technology for more than a decade and have reliably provided millions of charges to electric vehicles (EVs). The new third-generation Versicharge AC series continues this tradition with numerous groundbreaking enhancements and is further supported by Siemens local and remote services.



Preventive
Maintenance

Corrective
Maintenance

Spare Parts

Digital
Services

Training

Support and
Consulting

Service Packages

We offer world-class services and support throughout the entire lifetime of your charging infrastructure, in this way assuring maximum uptime and the highest availability of your vehicles. Our cloud-based service packages Care and Care Plus look after your chargers using the dedicated Siemens service backend.

Care

The basic Care package is included during the warranty period and can be extended by subscription.

It ensures that firmware updates keep your chargers up to date as eMobility continues to evolve. Remote analyses and diagnostics are performed by our support center on demand.

Care Plus *

Enjoy all Care digital services and even more with our Care Plus package. Your charger will be proactively monitored and analyzed by our operation center. Firmware updates will be delivered with priority.

* coming soon

VersiCharge AC wallbox – technical data

Features and functions	
Charging mode	Mode 3
Vehicle connection	Type 2 socket, 32 A or 7-m cable with type 2/32 A plug
AC power output	Single phase: up to 7.4 kW or three-phase: up to 22 kW
Environment	Indoor and outdoor
Mounting options	Wall- and pole-mounting
Touch button	Time delay, return to max. power level
Charging status LEDs	Powered up, time delay, charging state, reduced power level, authentication
Communication / status LEDs	Connected / not connected during operation / signal strength during commissioning
Parent / child	Up to 9 child units per parent unit for combined communication to back-end
Load management	via OCPP
Communication	
Interfaces	Ethernet, Wi-Fi, Modbus RS-485, Modbus TCP/IP*, for parent units additionally GSM, LTE, 4G
User authentication	RFID card (local white-list, MiFare)
Configuration	via VersiCharge mobile app or VersiCharge PC Tool
Backend protocol	OCPP 1.6, upgradeable to OCPP 2.0.1
Software upgrade	Remote update possible
Electrical design	
Power supply voltage	Single phase: 230 V / 7,2 kW, three-phase: 400 V / 22 kW; 50/60 Hz.
Rated current settings	10 / 13 / 16 / 20 / 32 A
Cross wire section	Single phase: 10 mm ² , three-phase: up to 10 mm ²
Network Type	TT / TN, for single phase units additionally IT
Energy metering	integrated MID metering
AC ground fault detection	30 mA AC
DC leakage detection	≤6 mA DC
RCCB/ FI	not integrated
Voltage protection	integrated
Over-current protection	Current +10% above configured threshold, min. +2 A / 5 seconds
Operating altitude	2,000 m
General design	
IP and IK rating	IP 56, IK10
Dimensions (HxWxD)	446 x 180 x 158 mm (from rev. 01.XX.XX), 446 x 180 x 178 mm (from rev. 03.XX.XX)
Weight	cable: 1~ 5,3kg; 3~ 7.2kg / socket: 1~ 2.9kg; 3~ 5.0kg
Ambient conditions	Operating temperature: -30°C - +50°C, storage temp.: -40°C - +60°C, 98% non condensing
Colors	Silver metallic (Pantone 10077), Black
Certificates and standards	
Certifications	CE
Standards	EN IEC 61851-1, EN IEC 61851-21-2, EN IEC 60068-2-52, EN IEC 61000-6-1, EN 61000-6-3, EN IEC 61000-6-4, EN 330 330, EN 300 328, EN 301 511, EN 301 893, IEC 62955

IEC variants			Parent	Child
Single phase	Cable	without SIM card	8EM1310-2EJ04-3GA1	8EM1310-2EJ04-0GA0
		with SIM card	8EM1310-2EJ04-3GA2	
	Socket	without SIM card	8EM1310-2EH04-3GA1	8EM1310-2EH04-0GA0
		with SIM card	8EM1310-2EH04-3GA2	
Three-phase	Cable	without SIM card	8EM1310-3EJ04-3GA1	8EM1310-3EJ04-0GA0
		with SIM card	8EM1310-3EJ04-3GA2	
	Socket	without SIM card	8EM1310-3EH04-3GA1	8EM1310-3EH04-0GA0
		with SIM card	8EM1310-3EH04-3GA2	

*More Modbus Details: www.siemens.com/versicharge-mb

Published by
Siemens AG
Smart Infrastructure
Distribution Systems
Mozartstrasse 31C
91052 Erlangen, Germany

For the U.S. published by
Siemens Industry Inc.
100 Technology Drive
Alpharetta, GA 30005, United States

For more information, please contact
our Customer Support Center.
Phone: +49 180 524 70 00
Fax: +49 180 524 24 71
(Charges depending on provider)
E-mail: support.energy@siemens.com

Article No. SIDS-B10056-00-7600
Dispo 06200
fb 8780 WS 1220

© Siemens 2022

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

